


ELG, Aluminum Electrolytic, 680 μ F, 20%, 200 VDC, -25/+105°C**Dimensions**

D	22mm +/-1mm
L	50mm +/-2mm
S	10mm +/-0.5mm
LL	5.8mm +/-1mm
F	1.5mm +/-0.1mm

Packaging Specifications

Packaging:	Bulk, Bag
-------------------	-----------

General Information

Supplier:	KEMET
Series:	ELG
Dielectric:	Aluminum Electrolytic
Description:	Snap-In, Aluminum Electrolytic
RoHS:	Yes
Lead:	2 Pin
AEC-Q200:	No

Specifications

Capacitance:	680 μ F
Capacitance Tolerance:	20%
Voltage DC:	200 VDC, 250 VDC (Surge)
Temperature Range:	-25/+105°C
Rated Temperature:	105°C
Life:	2000 Hrs
Dissipation Factor:	15.00% 120Hz 20C
Resistance:	121 mOhms (20kHz)
Ripple Current:	1750 mAmps (120Hz)
Leakage Current:	2700 μ A (5min 20°C)