Product data sheet Characteristics

XB5AS8442

Emergency stop switching off, plastic, red mushroom Ø40, Ø22, trigger latching turn to release, 1 NC





Main

Range of product	Harmony XB5			
Product or component type	Emergency switching off push-button Emergency stop push-button			
Device short name	XB5			
Bezel material	Dark grey plastic			
Fixing collar material	Plastic			
Head type	Standard			
Mounting diameter	22 Mm			
Sale per indivisible quantity	1			
Shape of signaling unit head	Round			
Type of operator	Trigger action and mechanical latching			
Reset	Turn to release Push-pull			
Operator profile	Red mushroom Ø 40 mm, unmarked			
Contacts type and composition	1 NC			
Contact operation	Slow-break			
Connections - terminals	Screw clamp terminals, $<= 2 \times 1.5 \text{ mm}^2$ with cable end conforming to EN 60947-1 Screw clamp terminals, $>= 1 \times 0.22 \text{ mm}^2$ without cable end conforming to EN 60947-1			
Device presentation	Complete product			

Complementary

Height	43 Mm			
Width	40 Mm			
Depth	82 Mm			
Terminals description ISO n°1	(11-12)NC			
Resistance to high pressure washer	7000000 Pa at 55 °C, distance : 0.1 m			
Contacts usage	Standard contacts			
Positive opening	With conforming to EN/IEC 60947-5-1 appendix K			
Operating travel	1.5 Mm (NC changing electrical state) 4.3 Mm (total travel)			
Mechanical durability	300000 Cycles			
Tightening torque	0.81.2 N.M conforming to EN 60947-1			

Shane of scraw head	Cross compatible with Philips no 1 screwdriver			
Shape of screw head	Cross compatible with Philips no 1 screwdriver Cross compatible with pozidriv No 1 screwdriver Slotted compatible with flat Ø 4 mm screwdriver Slotted compatible with flat Ø 5.5 mm screwdriver			
Contacts material	Silver alloy (Ag/Ni)			
Short-circuit protection	10 A cartridge fuse type gG conforming to EN/IEC 60947-5-1			
[Ith] conventional free air thermal current	10 A conforming to EN/IEC 60947-5-1			
[Ui] rated insulation voltage	600 V (pollution degree 3) conforming to EN 60947-1			
[Uimp] rated impulse withstand voltage	6 KV EN 60947-1			
[le] rated operational current	3 A at 240 V, AC-15, A600 conforming to EN/IEC 60947-5-1 6 A at 120 V, AC-15, A600 conforming to EN/IEC 60947-5-1 0.1 A at 600 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 0.27 A at 250 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 0.55 A at 125 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 1.2 A at 600 V, AC-15, A600 conforming to EN/IEC 60947-5-1			
Electrical durability	1000000 Cycles, AC-15, 2 A at 230 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C 1000000 Cycles, AC-15, 3 A at 120 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C 1000000 Cycles, AC-15, 4 A at 24 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C 1000000 Cycles, DC-13, 0.2 A at 110 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C 1000000 Cycles, DC-13, 0.5 A at 24 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C			
Electrical reliability	Λ < 10exp(-6) at 5 V, 1 mA in clean environment conforming to EN/IEC 60947 Λ < 10exp(-8) at 17 V, 5 mA in clean environment conforming to EN/IEC 60947-5-4			
Environment Protective treatment	TH			
Ambient air temperature for storage	-4070 °C			
Ambient air temperature for operation	-4070 °C			
Overvoltage category	Class II conforming to IEC 60536			
IP degree of protection	IP66 conforming to IEC 60529 IP67 IP69 IP69K			
NEMA degree of protection	NEMA 13 NEMA 4X			
IK degree of protection	IK03 conforming to IEC 50102			
Standards	JIS C8201-5-1 EN/IEC 60204-1 EN/IEC 60947-5-1 EN/ISO 13850 CSA C22.2 No 14 EN/IEC 60947-5-4 EN/IEC 60947-1 UL 508 IEC 60364-5-53 EN/IEC 60947-5-5 JIS C8201-1			
Product certifications	GL LROS (Lloyds register of shipping) DNV UL listed RINA CSA BV			
Vibration resistance	5 gn (f= 2500 Hz) conforming to IEC 60068-2-6			
Shock resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming- to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming- to IEC 60068-2-27			



Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	59 G
Package 1 Height	4.4 Cm
Package 1 width	5.3 Cm
Package 1 Length	9 Cm
Unit Type of Package 2	S03
Number of Units in Package 2	80
Package 2 Weight	5.208 Kg
Package 2 Height	30 Cm
Package 2 width	30 Cm
Package 2 Length	40 Cm
Unit Type of Package 3	P06
Number of Units in Package 3	640
Package 3 Weight	51.964 Kg
Package 3 Height	77 Cm
Package 3 width	80 Cm
Package 3 Length	60 Cm


Offer Sustainability

Sustainable offer status	Green Premium product			
REACh Regulation	REACh Declaration			
REACh free of SVHC	Yes			
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EEU RoHS Declaration			
Toxic heavy metal free	Yes			
Mercury free	Yes			
RoHS exemption information	₫Yes			
China RoHS Regulation	China RoHS Declaration			
Environmental Disclosure	Product Environmental Profile			
Circularity Profile	End Of Life Information			
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins			

Contractual warranty

Warranty	18 months


Dimensions



e: clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)


Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board



- Diameter on finished panel or support
- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
 (3) Ø22.5 mm recommended (Ø22.3 0 +0.4) / Ø0.89 in. recommended (Ø0.88 in. 0 +0.016)

Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	40	1.57	30	1.18
By Faston connectors	45	1.77	32	1.26
On printed circuit board	30	1.18	30	1.18

Detail of Lug Recess



- Diameter on finished panel or support
- For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- Ø22.5 mm recommended (Ø22.3 $_0$ ^{+0.4}) / Ø0.89 in. recommended (Ø0.88 in. $_0$ ^{+0.016})

Commercialised Product Life Status: