

Robust, extended-cuff hand protection for food processing and heavy-duty jobs

- **Strong protection:** TouchNTuff® 92-665 nitrile gloves reliably protect in the event of accidental exposure to chemicals
- **Comfort and durability:** The soft yet tough nitrile offers a comfortable feel while resisting rips and tears
- **Longer length:** An extended cuff enhances protection over the wrist and forearm
- **Secure grip:** Textured fingertips help wearers confidently grip objects and tools
- **Ideal for food applications:** These gloves are compliant with food handling requirements



Industries

- Life Sciences
- Chemical
- Food Processing

Recommended For

- Transferring liquids and solids
- Sample taking and processing
- Handling incoming goods
- Maintenance
- All food processing, applications that have food contact

TECHNICAL DATA SHEET

	Product Information
External Glove Surface	Textured Fingers
Audit Standards	ISO 9001
Product Certification	ASTM D6319, Category III, EN ISO 21420:2020, EN ISO 374-1:2016 Type B JKT, EN ISO 374-5:2016 Virus, FDA21 CFR 177-2600-US Food Contact Approved, EU Food Contact Approved, ISO 9001, UKCA
Packaging Overview	100 gloves per dispenser 10 dispensers per case 1000 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Thailand
Product Segmentation	High Risk
Antistatic	Yes EN1149
Silicone Free	Yes
Vulcanization Chemical Accelerators	Zinc Dibutyldithiocarbamate (ZDBC) <i>Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.</i>

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	300 / 12		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.11 / 4.3		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.14 / 5.5		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 14	≥ 14	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412
Force at break (N)	≥ 6	≥ 6	EN 455-2

ORDERING INFORMATION

Size	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
Product Code	92665080	92665090	92665100

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region
MY +603 8310 6688
apac.medical@ansell.com
CN: +86 21 38275000
infochina@ansell.com
JP: +813 5549 8151
info.medical.jp@ansell.com

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region
BR +55 (11) 3356-3100
latam.medical@ansell.com
MX: +52 442 296 2050
latam.medical@ansell.com
CO: +57 1 288 3247
latam.medical@ansell.com

Australia
Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia
Ansell PYC
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

