



Identification	Type Part-No.	LOCC-Box-SK 7-6420 716420
Description	0V Collective Terminal Single-channel design maximum total current 40 A	
Input	Nominal voltage DC 12 / 24 V Rated current 6x max. DC 10 A Reverse voltage protection No Termination Spring terminal: 0.25–2.5 mm ²	
Load Side	Output current max. DC 40 A	
General	Operation temperature range -25 °C – 60 °C Storage temperature range -40 °C – 85 °C Dimensions (w x h x d) 8.1 x 114.5 x 116.0 mm Housing material PA 6.6 (UL 94-V0; NFF I2, F2) Field installation rail TS 35 (EN 50022)	

23.03.2015 – Subject to technical modification

Part-No. 716420

USA: LUTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273, USA
Tel. +1 (704) 504-0222 • Fax +1 (704) 504-0223
www.lutze.com • info@lutze.com

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk




SYSTEMATIC TECHNOLOGY


Technical data sheet • Load monitoring

Protection class	IP 20
Installation position	Optional
Weight (kg/piece)	0.700

Dimensions



PIN assignment



23.03.2015 – Subject to technical modification

Part-No. 716420

USA: LUTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273, USA
Tel. +1 (704) 504-0222 • Fax +1 (704) 504-0223
www.lutze.com • info@lutze.com

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk