

# 18V WHEELBARROW BL LXT

## DCU180ZX3

DCU180 is a motorised wheelbarrow powered by 18V Li-ion LXT battery.



### TECHNICAL SPECIFICATIONS

Forward speed (Hi/Lo)	3.5 / 1.5 km/h
Max climbing angle	12 °
Max loading capacity	130 kg
Reverse speed	1.0 km/h
Battery Type	Lithium-ion
Body only machine	✓
Voltage	18 v
Noise sound pressure	70 dB(A)
Noise K factor	3 dB(A)
Vibration K factor	1.5 m/sec <sup>2</sup>
Vibration	2.5 m/sec <sup>2</sup>
Net weight	32.5 kg

### USER BENEFITS

- Overload protection
- Constant speed control
- Electronic 2-speed selection.
- Soft start
- Reverse gear
- LED job light
- 3 stage adjustable handle
- Brake lever with locking mechanism
- Folding handle for compact storage.
- Rear wheels with stopper
- Width adjustable rear wheels (Width between left and right ends is adjustable from 480 mm to 760 mm)
- Rear wheels can be detached and replaced with standing legs
- Brushless motor
- Lock key necessary for start-up

