


### CamCleaner 800



#### Advantages

- Healthier employees
- Less cleaning
- Less asthma and allergy suffering
- Reduced environmental impact

**Applications:** Air purifier for all types of indoor environments, for example offices, homes, schools, public environments and where high quality air purification is required. Can be connected to outdoor air.

**Power supply:** 200..240V

**Filter:** E11.

**Installation:** Mobile or stationary.

**Design:** Stainless steel / White

**Average air purification area:** 120m<sup>2</sup>

Item no.	Item name	Dimensions (WxHxD) mm	Transport- dimensions (WxHxD) mm	Weight kg	Filter included in standard versions*
94000022	CamCleaner 800 Stainless steel	550x638x263	655x665x365	20	E11
94000042	CamCleaner 800 White	550x638x263	655x665x365	20	E11

\* Other filter classes available on request

#### Upgrades/Accessories/Exchange

Item no.	Item name	Filter class compliant with EN1822	Number per air purifier	Comments
<b>Upgrades</b>				
94000023	Hepa 13 (Includes 2 pcs H13 filter)	H13	2	
<b>Accessories</b>				
94000024	Molecular box with 3 pcs Camcarb Green-R 2600	VOC	1	
94000025	Suction side (outdoor connection)		1	
94000015	UK plug 230V, UK 50Hz		1	
94000034	Wheel plate		2	
94000032	Prefilter mats		2	
<b>Exchanges</b>				
	Main filter Micretain MXEM 11-252x610x150-00	E11	2	Standard
	Main filter Absolute MXE 13-252X610X150-00	H13	2	
	CamCarb Green-R 2600	VOC	3	

\* Other filter classes available on request

#### Operating specifications

Setting	Air flow m <sup>3</sup> /h	Energy consumption /W	Noise level dBA	System efficiency 0,3-0,4µm (%)
1	180	5	30	>95
2	250	6	33	>95
3	300	7	34	>95
4	347	8	35	>95
5	520	40	46	>95
6	720	124	56	>95