

TLR3A25DR006FTDG

✕ OBSOLETE

CGS | CGS TLR

TE Internal #: 4-1879378-7

TE Internal Description: TLR 2512 2.5W R006 1% 50PPM 2K RL

Metal Chip Resistor: Current Sense

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors > Metal Chip Resistor: Current Sense



Resistance Value: .006  $\Omega$

Resistor Type: **Current Sensing Resistor**

Package Size Code: 2512

Power Rating: 2.5 W

Passive Component Tolerance: 1 %

[All Metal Chip Resistor: Current Sense \(49\)](#)

Features

Product Type Features

Resistor Type	Current Sensing Resistor
Package Size Code	2512

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Resistance Value	.006 $\Omega$
Power Rating	2.5 W
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Usage Conditions

Temperature Coefficient	$\pm 50$ ppm/ $^{\circ}\text{C}$
-------------------------	----------------------------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance



For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2019 (201) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | CGS TLR



Surface Mount Resistors(41)

Customers Also Bought




TE Part #2337238-3  
TACT MINI GW 5.2X5.2X2 160GF



TE Part #1-830611-0  
LGH 1/2 SNGL MLD END



TE Part #3-2176307-2  
RP 1E 0.1W 26K1 0.1% 25PPM 5K RL




TE Part #7-1879648-1  
H4P 287R 0.5% 100PPM



TE Part #9-1625971-5  
HSA25 R01 10%



TE Part #7-1879354-5  
RR03 5% 390R AMMO



TE Part #3-1437162-8  
FSP-12A-11



TE Part #1-1879353-9  
RR02 5% 24K AMMO



TE Part #7-2176305-3  
RP 1E 0.1W 604R 0.1% 25PPM 5K RL



TE Part #2-2176392-9  
RQ 1206 261K 0.1% 10PPM 5K RL

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_4-1879378-7\_BA.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_4-1879378-7\_BA.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_4-1879378-7\_BA.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.