

### **FEATURES**

- Insulation Resistance >= 100 MO
- Neoprene O-Ring
- Brass nickel plated coupling nut

# RS PRO M12 FEMALE TO MALE STRAIGHT 8 PIN 8 WIRE 2m PUR CABLE

RS Stock No.: 2067658



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description ATTRIB<u>UTE 1</u>

### **M12 Connector Cable Assembly**

Brought to you under the trusted RS Brand, this range of M12 connector cable assemblies are commonly used in sensor and automation equipment. Fitted with a secure coupling nut, these RS M12 cable assemblies are an ideal solution for when reliable data transference is needed.

The M12 connector boasts a high degree of environmental protection, and is ideal for industrial use, with applications ranging from process control to commercial electronics.

#### Features and Benefits:

- Insulation Resistance >= 100  $M\Omega$
- Neoprene O-Ring
- · Brass nickel plated coupling nut

#### **General Specifications**

Rated Operational Voltage	30 V
Current Rating	2A
Insulation Resistance	>= 100 MΩ
Temperature Range	-25°C +75°C
Coding	A-Coded

#### **Material Specifications**

Grip Material	PU
Contact	Cu-Zn
Contact Plating	Gold Flash
Contact Carrier	Nylon 66
O-Ring	Neoprene
Grip Color	Black
Coupling Nut	Brass Nickel-Plated

## RS PRO M12 FEMALE TO MALE CONNECTOR



#### **Cable Specifications**

Cable Length-L	2 m
Cable Type	8 Core PUR Multi Strand
Sheath Color	Black
Cross Section of Wire	0.25 sq. mm
Core Dia	1.3 mm
Cable Dia	6.8 ± 0.1 mm

#### **Protection Category**

Degree of Protection IP67

#### **Additional Information**

Custom Tariff Number 85369090

#### **Approvals**

Standards Met IEC 61076-2-101


#### **Similar Products**

Stock No.	Brand	Product Name	Attribute 1	Attribute 2

## RS PRO M12 FEMALE TO MALE CONNECTOR



## Connection Diagrams / Assembly Diagrams / Illustrations / Accessories





All Dimensions are in mm.