

Product data sheet

Specifications



Repacked Multisound siren,
Harmony XVS, white colour, 106dB,
2tones, 12...24V AC DC

XVS10BMW



This repacked option saves 9.019 over the
standard condition

Main

Range of product	Harmony XVS
Product or component type	Siren
Device short name	XVS
Colour	White
Signalling type	2 tones siren
[Us] rated supply voltage	12 V AC/DC 24 V AC/DC
Noise level	106 dB (continuous or intermittent tone) at 1 m

Complementary

Material	PC: body
Product weight	0.8 kg
Marking	CE
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	300 mA at 24 V 500 mA
Clamping connection capacity	<= 1 x 1.5 mm²
Electrical connection	Cable: 6.5...8.5 mm
Width	114 mm
Height	114 mm
Depth	153.2 mm

Environment

Standards	IEC 60947-1 IEC 60947-5-1
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-30...50 °C
Electrical shock protection class	Class II conforming to IEC 61140
IP degree of protection	IP53

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number of Units in Package 1	1
Package 1 Height	19.500 cm
Package 1 Width	14.000 cm
Package 1 Length	14.000 cm
Package 1 Weight	1.032 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

9 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

Fe0ee3ab-dd49-4abe-bd8e-c49754e2c442

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No