




Switches > Tactile Switches



Contact Current Rating: 50 mA

Actuator Style: Round Actuator

Operating Function: Off (On)

Contact Base Material: Copper Alloy

Switch Contact Plating Material: Silver

Features

Product Type Features

Leg Style	Gull Wing
Switch Connection Type	Printed Circuit Board
Illuminated	Without
Actuator Style	Round Actuator

Configuration Features

Switch Feedback Type	Tactile
ESD Grounding Terminal	Without
Ganged	With
Operating Function	Off (On)
Support Bracket	Without
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single

Electrical Characteristics

Operating Voltage	24 VDC
-------------------	--------



Body Features

Case Material	LCP
Actuator Profile	Extended
Case Color	Black
Actuator Material	PPS
Cover Material	Steel
Actuator Force	160 g[5.64 oz]
Product Orientation	Vertical
Actuator Color	Black

Contact Features

Contact Current Rating	50 mA
Contact Base Material	Copper Alloy
Switch Contact Plating Material	Silver

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Housing Features

Low Profile	With
Process Sealed	No

Dimensions

Button Width	3.5 mm[.138 in]
Product Height	7 mm[.276 in]
Actuator Length	3.4 mm[.134 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C
-----------------------------	-------------

Packaging Features

Packaging Method	Package/Box
------------------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold







EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2-1977223-8 FSM14JSMAS=6MM TACT SWITCH, SMT 160gf	 TE Part # 1825910-6 FSM4JH=6MM TACT SWITCH, HIGH TEMP	 TE Part # 7-1437565-1 FSM91504F=TACT SWITCH SPECIAL	 TE Part # 2-1825910-7 FSM14JH=6MM TACT SWITCH, HIGH TEMP
 TE Part # 3-1437565-0 FSM2JSMATR=ON T/R	 TE Part # 4-1437565-2 FSM4JSMATR=TACT SWITCH 6X6MIL		

Also in the Series | Alcoswitch FSMJSMA

FSM6JSMATR

50 mA Tactile Switch, Round Actuator, Off (On), Copper Alloy, Silver Contact Plating,
Low Profile, 24 VDC, Alcoswitch FSMJSMA



Tactile Switches(22)

Customers Also Bought




TE Part #6609103-6
PM0S0DH60=C1239



TE Part #1-5499345-2
A/L UNIV HDR 64P RA SHT LAT



TE Part #10220685-00
CHPG-100K +/- 2% B 4075 +/- 1%
BT63-H



TE Part #CAT-C339-R529A
Thick Film Resistor: Current Sense




TE Part #2-1879355-4
RR03 5% 39K AMMO



TE Part #5-2176329-8
CRGP 1210 560K 1%



TE Part #CAT-H3399-CH8172
Heavy Duty Sealed Connector Series
Housings



TE Part #1825360-1
ADE02A04=2 POS DIP SWITCH

Documents

Product Drawings

FSM6JSMATR=TACT SWITCH 6X6MIL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-1437565-0_V1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-1437565-0_V1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_5-1437565-0_V1.3d_igs.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



[Datasheets & Catalog Pages](#)
[SWITCHES_CORE_PROGRAM_CATALOG](#)

English
[Products for Mobile Equipment](#)
English