




Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Wire**

Number of Positions: **4**

Centerline (Pitch): **4.14 mm [.162 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	2

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

Contact Features

Multiple Contact Types	Without
Contact Retention Within Housing	Without
Contact Type	Socket



Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	4.14 mm[.162 in]
Housing Color	Black
Housing Material	Nylon 66

Dimensions

Row-to-Row Spacing	4.14 mm[.162 in]
--------------------	------------------

Usage Conditions

Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Identification Marking

Circuit Identification Feature	With
--------------------------------	------

Industry Standards

CSA Rating	Certified, LR 7189
UL Rating	Recognized
Agency/Standard	CSA, UL
Approved Standards	UL E28476
UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	500
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------









EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 1-770988-1 MINI UMNL SOK 22-18AWG LP LF	 TE Part # 1-770985-0 MINI UMNL PIN 26-22AWG AU LP	 TE Part # 1-770987-0 MINI UMNL PIN 22-18 AWG AU LP	 TE Part # 770988-3 MINI UMNL SOK 22-18AWG AU LP
 TE Part # 1-770988-0 MINI UMNL SOK 22-18AWG AU	 TE Part # 1-794059-0 MINI UMNL PIN L/P LF	 TE Part # 770988-1 MINI UMNL SOK 22-18AWG SN LP	 TE Part # 770986-1 MINI UMNL SOK 26-22AWG SN LP



 TE Part # 794058-1 MINI UMNL SOK L/P	 TE Part # 170365-3 MINI UNIVERSAL M-N-L SOCKET LP	 TE Part # 170364-3 MINI UNIVERSAL M-N-L PIN LP	 TE Part # 770985-1 MINI UMNL PIN 26-22AWG SN LP
 TE Part # 1-794407-1 MINI UMNL SOK 20-16 AWG AU LF	 TE Part # 170363-3 MINI UNIVERSAL M-N-L PIN LP	 TE Part # 171638-1 MINI U-M-N-L PIN CONT. L.P	 TE Part # 171639-1 MINI U-M-N-L SOCKET L.P
 TE Part # 770903-3 MINI UMNL PIN 22-18 AWG AU	 TE Part # 170366-3 MINI UNIVERSAL M-N-L SOCKET LP	 TE Part # 794059-1 MINI UMNL PIN L/P	 TE Part # 170364-1 MINI UNIVERSAL M-N-L PIN LP

Also in the Series | Mini-Universal MATE-N-LOK

 Connector Contacts(9)	 Insertion & Extraction Tools(1)	 PCB Headers & Receptacles(1)	 Power Contacts(84)
 Rectangular Backshells & Clamps(2)	 Rectangular Boots & Strain Relief(2)	 Rectangular Connector Keying Plugs(2)	 Rectangular Connector Locking(2)



Rectangular Connector Seals(17)



Rectangular Power Connectors(243)

Customers Also Bought



TE Part #643075-3
Nylon PCB Connector Covers: 2.54 mm, MTA 100



TE Part #3-643813-3
Nylon Tin Plated Receptacle: 2.54 mm, with Mating Alignment, MTA 100



TE Part #3-643818-5
05P MTA156 CONN ASSY 20AWG YEL



TE Part #1-172159-2
MINI UNIVERSAL M-N-L CAP 4P



TE Part #5-1377175-4
SMP 0-0165035-0



TE Part #170362-4
MINI UNIVERSAL M-N-L SOCKET



TE Part #1825043-3
UP01DTANLA04,MICROSWITCH,SNAP



TE Part #292180-1
CAP ASS'Y W/O COMMONING TAB FO

Documents

Product Drawings
4 POS SR MINI UNIV

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-172167-9_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-172167-9_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-172167-9_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Product Specifications

Application Specification

English

Product Environmental Compliance

MD_1-172167-9_0606201875_dmtec

English

MD_1-172167-9_0606201875_dmtec

English

Instruction Sheets

Instruction Sheet (U.S.)

English