


# Actuator

22-  
335.111D

Distribution by  
Rs-online



<https://rs-online.eao.com/p/22-335.111D>

Your product:

---



## 22-335.111D Actuator

### FRONT

|                       |               |
|-----------------------|---------------|
| Front dimension:      | 36 mm x 24 mm |
| Front form:           | Rectangular   |
| Front bezel colour:   | Black         |
| Front bezel material: | Plastic       |

### MOUNTING

|                   |                |
|-------------------|----------------|
| Design:           | Flush          |
| Mounting cut-out: | 22 mm x 30 mm  |
| Mounting type:    | Panel mounting |

### ELECTRICAL CHARACTERISTICS

|                                          |                                                                                                                                                                                                                                                                                                       |
|------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Switching voltage and switching current: | 400 VAC, 10 A (ohmic)<br>400 VAC, 4 A (inductive, $\cos(\phi) = 0.7$ )<br>250 VAC, 5 A (inductive, $\cos(\phi) = 0.7$ )<br>125 VAC, 8 A (inductive, $\cos(\phi) = 0.7$ )<br>110 VDC, 0.4 A (inductive, L:R = 30 ms)<br>60 VDC, 1.5 A (inductive, L:R = 30 ms)<br>24 VDC, 6 A (inductive, L:R = 30 ms) |
| Contacts:                                | 1 NC / 1 NO                                                                                                                                                                                                                                                                                           |
| Switching rating:                        | 400 V @ 10 A                                                                                                                                                                                                                                                                                          |
| Electrical lifetime:                     | 50 000 cycles of operation                                                                                                                                                                                                                                                                            |
| Electric strength:                       | 2000 VAC, 50 Hz, 1 minute, as per IEC 60512-2-11 between all terminals and earth                                                                                                                                                                                                                      |

### MECHANICAL CHARACTERISTIC

|           |                |
|-----------|----------------|
| Terminal: | Screw terminal |
|-----------|----------------|

|                             |                                                                                                                                                                       |
|-----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Contact material:</b>    | Silver                                                                                                                                                                |
| <b>Switching action:</b>    | Rest (a) - Maintained                                                                                                                                                 |
| <b>Switching system:</b>    | Snap-action switching element                                                                                                                                         |
| <b>Switching system:</b>    | Self-cleaning, double-break snap action switching system (contact opening width 2 mm x 1.5 mm).<br>Max. 2 normally closed or 2 normally open contacts, or one of each |
| <b>Switching positions:</b> | 2 positions                                                                                                                                                           |
| <b>Switching angle:</b>     | 90° right                                                                                                                                                             |
| <b>Mechanical lifetime:</b> | 40 000 cycles of operation                                                                                                                                            |
| <b>Operating force:</b>     | 4.4 N ±1 N (1 switching element), 7.8 N ±1 N (2 switching element)                                                                                                    |
| <b>Operating Travel:</b>    | 5.5 mm ± 0.5 mm                                                                                                                                                       |
| <b>Travel:</b>              | > 3 mm                                                                                                                                                                |
| <b>Terminal details 1:</b>  | Max. wire cross-section 2 mm x 2.5 mm <sup>2</sup><br>Max. wire cross-section of stranded cable 2 x 1.5 mm <sup>2</sup>                                               |
| <b>Weight:</b>              | 0.051 kg                                                                                                                                                              |

## AMBIENT CONDITION

|                               |                                                                                        |
|-------------------------------|----------------------------------------------------------------------------------------|
| <b>IP Protection:</b>         | IP20 rear side, IP65 front side, according to IEC 60529                                |
| <b>Operating temperature:</b> | – 25 °C ... + 55 °C                                                                    |
| <b>Storage temperature:</b>   | – 40 °C ... + 95 °C                                                                    |
| <b>Shock resistance:</b>      | 50 g for 11 ms, according to IEC 60512-4-3                                             |
| <b>Vibration resistance:</b>  | 10 g at 10 Hz...2000 Hz, amplitude 0.75 mm (Sinusoidal), according to DIN EN 60512-4-4 |

## CERTIFICATE


|                      |                                                       |
|----------------------|-------------------------------------------------------|
| <b>Approbations:</b> | CB (IEC 61058-1), CSA, EAC, ENEC (EN 61058-1), UL     |
| <b>Conformities:</b> | CE, UKCA, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD) |
| <b>REACH:</b>        | REACH compliant                                       |
| <b>RoHS:</b>         | RoHS compliant                                        |

## OTHER


|                            |                                                                                                                         |
|----------------------------|-------------------------------------------------------------------------------------------------------------------------|
| <b>Short Description:</b>  | Actuator, 22 mm x 30 mm, 36 mm x 24 mm, Rectangular, Black, Plastic, 1 NC / 1 NO, Rest (a) - Maintained, Screw terminal |
| <b>Product attributes:</b> | Standard lock: DOM 311                                                                                                  |
| <b>Hints:</b>              |                                                                                                                         |

Standard lock: DOM 311


**Switching positions:**




**Wiring diagrams:**



**Mounting cut-outs:**



**Dimension drawings:**



A = Screw terminal  
B = Plug-in terminal 6.3 mm x 0.8 mm