



**Part Number :** [22284300](#)  
**Product Description :** KK 254 Breakaway Header,  
Vertical, 30 Circuits, Tin (Sn) Plating, Mating Pin Length  
6.09mm  
**Series Number :** 42375  
**Status :** Active  
**Product Category :** PCB Headers and Receptacles  
**Engineering Number :** 42375-0030



## Documents & Resources

### Drawings

[022284300 sd.pdf](#)  
[PK-40873-0041-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)  
[SOLIDWORKS](#)  
[Creo](#)  
[Symbol and Footprint \(Multi-Format\)](#)

### Specifications

[PS-10-07-001.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                                              |
|--------------------|--------------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Compliant with Exemption 44; 33                                                                              |
| China RoHS         | <br>per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                                 |
| Low-Halogen Status | Not Low-Halogen per IEC<br>61249-2-21                                                                        |
| REACH SVHC         | Not Contained per D(2025)4165-DC<br>(25 June 2025)                                                           |
| EU RoHS            | Compliant per EU 2015/863                                                                                    |

## Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

|                |                                                                                            |
|----------------|--------------------------------------------------------------------------------------------|
| Status         | Active                                                                                     |
| Category       | PCB Headers and Receptacles                                                                |
| Series         | 42375                                                                                      |
| Description    | KK 254 Breakaway Header, Vertical, 30 Circuits, Tin (Sn) Plating, Mating Pin Length 6.09mm |
| Application    | Board-to-Board, Signal, Wire-to-Board                                                      |
| Component Type | PCB Header                                                                                 |
| Product Name   | KK 254                                                                                     |
| UPC            | 800753786288                                                                               |

### Agency

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

### Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum             | 500V |

### Physical

|                                |                                |
|--------------------------------|--------------------------------|
| Breakaway                      | Yes                            |
| Circuits (Loaded)              | 30                             |
| Circuits (maximum)             | 30                             |
| Color - Resin                  | Black                          |
| Durability (mating cycles max) | 25                             |
| First Mate / Last Break        | No                             |
| Flammability                   | 94V-0                          |
| Glow-Wire Capable              | No                             |
| Guide to Mating Part           | No                             |
| Keying to Mating Part          | None                           |
| Lock to Mating Part            | None                           |
| Material - Plating Mating      | Tin                            |
| Material - Resin               | High Temperature Thermoplastic |
| Net Weight                     | 1.944/g                        |
| Number of Rows                 | 1                              |
| Orientation                    | Vertical                       |
| Packaging Type                 | Bag                            |
| PCB Locator                    | No                             |
| PCB Retention                  | None                           |
| PCB Thickness - Recommended    | 1.60mm                         |
| PC Tail Length                 | 3.18mm                         |
| Pitch - Mating Interface       | 2.54mm                         |
| Polarized to Mating Part       | No                             |
| Polarized to PCB               | No                             |
| Shrouded                       | No                             |
| Stackable                      | No                             |
| Temperature Range - Operating  | See Product Specification      |
| Termination Interface Style    | Through Hole                   |

### Solder Process Data

|                              |      |
|------------------------------|------|
| Max-Duration                 | 5    |
| Lead-Free Process Capability | WAVE |
| Max-Cycle                    | 1    |
| Max-Temp                     | 235  |

---

# Mates With / Use With

## Mates with Part(s)

| Description                                    | Part Number |
|------------------------------------------------|-------------|
| KK 254 Single Row Crimp Housings               | <u>2695</u> |
| KK 254 Receptacle Housings                     | <u>7880</u> |
| KK 254 PC Board Connector                      | <u>4455</u> |
| 2.54mm Pitch C-Grid Shunt<br>Terminal Housings | <u>7859</u> |