




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **20**

Number of Rows: **2**

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Fully Shrouded
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Signal Positions	20
Connector Contact Load Condition	Fully Loaded
Stackable	No
PCB Mount Orientation	Vertical
Number of Positions	20
Number of Rows	2

Electrical Characteristics

Operating Voltage	125 VAC
-------------------	---------



Dielectric Withstanding Voltage (Max)500 VAC

Body Features

Connector Profile	Standard
Primary Product Color	Black

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	.5 µm[19.69 µin]
PCB Contact Termination Area Plating Material Finish	Bright
Contact Mating Area Plating Material Thickness	.38 µm[14.96 µin]
Mating Square Post Dimension	.5 mm[.02 in]
PCB Contact Termination Area Plating Material Thickness	2 µm[78.74 µin]
Contact Shape & Form	Square
Contact Layout	Inline
Contact Mating Area Length	3.6 mm[.142 in]
Contact Base Material	Brass
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Pin
Contact Current Rating (Max)	2 A

Termination Features

Square Termination Post & Tail Dimension	.5 mm[.02 in]
Termination Method to PCB	Surface Mount

Mechanical Attachment

Mating Retention Type	Locking Ramp
Mating Retention	With
Mating Alignment Type	Polarizing Slot
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	PA9T GF
Centerline (Pitch)	2 mm[.079 in]

Dimensions

--	--



Row-to-Row Spacing	2 mm[.079 in]
Connector Width	6.3 mm[.248 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Connector Height	6.4 mm[.252 in]
Connector Length	22.65 mm[.892 in]

Usage Conditions

Housing Temperature Rating	High
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Operation/Application

Assembly Process Feature	Pick and Place Cover
Circuit Application	Signal

Industry Standards

Compatible With Agency/Standards Products	UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2-2316109-0

20P,2MM,REC,HSG,DR,CRIMP,LCK  
RAMP,BOX

Also in the Series | AMPMODU 2 mm

Board-to-Board Headers & Receptacles(8160)

Connector Contacts(27)

PCB Headers & Receptacles(8190)

Wire-to-Board Connector Assemblies & Housings(202)

Wire-to-Board Headers & Receptacles (1037)

Customers Also Bought



TE Part #1-2214574-0  
2X2 QSFP CAGE AND PT  
CONNECTOR ASSEMBLY

TE Part #1-2227669-0  
ZQSFP+ STACKED REC ASSEMBLY  
2X1,4LP DOWN

TE Part #CAT-D33047-SO1339  
DDR4 SO DIMM Sockets

TE Part #2357739-2  
16G,05FH,REC,220PIN,4H,HT W/ CAP

TE Part #2298896-8  
2X1 QSFP+ SPRING CAGE AND  
CONNECTOR

TE Part #2198325-7  
zSFP+ STACKED 2X2 RECEPTACLE  
ASSEMBLY

TE Part #2357798-2  
16G,05FH,plug,220P,8H,HT, W/ CAP

TE Part #2357787-3  
16G,05FH,plug,220P,5H,emboss, W/  
CAP

TE Part #2007492-6  
SFP+assy2x1Spring Fingers Inner LP Sn

Documents

Product Drawings

20P,2MM,SHRD HDR,DRV,T,SMD,0.38AU,TR W/CP

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2-2842241-0\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-2842241-0\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-2842241-0\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English