

Cable housing - PH 1,5/S/12 - 3212840

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable housing, Length: 19.9 mm, Width: 42 mm, Height: 36.8 mm, Number of positions: 12, Color: gray


The figure shows the PH 1.5/S/6 version

Why buy this product

- ✓ Robust cable housing for strain relief on connecting cables
- ✓ Can be aligned without any loss of pitch
- ✓ Additional scope for marking plugs



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 573610
Weight per Piece (excluding packing)	14.2 g
Custom tariff number	85472000
Country of origin	Poland
Note	Made to Order (non-returnable)

Technical data

General

Color	gray
Inflammability class according to UL 94	V0
Number of positions	12

Dimensions

Width	42 mm
Length	19.9 mm
Height	36.8 mm

Cable housing - PH 1,5/S/12 - 3212840

Classifications

eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27141145
eCl@ss 5.1	27141145
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120

ETIM

ETIM 4.0	EC000437
ETIM 5.0	EC000451

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121411
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411