

Sensor/Actuator cable - SAC-5P-10,0-28R/FS SCO RAIL - 1407333

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sensor/Actuator cable, 5-position, RADOX® GKW S halogen-free, black, shielded, free cable end, on Socket straight M12 SPEEDCON, A-coded, Cable length: 10 m, For railway applications

Why buy this product

- ✓ Easy and safe: 100% electrically tested plug-in components
- ✓ Safety thanks to flame retardancy: PA 6.6 grip and RADOX® cable meet the highest requirements
- ✓ Securely locked by special vibration brake
- ✓ Resistant to temperature influences – tested for an extended temperature range and for resistance to temperature shocks
- ✓ Reliable signal transmission – 360° shielding in environments with electromagnetic interference



Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 774499 |
| Weight per Piece (excluding packing) | 743.0 g |
| Custom tariff number | 85444290 |
| Country of origin | Poland |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|-----------------|------|
| Length of cable | 10 m |
|-----------------|------|

Ambient conditions

| | |
|---------------------------------|----------------------------------|
| Ambient temperature (operation) | -40 °C ... 85 °C (Plug / socket) |
| Degree of protection | IP65 |

General

| | |
|-----------------------|------|
| Rated current at 40°C | 4 A |
| Rated voltage | 60 V |
| Number of positions | 5 |

Sensor/Actuator cable - SAC-5P-10,0-28R/FS SCO RAIL - 1407333

Technical data

General

| | |
|------------------------------|-------------------------------|
| Contact resistance | ≤ 5 mΩ |
| Insulation resistance | ≥ 100 MΩ |
| Coding | A - standard |
| Standards/regulations | M12 connector IEC 61076-2-101 |
| Status display | No |
| Protective circuit/component | Unwired |
| Surge voltage category | II |
| Pollution degree | 3 |
| Insertion/withdrawal cycles | ≥ 100 |
| Torque | 0.4 Nm (M12 connector) |

Material

| | |
|---|------------------------------|
| Inflammability class according to UL 94 | V0 |
| Contact material | CuSn |
| Contact surface material | Ni/Au |
| Contact carrier material | PA 6.6 |
| Material of grip body | PA 6.6 |
| Material, knurls | Zinc die-cast, nickel-plated |
| Sealing material | NBR |

Cable

| | |
|---|---|
| Cable type | Shielded black RADOX® |
| Cable type (abbreviation) | 28R |
| Conductor cross section | 5x 0.5 mm² |
| AWG signal line | 20 |
| Conductor structure signal line | 19x 0.18 mm |
| Core diameter including insulation | 1.43 mm |
| Wire colors | White 1, white 2, white 3, white 4, white 5 |
| Overall twist | 5 cores, twisted |
| Shielding | Tinned copper braided shield |
| External sheath, color | black |
| External cable diameter D | 6.2 mm ±0.3 mm |
| Minimum bending radius, fixed installation | 3 x D |
| Minimum bending radius, flexible installation | 4 x D |
| Cable weight | 70 kg/km |
| Outer sheath, material | RADOX® GKW S |
| Material conductor insulation | RADOX® TI303 |
| Conductor material | Tin-plated Cu litz wires |
| Conductor resistance | ≤ 40.1 Ω/km |
| Nominal voltage, cable | 600 V AC (Core-ground, U ₀) |
| | 1000 V AC (Core-ground, U) |

Sensor/Actuator cable - SAC-5P-10,0-28R/FS SCO RAIL - 1407333

Technical data

Cable

| | |
|---------------------------------|---|
| | ≤ 720 V AC (core-ground) |
| | ≤ 1200 V AC (Core-ground, U _m) |
| | ≤ 900 V DC (Core-ground, V ₀) |
| | ≤ 1500 V DC (core-core) |
| Test voltage, cable | 3500 V AC (50 Hz, 5 min.) |
| | 8400 V DC (50 Hz, 5 min.) |
| Special properties | Fire protection in rail vehicles NF F16-101 Category A1, A2, B |
| | Fire protection in rail vehicles NF F16-101 Class C/F0 |
| | Fire protection in rail vehicles according to DIN 5510 Risk level 1 - 4 |
| | Fire protection in rail vehicles according to CEI 11170 Risk level LR1 - LR4 |
| | Fire protection in rail vehicles according to CEN/TS 45545 Risk level HL1 - HL3 |
| Flame resistance | According to EN 60332-1-2 |
| | according to EN 50305, 9.1.2 |
| Halogen-free | According to EN 50267-2-1 |
| Concentration of fumes | according to EN 61034-2 |
| Fume corrosiveness | according to EN 50267-2-2 |
| Fume toxicity | according to EN 50305, 9.2 |
| Ambient temperature (operation) | -40 °C ... 120 °C (cable, fixed installation) |
| | -25 °C ... 90 °C (cable, flexible installation) |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27060306 |
| eCl@ss 4.1 | 27060306 |
| eCl@ss 5.0 | 27061801 |
| eCl@ss 5.1 | 27061801 |
| eCl@ss 6.0 | 27061801 |
| eCl@ss 7.0 | 27061801 |
| eCl@ss 8.0 | 27279218 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC001855 |
| ETIM 4.0 | EC001855 |
| ETIM 5.0 | EC001855 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 31251501 |
| UNSPSC 7.0901 | 31251501 |
| UNSPSC 11 | 31251501 |

Sensor/Actuator cable - SAC-5P-10,0-28R/FS SCO RAIL - 1407333

Classifications

UNSPSC

| | |
|--------------|----------|
| UNSPSC 12.01 | 31251501 |
| UNSPSC 13.2 | 31251501 |

Accessories

Accessories

Conductor marking

Insert label - PABA WH/15 - 1013151



Insert label, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Thread on, Cable diameter: 0.6-50 mm, Lettering field: 15 x 4 mm

Insert label - PABA YE/15 - 1013698



Insert label, Strip, yellow, unlabeled, can be labeled with: Plotter, Mounting type: Thread on, Cable diameter: 0.6-50 mm, Lettering field: 15 x 4 mm

Insert label - PABA RD/15 - 1013944



Insert label, Strip, red, unlabeled, can be labeled with: Plotter, Mounting type: Thread on, Cable diameter: 0.6-50 mm, Lettering field: 15 x 4 mm

Cutting tools

Diagonal cutter - CUTFOX-S VDE - 1212207



Diagonal cutter for copper and aluminum conductors, VDE-tested

Marker carrier cable

Sensor/Actuator cable - SAC-5P-10,0-28R/FS SCO RAIL - 1407333

Accessories

Conductor marker carrier - PATG 2/15 - 1013038



Conductor marker carrier, transparent, unlabeled, Mounting type: slide on, Cable diameter: 2-4 mm, Lettering field: 4 x 15 mm

Conductor marker carrier - PATG 3/15 - 1013041



Conductor marker carrier, transparent, unlabeled, Mounting type: slide on, Cable diameter: 4-7 mm, Lettering field: 4 x 15 mm

Conductor marker carrier - PATG 4/15 - 1013054



Conductor marker carrier, transparent, unlabeled, Mounting type: slide on, Cable diameter: 6-10 mm, Lettering field: 4 x 15 mm

Marker pen

Marker pen - B-STIFT - 1051993



Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm

Protective cap

Screw plug - PROT-M12 MS-PA-CHAIN - 1430899



M12 sealing cap with fixing band, for sensor cables, for free M12 sockets

Safety locking

Sensor/Actuator cable - SAC-5P-10,0-28R/FS SCO RAIL - 1407333

Accessories

Locking clip - SAC-M12-EXCLIP-F - 1558991



Screwdriver tools

Adapter insert - TSD-M SAC-BIT ADAPTER - 1212600



Adapter bit for TSD-M...torque tools, E6.3-1/4" drive with 4 mm hexagon to accommodate SAC bits

Tool - SAC BIT M12-D15 - 1208432



Nut for assembling sensor/actuator cables with M12 connector and for M12 connectors with QUICKON fast connection technology, for 4 mm hexagonal drive

Stripping tool

Stripping tool - WIREFOX SAC-1 - 1212757



Stripping pliers, for halogen-free sensor/actuator cables (SAC cables), with PUR and PVC insulation, from Ø of 3.2 to 4.4 mm, any stripping length

Stripping tool - WIREFOX SAC - 1212623



Stripping pliers, for halogen-free sensor/actuator cables (SAC cables), with PUR and PVC insulation, from Ø of 4.4 to 7 mm, any stripping length

Sensor/Actuator cable - SAC-5P-10,0-28R/FS SCO RAIL - 1407333

Accessories

Stripping tool - WIREFOX 10 - 1212150



Stripping tool, for cables and conductors from 0.02 - 10 mm², self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm² stranded/1.5 mm² solid, replaceable stripping blade

Torque tool

Torque screwdriver - TSD 04 SAC - 1208429



Torque screwdriver, with preset torque of 0.4 Nm and 4 mm hexagonal drive for M12 connectors


Torque screwdriver - TSD-M 1,2NM - 1212224



Torque screw driver, accuracy as per EN ISO 6789 standard, adjustable from 0.3 - 1.2 Nm

Drawings

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view


Cable cross section



Shielded black RADOX[®] [28R]

Sensor/Actuator cable - SAC-5P-10,0-28R/FS SCO RAIL - 1407333

Dimensioned drawing



Circuit diagram



Socket M12-SPEEDCON, straight, shielded

Contact assignment of the M12 socket