

# RING TONGUE TERMINALS WITH CONTAINED PALM A30B-M10/19

*for L.V. circuit breakers for copper conductors*

This range of terminals features contained palm width and has been specifically developed for application on L.V. circuit breakers with reduced space terminal blocks. The contained palm width allows an immediate and easier installation.


Cembre terminals are manufactured from electrolytic copper tube. The specifically designed section of the barrel and the choice of principal dimensions are optimising the best combination of mechanical strength and electrical conductivity. These terminals are annealed to guarantee optimum ductility and are electrolytically tin-plated to avoid oxidation.

The barrel is provided with an internal taper to ease the introduction of the conductor; furthermore, its length grants a comfortable and correct positioning between dies, during crimping operations. Each palm is marked with the Cembre logo and part number.

Manufactured from electrolytic copper tube Cu-OF CW008A conform to UNI EN 13600



CERTIFICATES 

 E125401

# RING TONGUE TERMINALS WITH CONTAINED PALM **A30B-M10/19**

## *Technical characteristics*

### PROPERTIES

Width	19 mm
Length	70 mm
Diameter	16.7 mm
Diameter of the hole	10.5 mm
Pack qty	50
Min. pack qty	25
M	18 mm
N	9 mm
Ø Stud mm	10 mm
Maximum diameter of the stripped cable	16.7 mm
Without inspection hole	Y
Material (Body)	ETP Copper elettrolytically tinned
Material (Seam)	ETP Copper elettrolytically tinned

