On-off/soft-start valves MS-EM/EE/DL/DE, **MS** series





Festo Core Range

Solves the majority of your automation tasks

the most important products and functions from our broad product catalogue, and added the quickest delivery.

With the Festo Core Range, we have selected

The Core Range offers you the best value

for your automation tasks.

Worldwide: Simply good:

Fast:

Quickest delivery - wherever, whenever Expected high Festo quality Easy and fast to select



Service unit components of the MS series

Solutions for every application

With its large product range, highly effective components and a wide choice of functions, the MS series from Festo offers a complete concept for compressed air preparation. It is suitable for simple standard applications as well as application-specific solutions with very high quality requirements. Available as individual components, pre-assembled combinations ex-stock,

application-specific combinations or complete turnkey solutions. The five sizes in the MS series achieve maximum flow rates with low space requirements.

Freely combinable function modules

Pressure regulators, on/off and softstart valves with safety function, filters, pressure and flow sensors, dryers, sensors and lubricators can be assembled into a suitable solution for every task. With the modular structure the components can be combined as required. The simple connection system saves time because replacing individual modules does not require disassembling the entire combination. Many of the components are also UL and ATEX certified.

CAD models and configurator

Convenient tools for planning and selecting application-specific individual components and combinations. The product configurator lets you configure customised solutions quickly and transfer the order data without any hassle.

Engineering tools

Selection tool for choosing the right service unit without oversizing, and with the right air purity class:

→ www.festo.com/engineering/ service unit



Integrated sensors

Pressure and flow sensors


Safety functions Soft-start/quick exhaust valves MS6-SV/MS9-SV



Service unit combinations MSE6

Intelligent mix of sizes





- Reliable compressed air preparation and supply for systems
- Integrated or stand-alone
- Easy to connect with M8/M12 plug



- Fast and reliable exhausting of systems up to Performance Level e, certified to EN ISO 13849-1
- · Integrated soft-start function



- Fully automatic monitoring and regulation of the compressed air supply
- Automatic shut-off of the compressed air in stand-by mode
- Detection and notification of leakages
- Condition monitoring of relevant process data



- Optimum flow rate with a size that is up to 18% smaller
- Excellent energy efficiency
- Cost-optimised combinations save up to 30%!

Size differences						
Size		MS2	MS4	MS6	MS9	MS12
Grid dimension	[mm]	25	40	62	90	124
Connection sizes		M5, QS-6	G1/8, G1/4, G3/8	G1/4, G3/8, G1/2, G3/4	G1/2, G3/4, G1, G1 1/4, G1 1/2	G1, G1 1/4, G1 1/2, G2
Standard nominal flow rate qnN ¹⁾	[l/min]	350	1800	6500	20000	22000

¹⁾ Using pressure regulator MS-LR as an example

Note

Information

The next few pages provide a brief overview of the product range for the MS series service unit components.

You can find detailed information and all the technical data in the documentation for the relevant service unit component.

Accessories such as connecting plates or mounting brackets can be ordered either via the configurator or separately.

Design of a service unit

The sequence of the individual components within a service unit combination is relevant for safety and functionality. The service unit components cannot be combined in any order in the flow direction. There are restrictions and rules.

The configurator for the service unit MSB is a reliable and convenient way of arranging individual service unit components and it ensures compliance with the applicable rules. As a result, you get a fully assembled unit, including UL or ATEX certification, if necessary.

When combining a unit from individually configured and ordered service unit components, the points on the right must be adhered to under all circumstances.

- Regulators MS-LFR/LR/LRP/LRE are only permissible in the flow direction with the same or decreasing pressure regulation range
- Filters MS-LFR/LF/LFM/LFX are only permissible in the flow direction with an increasing grade of filtration
- Lubricators MS-LOE are not permitted in the flow direction upstream of a filter MS-LFR/LFM/LF/LFX, water separator MS-LWS or membrane air dryer MS-LDM1
- A micro filter MS-LFM must be installed in the flow direction upstream of an activated carbon filter MS-LFX or membrane air dryer MS-LDM1
- A flow sensor SFAM cannot be installed directly downstream of a regulator MS-LFR/LR; a branching module MS-FRM must be positioned between them
- A soft-start/quick exhaust valve MS-SV must be the last service unit component in the flow direction

Туре	Description	Size	Pneumatic o	connection				
			Push-in	Female th	read		Connecting plate with thr	ead
			connector	M	G	NPT	G	NPT
Combinations								
Service unit c	ombinations MSB-FRC							Datasheets → Internet: ms
	Combinations of filter regu-	4	1-	-	1/8, 1/4	-	-	-
	lator and lubricator	6	_	-	1/4, 3/8, 1/2	-	-	-
. In								
Service unit c	ombinations MSB							Datasheets → Internet: ms
91	7 combinations, predefined	4	-	_	1/4	-	-	-
		6	-	-	1/2	-	-	-
- Ballet	Freely configurable combin-	4	_	-	1/8, 1/4	_	1/8, 1/4, 3/8	1/8, 1/4, 3/8
	ations	6	_	_	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
图。	î l	9	_	-	3/4, 1	3/4, 1	1/2, 3/4, 1 1/4, 1 1/2	1/2, 3/4, 1 1/4, 1 1/2
II in	,							
Service unit c	ombinations MSE6				<u> </u>			Datasheets → Internet: mse
4 24-	Combinations with fieldbus	6	-	-	_	-	1/2	-
10.7	connection for measuring				-			
03	pressure, flow rate and con-							
100	sumption							


ype	Description	Size	Pneumatic o	Female thre	nad .		Connecting plate with thre	ad.
			connector	M	G	NPT	G Connecting plate with time	NPT
				IVI	9	MII	· ·	MI I
ndividual de								
ilter regulat		1	T :	T.,		1	Datasheets → Internet: ms2-lfr; m	ns4-lfr; ms6-lfr; ms9-lfr; ms12
- 0	Filter and pressure regula-	2	QS-6	M5		-	-	-
67.	tor in a single device, grade	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
100	of filtration 5 or 40 μm	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
- 11.		9	-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
Ψ.		12	-	-	_	-	1, 1 1/4, 1 1/2, 2	_
ilter regulat	ors MS-LFR-B						Datasheets	→ Internet: ms4-lfr-b; ms6-l
	Filter and pressure regula-	4	_	_	1/4	-	_	_
	tor in a single device in	6	1-	-	1/2	-	_	_
. 15	polymer housing, grade of				-1 -			
	filtration 5 or 40 µm							
*								
ilters MS-LF	:						Datasheets → Interne	t: ms4-lf; ms6-lf; ms9-lf; ms1
Sec.	Grade of filtration 5 or	4	_	_	1/8, 1/4	_	1/8, 1/4, 3/8	1/8, 1/4, 3/8
·	40 μm	6	1_	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	1-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
1		12	-	-	-	-	1, 1 1/4, 1 1/2, 2	_
						ı		
ine and mic	ro filters MS-LFM	1		1			Datasheets → Internet: ms4-l	
1	Grade of filtration 0.01 or	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
4	1 μm	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
1		9	-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
1		12	-	-	_	-	1, 1 1/4, 1 1/2, 2	_
Activated car	bon filters MS-LFX						Datasheets → Internet: ms	4-lfx; ms6-lfx; ms9-lfx; ms12
Sec.	For removing liquid and	4	_	_	1/8, 1/4	_	1/8, 1/4, 3/8	1/8, 1/4, 3/8
-	gaseous oil particles	6	_	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	1_	1-	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
1		12	-	-	-	-	1, 1 1/4, 1 1/2, 2	-
					I	1		
Vater separa	ators MS-LWS	1 .		1	T.,	1		et: ms6-lws; ms9-lws; ms12-
Photo:	Remove condensate from	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
100	compressed air, mainten-	9	-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
	ance-free	12					1, 1 1/4, 1 1/2, 2	

Туре	r service unit components of th Description	Size							
,,	2 33611941011		Push-in	Female thread			Connecting plate with threa	ıd	
			connector	M	G	NPT	G	NPT	
Individual devi	ces								
Pressure regula						[Datasheets → Internet: ms2-lr;	ms4-lr; ms6-lr; ms9-lr; ms12	
-	For setting the required	2	QS-6	M5	_	-	-	-	
1	operating pressure,	4	-	-	1/8, 1/4	_	1/8, 1/4, 3/8	1/8, 1/4, 3/8	
- 45	4 pressure regulation	6	-	-	1/4, 3/8, 1/2	_	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4	
9 1	ranges	9	-	_	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2	
40		12	-	-	-	-	1, 1 1/4, 1 1/2, 2	-	
Pressure regula		Ι.	1	1	1	1	Datasheets	i → Internet: ms4-lr-b; ms6-l	
	For setting the required	4	-	-	1/4	-	-	-	
-	operating pressure, in polymer housing	6	_	-	1/2	-	-	<u> -</u>	
010	polymer mousing								
1957									
Pressure regula	ators MS-LRB						Datashee	ts → Internet: ms4-lrb; ms6-	
	For configuring a regulator	4	-	_	1/4	-	1/8, 1/4, 3/8	-	
9.4	manifold with independent	6	-	-	1/2	-	1/4, 3/8, 1/2, 3/4	-	
10000	pressure regulation ranges.					1			
10015	Pressure output is to the								
-	front or rear.								
Precision press	sure regulators MS-LRP							Datasheets → Internet: ms6-	
	For precise setting of the re-	6	-	_	1/4, 3/8, 1/2	_	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4	
	quired operating pressure,			'				*	
-	4 pressure regulation								
WHA.	ranges,								
	pressure hysteresis								
	0.02 bar								
Precision press	sure regulators MS-LRPB								
							Da	atasheets → Internet: ms6-lr	
100	For configuring a regulator	6	-	-	1/2	_	1/4, 3/8, 1/2, 3/4	atasheets → Internet: ms6-l	
(3)		6	_	-	1/2	-	1	atasheets → Internet: ms6-l –	
	For configuring a regulator manifold with independent pressure regulation ranges.	6	-	-	1/2	-	1	atasheets → Internet: ms6-l -	
1	For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is to the	6	_	-	1/2	-	1	atasheets → Internet: ms6-l	
	For configuring a regulator manifold with independent pressure regulation ranges.	6	-	-	1/2	-	1	atasheets → Internet: ms6-li -	
Electric pressur	For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is to the	6	-	_	1/2	-	1/4, 3/8, 1/2, 3/4	-	
Electric pressur	For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is to the front or rear.		-	-		-	1/4, 3/8, 1/2, 3/4		
Electric pressur	For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is to the front or rear. re regulators MS-LRE Electrically adjustable pres-				1/2		1/4, 3/8, 1/2, 3/4	-	
Electric pressur	For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is to the front or rear.						1/4, 3/8, 1/2, 3/4	 Datasheets → Internet: ms6	
Electric pressur	For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is to the front or rear. re regulators MS-LRE Electrically adjustable pressure regulator,						1/4, 3/8, 1/2, 3/4		
electric pressur	For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is to the front or rear. The regulators MS-LRE Electrically adjustable pressure regulator, 4 pressure regulation						1/4, 3/8, 1/2, 3/4		
	For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is to the front or rear. The regulators MS-LRE Electrically adjustable pressure regulator, 4 pressure regulation ranges					-	1/4, 3/8, 1/2, 3/4	Datasheets → Internet: ms6	
	For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is to the front or rear. The regulators MS-LRE Electrically adjustable pressure regulator, 4 pressure regulation ranges S-LOE Add a precisely adjustable					-	1/4, 3/8, 1/2, 3/4	Datasheets → Internet: ms6	
	For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is to the front or rear. The regulators MS-LRE Electrically adjustable pressure regulator, 4 pressure regulation ranges S-LOE Add a precisely adjustable amount of oil to the com-	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4 1/4, 3/8, 1/2, 3/4 Datasheets → Internet: ms4-lo	Datasheets → Internet: ms6- 1/4, 3/8, 1/2, 3/4	
	For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is to the front or rear. The regulators MS-LRE Electrically adjustable pressure regulator, 4 pressure regulation ranges S-LOE Add a precisely adjustable amount of oil to the compressed air. The amount of	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4 1/4, 3/8, 1/2, 3/4 1/4, 3/8, 1/2, 3/4 Datasheets → Internet: ms4-le 1/8, 1/4, 3/8	Datasheets → Internet: ms6 1/4, 3/8, 1/2, 3/4 De; ms6-loe; ms9-loe; ms12- 1/8, 1/4, 3/8	
Electric pressur	For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is to the front or rear. The regulators MS-LRE Electrically adjustable pressure regulator, 4 pressure regulation ranges S-LOE Add a precisely adjustable amount of oil to the com-	6			1/4, 3/8, 1/2 1/8, 1/4 1/4, 3/8, 1/2	- - - -	1/4, 3/8, 1/2, 3/4 1/4, 3/8, 1/2, 3/4 1/4, 3/8, 1/2, 3/4 Datasheets → Internet: ms4-lo 1/8, 1/4, 3/8 1/4, 3/8, 1/2, 3/4	Datasheets → Internet: ms6 1/4, 3/8, 1/2, 3/4 Dee; ms6-loe; ms9-loe; ms12- 1/8, 1/4, 3/8 1/4, 3/8, 1/2, 3/4	

	Description	Size	Pneumatic o	Female thre	nad.		Connecting plate with thre	ad.
			connector	M	G	NPT	G G	NPT
ividual device	nc .				-			
off valves MS							Datasheets → Internet: ms4-e	om, mc6 om, mc0 om, mc1
on valves ivis	Manually actuated on/off	4	T_	1_	1/8, 1/4	Τ_	1/8, 1/4, 3/8	1/8, 1/4, 3/8
	valve for pressurising and	6	1_	-	1/4, 3/8, 1/2	 -	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	exhausting pneumatic sys-	9	-	1_	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/
9	tems.	12	-	1_	5/4, 1	3/4, 1	1, 1 1/4, 1 1/2, 2	1/2, 3/4, 1, 1 1/4, 1 1/
		12	<u> </u>	-	-	<u> </u>	1, 1 1/4, 1 1/2, 2	
£							D. I. I. I.	
off valves MS		1,	1	1	1/0 1/4		Datasheets → Internet: ms	
Contract of the Contract of th	Electrically actuated on/off valve for pressurising and	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
	exhausting pneumatic sys-	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
(0)	tems.	9	-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/
	tems.	12	-	-	-	-	1, 1 1/4, 1 1/2, 2	_
off valves MS		,			1//	1	Datasheets -	→ Internet: ms4-ee-b; ms6
4	Electrically actuated on/off	4	-	-	1/4	-	-	-
1	valve in polymer housing for pressurising and ex-	6	-	-	1/2	_	-	_
J	hausting pneumatic systems.							
-start valves	MS-DI						Natasheets → In	ternet: ms4-dl; ms6-dl; ms
	Pneumatically actuated	4	Τ_	T_	1/8, 1/4	T_	1/8, 1/4, 3/8	1/8, 1/4, 3/8
460.	soft-start valve for slow	6	1_	-	1/4, 3/8, 1/2	+-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	pressurisation and exhaust	12		1_	-	+-	1, 1 1/4, 1 1/2, 2	1/4, 5/0, 1/2, 5/4
	of pneumatic installations.	12				1-	1, 1 1/4, 1 1/2, 2	
start valvas	MC DE						Datashasta a Into	
-start valves		Ι,	1	1	1/0 1//	1		ernet: ms4-de; ms6-de; ms
	Electrically actuated soft- start valve for slowly pres-	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
60	surising and exhausting	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	pneumatic installations.	12	-	-		-	1, 1 1/4, 1 1/2, 2	
1								
off valves MS		·					Datasheets →	Internet: ms4-ede-b; ms6-
Con.	Electrically actuated soft-	4	-	-	1/4	-	-	-
786	start valve in polymer hous-	6	-	-	1/2	-	_	_
J	ing for slowly pressurising and exhausting pneumatic installations.							
-start/quick	exhaust valves MS-SV						Datashe	eets → Internet: ms6-sv; m
	For gradually increasing	6	Ī-	-	1/2	_	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	pressurisation and quick,	9	1_	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/
2]	safe pressure reduction in	<u> </u>	1	1	\[\sigma_1 \tau_2 \tau_2 \tau_3 \tau_4 \]	1 -1 +, +	-1-, -17, -, - 1/7, - 1/2	-1-, -17, 1, 1 1/7, 1 1/
	pneumatic piping systems. Up to category 1, PL c.							
2	Up to category 3, PL d.	6		-	1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	Up to category 4, PL e in the case of optional extension.							
-	Up to category 4, PL e.	6	_	-	1/2	-	1/4, 3/8, 1/2, 3/4	_
H					·			

Type Description		Size Pneumatic connection						
			Push-in	Female th	read		Connecting plate with thre	ad
			connector	M	G	NPT	G	NPT
ndividual de	vices							
Membrane ai	r dryers MS-LDM1						Datasheets	→ Internet: ms4-ldm; ms6-ld
•)	Wear-free membrane dryer	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
_ 1	with internal air consump- tion	6	-	-	1/4, 3/8, 1/2		1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
3ranching mo	odules MS-FRM						Datasheets → Internet: ms4-fr	m; ms6-frm; ms9-frm; ms12-f
100	Compressed air distributors	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	-
-	with 4 connections	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	-
-		9	-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	_	-	-	-	1, 1 1/4, 1 1/2, 2	-
Distributor bl	ocks MS-FRM-FRZ	,					Datasheets → Ir	nternet: ms4-frm-frz; ms6-frm-
100	Compressed air distributors	4	-	-	-	-	-	-
@1	with 4 connections and half	6	-	1-	-	-	-	-
2	the grid width							
Flow sensors	SFAM							Datasheets → Internet: sfa
(major)	For absolute flow rate infor-	6	-	-	-	-	1/2	1/2
A 12 15	mation and cumulative air	9	-	1-	-	-	1, 1 1/2	1, 1 1/2
	consumption measurement							

Peripherals overview



- Note

Additional accessories:

- Module connector for combination with size MS4/MS6 or size MS9
 - → Internet: amv, rmv, armv
- Adapter for mounting on profiles
 - → Internet: ipm-80, ipm-40-80, ipm-80-80

Peripherals overview

Moun	ting attachments and accessories	Order code	Description of
			→ Page/Internet
[1]	On/off valve	MS4/6-EM1	12
Can b	e ordered via the modular product system		
[3]	Mounting bracket	[WP]	18
	Mounting bracket (not shown)	[WPM]	
[4]	Mounting bracket	[WB]	
[5]	Mounting bracket	[WBM]	
[8]	Connecting plate SET ¹⁾	[AG]	
	Connecting plate SET ¹⁾	[AQ]	
[11]	Pressure sensor SDE1 with LCD display	[AD1], [AD2], [AD3], [AD4]	
[12]	Pressure sensor SDE5 with status indicator	[AD7], [AD8], [AD9], [AD10]	
[14]	Adapter for EN pressure gauge 1/8, 1/4	[A8], [A4]	
[18]	MS pressure gauge	[AG], [RG]	
[19]	Silencer	[S]	
Can b	e ordered as accessories		
[2]	Module connector	MS4/6-MV	ms4-mv, ms6-mv
[3]	Mounting bracket	MS4/6-WP	ms4-wp, ms6-wp
	Mounting bracket (not shown)	MS4/6-WPB/WPE/WPM	ms4-wp, ms6-wp
[4]	Mounting bracket	MS4/6-WB	ms4-wb, ms6-wb
[5]	Mounting bracket	MS4-WBM	ms4-wbm
[6]	Cover cap	MS4/6-END	ms4-end, ms6-end
[7]	Mounting plate ²⁾	MS4/6-AEND	ms4-aend, ms6-aend
[8]	Connecting plate SET ²⁾	MS4/6-AG	ms4-ag, ms6-ag
[9]	Padlock	LRVS-D	103
[10]	Connecting cable	NEBU-M8LE3, NEBU-M12LE4	103
[13]	Connecting cable	NEBU-M8LE3	103
[15]	Pressure gauge	MA	103
[16]	Pressure sensor	SPAUT	102
[17]	Connecting cable	NEBU-M8LE4, NEBU-M12LE4	103
[19]	Silencer	U	103

Module connector [2] is included in the scope of delivery.
 Module connector MS4/6-MV [2] or mounting bracket MS4/6-WP, WPB, WPE, WPM [3] is required for mounting.

Type codes – MS4-EM1

, ,					
001	Series				
MS	MS series				
002	Size				
4	Grid dimension 40 mm				
003	Function				
EM1	On/off valve, manual	1			
LIVII	on/on vaive, manual				
004	Pneumatic connection				
1/8	Female thread G1/8				
1/4	Female thread G1/4				
AGA	Sub-base G1/8				
AGB	Sub-base G1/4				
AGC	Sub-base G3/8				
AQK	Sub-base 1/8 NPT				
AQN	Sub-base 1/4 NPT				
AQP	Sub-base 3/8 NPT				
005	Silencer				
	None				
S	Silencer				
006	Pressure gauge alternatives				
	None				
AG	MS pressure gauge				
A8	Adapter for EN pressure gauge 1/8, without pressure gauge				
A4	Adapter for EN pressure gauge 1/4, without pressure gauge				
RG	Integrated pressure gauge, red/green scale				
AD1	Pressure sensor with LCD display, M8 plug, PNP, 3-pin				
AD2	Pressure sensor with LCD display, M8 plug, NPN, 3-pin				
AD3	Pressure sensor with LCD display, M12 plug, PNP, 4-pin, ana-				

logue output 4 ... 20 mA

logue output 4 ... 20 mA

ue comparator, PNP, N/O

ue comparator, PNP, N/C

window comparator, PNP, N/C

parator, PNP, N/O

Pressure sensor with LCD display, M12 plug, NPN, 4-pin, ana-

Pressure sensor with switching display, M8 plug, threshold val-

Pressure sensor with switching display, M8 plug, threshold val-

Pressure sensor with switching display, M8 plug, window com-

Pressure sensor with operational status indicator, M8 plug,

007	Alternative pressure gauge scale	
	MS pressure gauge	
PSI	psi	
MPA	MPa	
Lana	l=	
008	Type of mounting	
	Without mounting bracket	
WP	Mounting bracket basic design	
WPM	Mounting bracket for hooking in service unit components	
WB	Mounting centrally at rear (wall mounting top and bottom), con-	
	necting plates not required	
WBM	Mounting centrally at rear (wall mounting top), connecting	
	plates not required	
009	EU certification	
009		
	None	
EX4	II 2GD	
010	UL certification	
010		
	None	
UL1	cULus ordinary location for Canada and USA	
011	Flow direction	
-	Flow direction from left to right	
Z	Flow direction from right to left	

AD4

AD7

AD8

AD9

AD10

Type codes – MS6-EM1

001	Series	
MS6	MS-series, size 6	
002	Size	
6	Grid dimension 62 mm	
003	Function	
EM1	On/off valve, manual	
004	Pneumatic connection	
1/4	Female thread G1/4	
3/8	Female thread G3/8	
1/2	Female thread G1/2	
AGB	Sub-base G1/4	
AGC	Sub-base G3/8	
AGD	Sub-base G1/2	
AGE	Sub-base G3/4	
AQN	Sub-base 1/4 NPT	
AQP	Sub-base 3/8 NPT	
AQR	Sub-base 1/2 NPT	
AQS	Sub-base 3/4 NPT	
005	Silencer	
	None	
S	Silencer	

006	Pressure gauge alternatives				
	None				
AG	MS pressure gauge				
A4	Adapter for EN pressure gauge 1/4, without pressure gauge				
RG	Integrated pressure gauge, red/green scale				
AD1	Pressure sensor with LCD display, M8 plug, PNP, 3-pin				
AD2	Pressure sensor with LCD display, M8 plug, NPN, 3-pin				
AD3	Pressure sensor with LCD display, M12 plug, PNP, 4-pin, analogue output 4 20 mA				
AD4	Pressure sensor with LCD display, M12 plug, NPN, 4-pin, analogue output 4 20 mA				
AD7	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/O				
AD8	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C				
AD9	Pressure sensor with switching display, M8 plug, window comparator, PNP, N/O				
AD10	Pressure sensor with operational status indicator, M8 plug,				
	window comparator, PNP, N/C				
007	window comparator, PNP, N/C Alternative pressure gauge scale				
007					
	Alternative pressure gauge scale				
007 PSI MPA	Alternative pressure gauge scale MS pressure gauge				
PSI	Alternative pressure gauge scale MS pressure gauge psi				
PSI MPA	Alternative pressure gauge scale MS pressure gauge psi MPa				
PSI MPA	Alternative pressure gauge scale MS pressure gauge psi MPa Type of mounting				
MPA 008	Alternative pressure gauge scale MS pressure gauge psi MPa Type of mounting Without mounting bracket				
PSI MPA 008	Alternative pressure gauge scale MS pressure gauge psi MPa Type of mounting Without mounting bracket Mounting bracket basic design				
PSI MPA 008 WP WPM WB	Alternative pressure gauge scale MS pressure gauge psi MPa Type of mounting Without mounting bracket Mounting bracket basic design Mounting bracket for hooking in service unit components Mounting centrally at rear (wall mounting top and bottom), con-				
PSI MPA 008 WP WPM WB	Alternative pressure gauge scale MS pressure gauge psi MPa Type of mounting Without mounting bracket Mounting bracket basic design Mounting bracket for hooking in service unit components Mounting centrally at rear (wall mounting top and bottom), connecting plates not required				
PSI MPA 008 WP WPM WB	Alternative pressure gauge scale MS pressure gauge psi MPa Type of mounting Without mounting bracket Mounting bracket basic design Mounting bracket for hooking in service unit components Mounting centrally at rear (wall mounting top and bottom), connecting plates not required EU certification				
PSI MPA 008 WP WPM WB	Alternative pressure gauge scale MS pressure gauge psi MPa Type of mounting Without mounting bracket Mounting bracket basic design Mounting bracket for hooking in service unit components Mounting centrally at rear (wall mounting top and bottom), connecting plates not required EU certification None				
PSI MPA 008 WP WPM WB 009	Alternative pressure gauge scale MS pressure gauge psi MPa Type of mounting Without mounting bracket Mounting bracket basic design Mounting bracket for hooking in service unit components Mounting centrally at rear (wall mounting top and bottom), connecting plates not required EU certification None II 2GD				

011

Flow direction

Flow direction from left to right Flow direction from right to left

On/off valves MS4/MS6-EM1, MS series

Datasheet

Function



- N - Flow rate 1200 ... 8700 l/min
- N - Temperature range
-10 ... +60°C
- → Operating pressure

0 ... 18 bar




 Manually actuated on/off valve for pressurising and exhausting pneumatic systems

• The valve is switched by turning the rotary knob

A silencer can be connected to port
 3 or the exhaust air can be ducted
 here

• When the valve is closed, the rotary knob can be secured with a padlock



• Optional pressure sensor

• Optional device variant EX4 for use in potentially explosive areas in zones 1, 2, 21 and 22



General technical data

General technical data							
Size		MS4	N	156			
Pneumatic connection 1	., 2						
Female thread		G1/8 or G1/4	G	1/4, G3/8 or G1/2			
Connecting plate	[AG]	G1/8, G1/4 or G3/8	G	1/4, G3/8, G1/2 or G3/4			
	[AQ]	1/8 NPT, 1/4 NPT or 3/8 NPT	1	1/4 NPT, 3/8 NPT, 1/2 NPT or 3/4 NPT			
Pneumatic connection 3	3	G1/4	G	1/2			
Design		Rotary switching valve					
Type of mounting		With accessories					
		In-line installation					
Mounting position		Any ¹⁾					
Display pressure		Via pressure sensor for indicating the output pressure and electrical output via LCD display					
		Via pressure sensor for indicating the output pressure and electrical output via status indicator					
		Via pressure gauge for displaying the output pressure					
		Via pressure gauge with red/green scale for indicat	Via pressure gauge with red/green scale for indicating the output pressure				
		Prepared for G1/8	_				
		Prepared for G1/4	Prepared for G1/4				
Valve function		3/2-way valve, bistable	3/2-way valve, bistable				
Exhaust air function		Cannot be throttled	Cannot be throttled				
Switching position indic	ation	Knob actuator direction = flow direction					
Type of control		Direct					
Flow direction		Not reversible					

¹⁾ The on/off valve must be mounted vertically when combined with a pressure sensor as condensate must not collect in the pressure sensor.

 $[\]mbox{\ensuremath{|\hspace{-1.6pt}|}}$ Note: This product conforms to ISO 1179-1 and ISO 228-1.

Characteristic flow rate values					
Size	MS4		MS6		
Pneumatic connection 1, 2	G1/8	G1/8 G1/4 G		G3/8	G1/2
Standard nominal flow rate qnN1) [l/m	in]				
In main flow direction 1 → 2	1200	2200	3000	5500	8700
In relief direction 2 → 3	1900	1700	6800	6600	6200
C value [l/s*min]					
In main flow direction 1 → 2	4.6	9.0	10.7	21.2	30.8
b value					
In main flow direction 1 → 2	0.51	0.39	0.56	0.49	0.57

¹⁾ Measured at p1 = 6 bar and p2 = 5 bar, Δ p = 1 bar.

Operating and environmental conditions					
Size		MS4		MS6	
On/off valve		Without pressure sensor	With pressure sensor	Without pressure sensor	With pressure sensor
Operating pressure	[bar]	0 14 (0 10)1)	0 10	0 18 (0 10) ¹⁾	0 10
Operating medium	Operating medium Compressed air to ISO 8573-1:2010 [7:4:4]				
Inert gases					
Note on the operating/pilot m	ote on the operating/pilot medium Lubricated operation possible (in which case lubricated operation will always be required)				
Ambient temperature	[°C]	-10 +60	0 +50	-10 +60	0 +50
Temperature of medium	[°C]	-10 +60	0 +50	-10 +60	0 +50
Corrosion resistance class CRC ²⁾ 2					
Food-safe ³⁾		See supplementary material information			
UL certification ³⁾		c UL us - Recognized (OL)			

- 1) Value in brackets applies to MS4/MS6-EM1 with UL certification.
- 2) Corrosion resistance class CRC 2 to Festo standard FN 940070
 - Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.
- 3) Additional information: www.festo.com/catalogue/ms → Support/Downloads.


ATEX	
EU certification	[EX4]
ATEX category for gas	II 2G
Type of ignition protection for gas	Ex h IIC T6 Gb X
ATEX category for dust	2D
Type of ignition protection for dust	Ex h IIIC T60°C Db X
Explosion-proof ambient temperature	-10°C ≤ Ta ≤ +60°C
CE marking (see declaration of conformity) ¹⁾	To EU Explosion Protection Directive (ATEX)

1) Additional information: www.festo.com/catalogue/ms → Support/Downloads.


Weight [g]		
Size	MS4	MS6
On/off valve	190	580
On/off valve with silencer	210	655

Materials

Sectional view



On/o	ffvalve	
[1]	Housing	Die-cast aluminium
[2]	Rotary piston	Reinforced PA
[3]	Spool	Reinforced PA
-	Seals	NBR, TPE-U(PU)
Note	on materials	RoHS-compliant
		Free of copper and PTFE (not with MS pressure gauge with standard scale or pressure sensor)




Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions – Pressure gauge/pressure gauge alternatives


[AG] Integrated MS pressure gauge with standard scale

[RG] Integrated MS pressure gauge with red/green scale



Download CAD data → www.festo.com


[A8] Adapter for EN pressure gauge 1/8, without pressure gauge



Туре	B2	B3	D1	D4
MS4				
MS4-EM1-1/8AG	21	57	G1/8	
MS4-EM1-1/4AG	21	5/	G1/4	_
MS4-EM1-1/8RG	21	58.5	G1/8	
MS4-EM1-1/4RG	21	30.3	G1/4	_
MS4-EM1-1/8A8	21	58.5	G1/8	G1/8
MS4-EM1-1/4A8	21	30.3	G1/4	01/0
MS4-EM1-1/8A4	21	58.5	G1/8	G1/4
MS4-EM1-1/4A4	21	30.5	G1/4	01/4
MS6				
MS6-EM1-1/4AG			G1/4	
MS6-EM1-3/8AG	31	77	G3/8	_
MS6-EM1-1/2AG			G1/2	
MS6-EM1-1/4RG			G1/4	
MS6-EM1-3/8RG	31	78.5	G3/8	_
MS6-EM1-1/2RG			G1/2	
MS6-EM1-1/4A4			G1/4	
MS6-EM1-3/8A4	31	78.5	G3/8	G1/4
MS6-EM1-1/2A4			G1/2	

Dimensions – Pressure sensor

[AD1], [AD2], [AD3], [AD4] Pressure sensor with LCD display



[AD1]:

SDE1-D10-G2-MS...-L-P1-M8 with 3-pin plug M8x1, 1 switching output PNP

[AD2]:

SDE1-D10-G2-MS...-L-N1-M8 with 3-pin plug M8x1, 1 switching output NPN

Download CAD data → www.festo.com

Datasheets → Internet: sde1


[AD3]:


SDE1-D10-G2-MS...-L-PI-M12 with 4-pin plug M12x1, 1 switching output PNP and 4 ... 20 mA analogue

[AD4]:

SDE1-D10-G2-MS...-L-NI-M12 with 4-pin plug M12x1, 1 switching output NPN and 4 ... 20 mA analogue

[AD7], [AD8], [AD9], [AD10] Pressure sensor with status indicator





Flow direction

[AD7]:

SDE5-D10-O-...-P-M8 with 3-pin plug M8x1, threshold value comparator, 1 switching output PNP, N/O contact

[AD8]:

SDE5-D10-C-...-P-M8 with 3-pin plug M8x1, threshold value comparator, 1 switching output PNP, N/C contact

Datasheets → Internet: sde5

[AD9]:

SDE5-D10-O3-...-P-M8 with 3-pin plug M8x1, window comparator, 1 switching output PNP, N/O contact


[AD10]:

SDE5-D10-C3-...-P-M8 with 3-pin plug M8x1, window comparator, 1 switching output PNP, N/C contact

Туре	B2	В3	B5	В6	D6	L5	L6
MS4							
MS4AD1, AD2	21	82.6	32	22.2	M8x1	25.1	46.7
MS4AD3, AD4	21	82.0	32	32.3	M12x1	35.1	55.8
MS4AD7, AD8, AD9, AD10	21	59.1	~32	16	M8x1	_	_
MS6							
MS6AD1, AD2	21	102	F.1	22.2	M8x1	25.1	46.7
MS6AD3, AD4	31	103	51	32.3	M12x1	35.1	55.8
MS6AD7, AD8, AD9, AD10	31	79.1	~51	16	M8x1	-	-

Dimensions - Silencer





Туре	D2	L4
MS4-EM1S	20	49
MS6-EM1S	28	109

★ Core Range

Ord	ering	data
U. u	٠	uutu

oracing auta					
Size	Connection	Flow direction	Part no.	Туре	
MS4	G1/4	From left to right	★ 541258	MS4-EM1-1/4	
MS6	G1/2	From left to right	★ 541267	MS6-EM1-1/2	
With silencer					
MS4	G1/4	From left to right	★ 541259	MS4-EM1-1/4-S	
MS6	G1/2	From left to right	★ 541268	MS6-EM1-1/2-S	

Ord	ering	data
Oiu	CHILIS	uutu

Size	Connection	Flow direction	Part no.	Туре
MS4	G1/8	From left to right	541262	MS4-EM1-1/8
	G1/4	From right to left	541261	MS4-EM1-1/4-Z
MS6	G1/4	From left to right	541271	MS6-EM1-1/4
	G3/8	From left to right	541275	MS6-EM1-3/8
	G1/2	From right to left	541270	MS6-EM1-1/2-Z
With silencer				
MS4	G1/8	From left to right	541263	MS4-EM1-1/8-S
	G1/4	From right to left	541260	MS4-EM1-1/4-S-Z
MS6	G1/4	From left to right	541272	MS6-EM1-1/4-S
	G3/8	From left to right	541276	MS6-EM1-3/8-S
	G1/2	From right to left	541269	MS6-EM1-1/2-S-Z

Ordering data – Modular product system

Ordering table Grid dimension [m	m] 40	62	Conditions	Code	Enter
					code
Module no.	541266	541279			
Series	Standard			MS	MS
Size	4	6			
Function	On/off valve, manual			-EM1	-EM1
Pneumatic connection	Female thread G1/8	-	[1]	-1/8	
	Female thread G1/4	Female thread G1/4	[1]	-1/4	
	-	Female thread G3/8	[1]	-3/8	
	-	Female thread G1/2	[1]	-1/2	
	Connecting plate G1/8	-		-AGA	
	Connecting plate G1/4	Connecting plate G1/4		-AGB	
	Connecting plate G3/8	Connecting plate G3/8		-AGC	
	-	Connecting plate G1/2		-AGD	
	-	Connecting plate G3/4		-AGE	
	Connecting plate 1/8 NPT	-	[1]	-AQK	
	Connecting plate 1/4 NPT	Connecting plate 1/4 NPT	[1]	-AQN	
	Connecting plate 3/8 NPT	Connecting plate 3/8 NPT	[1]	-AQP	
	-	Connecting plate 1/2 NPT	[1]	-AQR	
	-	Connecting plate 3/4 NPT	[1]	-AQS	
Rotary knob colour	Standard (black/blue)				
	Red			-R	
Silencer	None				
	Silencer			-S	
Pressure gauge/pressure gauge	None				
alternatives	MS pressure gauge, bar			-AG	
	Adapter for EN pressure gauge 1/8, without pressure gauge	-		-A8	
	Adapter for EN pressure gauge 1/4, without pr	essure gauge		-A4	
	Integrated pressure gauge, red/green scale			-RG	
	Pressure sensor with LCD display, M8 plug, 1 s	switching output PNP, 3-pin	[1] [2]	-AD1	
	Pressure sensor with LCD display, M8 plug, 1 s	switching output NPN, 3-pin	[1] [2]	-AD2	
	Pressure sensor with LCD display, plug M12, 1 4 20 mA	switching output PNP, 4-pin, analogue output	[1] [2]	-AD3	
	Pressure sensor with LCD display, plug M12, 1 4 20 mA	switching output NPN, 4-pin, analogue output	[1] [2]	-AD4	
	Pressure sensor with status indicator, plug M8	B, threshold value comparator, PNP, N/O contact	[1] [2]	-AD7	
	Pressure sensor with status indicator, plug M8	B, threshold value comparator, PNP, N/C contact	[1] [2]	-AD8	
	Pressure sensor with status indicator, plug M8	B, window comparator, PNP, N/O contact	[1] [2]	-AD9	
	Pressure sensor with status indicator, plug M8	B, window comparator, PNP, N/C contact	[1] [2]	-AD10	
Alternative pressure gauge scale	None				
	psi		[3]	-PSI	
	MPa		[4]	-MPA	

[1] 1/8; 1/4; 3/8; Not with EU EX4 certification. 1/2, AQK, AQN, AQP, AQR, AQS,

AD1 ... AD4, AD7 ... AD10, WPM

AD1 ... AD4,

Measuring range max. 10 bar.

AD7 ... AD10 PSI

Only in combination with pressure gauge AG.

Only in combination with pressure gauge AG or RG.

Ordering data – Modular product system

Ordering table Grid dimension [mm]	40	62	Conditions	Code	Enter code
Type of mounting	Without mounting bracket				
	Mounting bracket standard design		[5]	-WP	
	Mounting bracket for attaching service unit com	ponents	[1] [5]	-WPM	
	Mounting bracket centrally at rear (wall mounting top and bottom), connecting plates not required			-WB	
	Mounting bracket centrally at rear (wall mounting top), connecting plates not required	-		-WBM	
EU certification	None				
	II 2GD to EU Explosion Protection Directive (ATE)	()		-EX4	
UL certification	None				
	cULus, ordinary location for Canada and USA			-UL1	
Flow direction	Flow direction from left to right				
	Flow direction from right to left			-Z	


[1] 1/8; 1/4; 3/8; Not with EU EX4 certification. 1/2, AQK, AQN, AQP, AQR, AQS, AD1 ... AD4, AD7 ... AD10,

WPM

[5] WP, WPM

Only with connecting plate AGA, AGB, AGC, AGD, AGE, AQK, AQN, AQP, AQR or AQS.

Peripherals overview



- Note


Additional accessories:

- Module connector for combination with size MS4/MS6 or size MS9
 - → Internet: amv, rmv, armv
- Adapter for mounting on profiles
 - → Internet: ipm-80, ipm-40-80, ipm-80-80

Peripherals overview

Supply voltage [V24], [V24P], [10V24], [10V24C], [V110], [V230]

Supply voltage [10V24D], [10V24F], [10V24P]





Moun	ting attachments and accessories		
		Order code	→ Page/Internet
[1]	On/off valve	MS4/6-EE	24
Can b	e ordered via the modular product system		
[3]	Mounting bracket	[WP]	32
	Mounting bracket (not shown)	[WPM]	
[4]	Mounting bracket	[WB]	
[5]	Mounting bracket	[WBM]	
[8]	Connecting plate SET ¹⁾	[AG]	
	Connecting plate SET ¹⁾	[AQ]	
[10]	Pressure sensor SDE1 with LCD display	[AD1], [AD2], [AD3], [AD4]	
[11]	Pressure sensor SPAU with LCD display	[AD11], [AD12]	
[13]	Pressure sensor SDE5 with status indicator	[AD7], [AD8], [AD9], [AD10]	
[15]	Adapter for EN pressure gauge 1/8, 1/4	[A8], [A4]	
[18]	MS pressure gauge	[AG], [RG]	
[19]	Silencer	[S]	
Can b	e ordered as accessories		
[2]	Module connector	MS4/6-MV	ms4-mv, ms6-mv
[3]	Mounting bracket	MS4/6-WP	ms4-wp, ms6-wp
	Mounting bracket (not shown)	MS4/6-WPB/WPE/WPM	ms4-wp, ms6-wp
[4]	Mounting bracket	MS4/6-WB	ms4-wb, ms6-wb
[5]	Mounting bracket	MS4-WBM	ms4-wbm
[6]	Cover cap	MS4/6-END	ms4-end, ms6-end
[7]	Mounting plate ²⁾	MS4/6-AEND	ms4-aend, ms6-aend
[8]	Connecting plate SET ²⁾	MS4/6-AG	ms4-ag, ms6-ag
[9]	Connecting cable	NEBU-M8LE3, NEBU-M12LE4	103
[12]	Connecting cable	NEBU-M8LE4, NEBU-M12LE4	103
[14]	Connecting cable	NEBU-M8LE3	103
[16]	Pressure gauge	MA	103
[17]	Pressure sensor	SPAUT	102
[19]	Silencer	U	103
[20]	Illuminating seal	MEB-LD	102
[21]	Plug socket with cable	KMEB	102
[22]	Plug socket ³⁾	MSSD-EB	102
[23]	Locking clip	CPV18-HV	102
[24]	Connecting cable	NEBU-M12G5	103
[25]	Connecting cable	NEBU-M12W5	103

¹⁾ Module connector [2] is included in the scope of delivery.

²⁾ Module connector MS4/6-MV [2] or mounting bracket MS4/6-WP, WPB, WPE, WPM [3] is required for mounting.

3) For on/off valve MS...-V24P and MS...-V24-...-EX2, the plug socket is included in the scope of delivery.

Type codes

001	Series
MS	MS series
002	Size
4	Grid dimension 40 mm
003	Function
EE	On/off valve, electric
004	Pneumatic connection
1/8	Female thread G1/8
1/4	Female thread G1/4
AGA	Sub-base G1/8
\GB	Sub-base G1/4
\GC	Sub-base G3/8
NQK	Sub-base 1/8 NPT
QN .	Sub-base 1/4 NPT
AQP	Sub-base 3/8 NPT
005	Supply voltage
/230	230 V AC (connection pattern to EN 175301)
L0V24	24 V DC, 10 bar, connection pattern to EN 175301
/110	110 V AC (connection pattern to EN 175301)
10V24C	24 V DC, 10 bar (connection pattern to EN 175301) without manual override
10V24D	24 V DC, 10 bar, M12 (connection pattern to EN 60947-5-2)
	without manual override
10V24F	24 V DC, 10 bar, M12 (connection pattern to EN 60947-5-2).
	Manual override on the pilot actuator non-detenting, internally
	detenting
10V24P	24 V DC, 10 bar, M12 plug socket adapter (connection pattern
	to EN 60947-5-2)
/24	24 V DC (connection pattern to EN 175301)
/24P	24 V DC plug (connection pattern M12 to DESINA)
006	Silencer
	None
S	Silencer

007	Pressure gauge alternatives
	None
AG	MS pressure gauge
A8	Adapter for EN pressure gauge 1/8, without pressure gauge
A4	Adapter for EN pressure gauge 1/4, without pressure gauge Adapter for EN pressure gauge 1/4, without pressure gauge
RG	Integrated pressure gauge, red/green scale
AD1	
	Pressure sensor with LCD display, M8 plug, PNP, 3-pin
AD2	Pressure sensor with LCD display, M8 plug, NPN, 3-pin
AD3	Pressure sensor with LCD display, M12 plug, PNP, 4-pin, analogue output 4 20 mA
AD4	logue output 4 20 mA Pressure sensor with LCD display, M12 plug, NPN, 4-pin, ana-
AU4	logue output 4 20 mA
AD7	Pressure sensor with switching display, M8 plug, threshold val-
	ue comparator, PNP, N/O
AD8	Pressure sensor with switching display, M8 plug, threshold val-
	ue comparator, PNP, N/C
AD9	Pressure sensor with switching display, M8 plug, window com-
	parator, PNP, N/O
AD10	Pressure sensor with operational status indicator, M8 plug,
	window comparator, PNP, N/C
AD11	Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®,
	PNP, NPN, 010 V, 15 V, 420 mA
AD12	Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®,
	PNP, NPN, 010 V, 15 V, 420 mA
008	Alternative pressure gauge scale
000	
	MS pressure gauge
PSI	psi
MPA	MPa
009	Type of mounting
009	
	Without mounting bracket
WP	Mounting bracket basic design
WPM	Mounting bracket for hooking in service unit components
WB	Mounting centrally at rear (wall mounting top and bottom), con-
	necting plates not required
WBM	Mounting centrally at rear (wall mounting top), connecting
	plates not required
010	EU certification
010	
FVA	None
EX2	II 3GD
011	UL certification
011	
	None
UL1	cULus ordinary location for Canada and USA
04.2	Les reserves
012	Flow direction
	Flow direction from left to right
Z	Flow direction from right to left
013	Version

В

Basic

Type codes

001	Series	
MS6	MS-series, size 6	
002	Size	
6	Grid dimension 62 mm	
003	Function	
EE	On/off valve, electric	
004	Pneumatic connection	
1/4	Female thread G1/4	
3/8	Female thread G3/8	
1/2	Female thread G1/2	
AGB	Sub-base G1/4	
AGC	Sub-base G3/8	
AGD	Sub-base G1/2	
AGE	Sub-base G3/4	
AQN	Sub-base 1/4 NPT	
AQP	Sub-base 3/8 NPT	
AQR	Sub-base 1/2 NPT	
AQS	Sub-base 3/4 NPT	
005	Supply voltage	

005	Supply voltage	
V230	230 V AC (connection pattern to EN 175301)	
10V24	24 V DC, 10 bar, connection pattern to EN 175301	
V110	110 V AC (connection pattern to EN 175301)	
10V24C	24 V DC, 10 bar (connection pattern to EN 175301) without manual override	
10V24D	24 V DC, 10 bar, M12 (connection pattern to EN 60947-5-2) without manual override	
10V24F	24 V DC, 10 bar, M12 (connection pattern to EN 60947-5-2). Manual override on the pilot actuator non-detenting, internally detenting	
10V24P	24 V DC, 10 bar, M12 plug socket adapter (connection pattern to EN 60947-5-2)	
V24	24 V DC (connection pattern to EN 175301)	
V24P	24 V DC plug (connection pattern M12 to DESINA)	

006	Silencer	
	None	
S	Silencer	

007	Pressure gauge alternatives	
	None	
AG	MS pressure gauge	
A8	Adapter for EN pressure gauge 1/8, without pressure gauge	
A4	Adapter for EN pressure gauge 1/4, without pressure gauge	
RG	Integrated pressure gauge, red/green scale	
AD1	Pressure sensor with LCD display, M8 plug, PNP, 3-pin	
AD2	Pressure sensor with LCD display, M8 plug, NPN, 3-pin	
AD3	Pressure sensor with LCD display, M12 plug, PNP, 4-pin, ana-	
	logue output 4 20 mA	
AD4	Pressure sensor with LCD display, M12 plug, NPN, 4-pin, ana-	
	logue output 4 20 mA	
AD7	Pressure sensor with switching display, M8 plug, threshold val-	
	ue comparator, PNP, N/O	
AD8	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C	
AD9	Pressure sensor with switching display, M8 plug, window com-	
	parator, PNP, N/O	
AD10	Pressure sensor with operational status indicator, M8 plug,	
	window comparator, PNP, N/C	
AD11	Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®,	
	PNP, NPN, 010 V, 15 V, 420 mA	
AD12	Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®,	
	PNP, NPN, 010 V, 15 V, 420 mA	

008	ternative pressure gauge scale	
	MS pressure gauge	
PSI	psi	
MPA	MPa	

009	Type of mounting	
	Without mounting bracket	
WP	Mounting bracket basic design	
WPM	Mounting bracket for hooking in service unit components	
WB	Mounting centrally at rear (wall mounting top and bottom), con-	
	necting plates not required	

010	EU certification	
	None	
EX2	II 3GD	

011	UL certification	
	None	
UL1	cULus ordinary location for Canada and USA	

012	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	


On/off valves MS4/MS6-EE, MS series

Datasheet

Function



Flow rate 1000 ... 7000 l/min
Temperature range
-10 ... +60°C



- www.festo.com

- Electrically actuated on/off valve for pressurising and exhausting pneumatic systems
- With solenoid coil, without plug socket
- Choice of three voltage ranges
- Ducted exhaust possible via a threaded connection with silencer
- Manual override: non-detenting and detenting (variant 10V24/10V24F non-detenting only)
- Solenoid actuator can be repositioned by 180°



- Optional pressure sensor
- Optional device variant EX2 for use in potentially explosive areas in zones 2 and 22

General technical data

Ci		MC/	MC			
Size		MS4	MS6			
Pneumatic connection 1, 2						
Female thread		G1/8 or G1/4	G1/4, G3/8 or G1/2			
Connecting plate	[AG]	G1/8, G1/4 or G3/8	G1/4, G3/8, G1/2 or G3/4			
	[AQ]	1/8 NPT, 1/4 NPT or 3/8 NPT	1/4 NPT, 3/8 NPT, 1/2 NPT or 3/4 NPT			
Pneumatic connection 3		G1/4	G1/2			
Design		Piston spool				
Type of mounting		With accessories				
		In-line installation				
Mounting position		Any ¹⁾				
Display pressure		Via pressure sensor for indicating the output pressure and electrical	output via LCD display			
		Via pressure sensor for indicating the output pressure and electrical output via status indicator				
		Via pressure gauge for displaying the output pressure				
		Via pressure gauge with red/green scale for indicating the output pressure				
		Prepared for G1/8				
		Prepared for G1/4				
Valve function		3/2-way valve, closed, single solenoid				
Exhaust air function		Cannot be throttled				
Manual override						
With supply	[10V24], [10V24F]	Non-detenting				
voltage	[V24], [V24P],	Non-detenting/detenting				
	[10V24P], [V110],					
[V230]						
[10V24C], [10V24D]		None				
Reset method		Mechanical spring				
Switching position indic	ation	With accessories				
Type of control		Piloted				
Pilot air supply		Internal				
Flow direction		Not reversible				

¹⁾ The on/off valve must be mounted vertically when combined with a pressure sensor as condensate must not collect in the pressure sensor.

24

Electrical data

Characteristic coil data		
With supply	[V24], [V24P]	24 V DC: 1.5 W; permissible voltage fluctuations –25%/+10%
voltage	[10V24]	24 V DC: 1.8 W; permissible voltage fluctuations –15%/+10%
	[V110]	110 V AC: 50/60 Hz; pick-up power 3.0 VA; holding power 2.4 VA; permissible voltage fluctuations ±10%
	[V230]	230 V AC: 50/60 Hz; pick-up power 3.0 VA; holding power 2.4 VA; permissible voltage fluctuations –14%/+10%
Electrical connection		
With supply voltage	[V24], [10V24], [10V24C], [V110], [V230]	Plug, square design to EN 175301-803, type C
	[V24P], [10V24D], [10V24F], [10V24P]	M12x1 to ISO 20401 in line with EN 61076-2-101
Degree of protection fo	r solenoid coil	IP65
Duty cycle	[%]	100

Characteristic flow rate values							
Size	MS4		MS6				
Pneumatic connection 1, 2	G1/8	G1/4	G1/4	G3/8	G1/2		
Standard nominal flow rate qnN ¹⁾ [l/min]	Standard nominal flow rate qnN ¹⁾ [l/min]						
In main flow direction 1 → 2	1000	2000	2600	5500	7000		
In relief direction 2 → 3	1600	1600	7000	6200	5500		
C value [l/s*min]							
In main flow direction 1 → 2	4.5	9.5	11.0	22.0	29.0		
b value							
In main flow direction 1 → 2	0.5	0.44	0.5	0.5	0.4		

¹⁾ Measured at p1 = 6 bar and p2 = 5 bar, Δp = 1 bar.

Operating and environmental con	nditions								
Size	ze MS4			MS6					
On/off valve		Without pressure sens	or	With pressure sensor	Without pressure sens	sor	With pressure sensor		
Supply voltage		[V24], [V24P], [V110], [V230]	[10V24]		[V24], [V24P], [V110], [V230]	[10V24]			
Operating pressure	[bar]	4 14 (4 10)1)	4 10	4 10	4 18 (4 10)1)	4 10	4 10		
Operating medium	Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]						
		Inert gases							
Note on the operating/pilot mediu	ım	Lubricated operation possible (in which case lubricated operation will always be required)							
Ambient temperature	[°C]	-10 +60	-10 +50	0 +50	-10 +60	-10 +50	0 +50		
Temperature of medium	[°C]	-10 +60	-10 +50	0 +50	-10 +60	-10 +50	0 +50		
Corrosion resistance class CRC ²⁾		2							
Food-safe ³⁾		See supplementary material information (except for solenoid valve)							
UL certification ³⁾		c UL us - Recognized (OL)							
CE marking (see declaration of conformity) ³⁾		To EU EMC Directive							
		To EU Low Voltage Directive							
KC marking		_	_	KC EMC	_	_	KC EMC		

 $^{1) \}quad \text{Value in brackets applies to MS4/MS6-EE with UL certification or with silencer in combination with EU certification.} \\$

Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

³⁾ Additional information: www.festo.com/catalogue/ms \rightarrow Support/Downloads.


ATEX	1			
EU certification	[EX2]			
ATEX category for gas	II 3G			
Type of (ignition) protection for gas	Ex nA IIC T4 X Gc			
ATEX category for dust	3D			
Type of (ignition) protection for dust	Ex tc IIIC T105°C X Dc IP65			
Explosion-proof ambient temperature	-10°C≤Ta≤+60°C			
CE marking (see declaration of conformity) ¹⁾	To EU Explosion Protection Directive (ATEX)			
	To EU EMC Directive			
	To EU Low Voltage Directive			

 $^{1) \}quad \text{Additional information: www.festo.com/catalogue/ms} \rightarrow \text{Support/Downloads}.$

Weight [g]		
Size	MS4	MS6
On/off valve	273	740
On/off valve with silencer	289	816

Materials


Sectional view




On/o	ff valve	
[1]	Housing	Die-cast aluminium
[2]	Piston	NBR/aluminium
[3]	Springs	High-alloy stainless steel
[4]	End cover	PA PA
[5]	Plate	PA
[6]	Socket end connection	PA
_	Seals	NBR
Note	on materials	RoHS-compliant
		Free of copper and PTFE (not with supply voltage [24P], [10V24],
		MS pressure gauge with standard scale or pressure sensor)

Manual override

[V24], [V24P], [V110], [V230] Supply voltage




- [4] Manual override: non-detenting (as supplied)
- [5] Spool
- [6] Cover



Note

For detenting manual override, remove the grey cover [6] and push the spool [5] downwards.

[10V24], [10V24F], [10V24P] Supply voltage



[7] Manual override: non-detenting and detenting. ([10V24] and [10V24F] non-detenting only).

Dimensions - Basic version Download CAD data → www.festo.com With female thread, with cover plate [V24], [10V24], [10V24C], [V110], [V230] [10V24D], [10V24F], [10V24P] [V24P] Supply voltage Supply voltage Supply voltage ВЗ ВЗ В2 В2 В1 [3] 4 1 6 \Box 7 1 = not assigned 2 = not assigned 1 1 ٥ 3 = com(-)4 = Signal (+) solenoid 14 D'5 B4. В5 [1] Plug connection to [2] Solenoid actuator can be repos-[4] Electrical connection M12x1 to Flow direction EN 175301-803 itioned by 180°, i.e. solenoid ISO 20401 conforming to points to the front EN 61076-2-101, 4-pin version [3] PIN for solenoid actuators 110 V for connecting cable NEBU-M12 and 230 V only Type В1 В4 B5 В6 В7 D1 D5 D7 [V24] [10V24] [V24] [10V24] [10V24C] [10V24C] [V24P] [V24P] [V110] [10V24D] [V110] [10V24D] [V230] [10V24F] [V230] [10V24F] [10V24P] [10V24P] MS4-... MS4-EE-1/8 G1/8 35 75 40 42 68 21 54 31 11 G1/4 M12x1 MS4-EE-1/4 G1/4 MS6-... MS6-EE-1/4 G1/4 MS6-EE-3/8 52 45 97 90 31 76 11 G3/8 G1/2 M12x1 MS6-EE-1/2 G1/2 L3 L8 L9 Туре L1 [V24] [V24P] [V24-EX2] [10V24] [10V24D] [V24P] [V24-EX2] [10V24F] [V110] [10V24C] [V230] [10V24P] MS4-... MS4-EE-1/8 142.8 156¹⁾ 160¹⁾ 140 145 59 100 22¹⁾ 26¹⁾ 26 MS4-EE-1/4 MS6-... MS6-EE-1/4 199¹⁾ 203¹⁾ 22¹⁾ 26¹⁾ MS6-EE-3/8 186 183 188 84 143 8.6 27.5 MS6-EE-1/2


¹⁾ Measured with plug socket MSSD-EB (included in the scope of delivery).

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions – Pressure gauge/pressure gauge alternatives

[AG] Integrated MS pressure gauge with standard scale


[RG] Integrated MS pressure gauge with red/green scale



Download CAD data → www.festo.com

[A8] Adapter for EN pressure gauge 1/8, without pressure gauge


 $[{\rm A4}] \quad \text{Adapter for EN pressure gauge 1/4, without pressure gauge}$




Туре		B2		В3	D1	D4
	[V24] [V24P] [V110] [V230]	[10V24] [10V24C] [10V24D] [10V24F] [10V24P]	[V24] [V24P] [V110] [V230]	[10V24] [10V24C] [10V24D] [10V24F] [10V24P]		
MS4						
MS4-EE-1/8AG	42	35	86	79	G1/8	-
MS4-EE-1/4AG MS4-EE-1/8RG					G1/4 G1/8	
MS4-EE-1/4RG	42	35	87.5	80.5	G1/8	-
MS4-EE-1/8A8			70.5		G1/8	64/6
MS4-EE-1/4A8	42	35	79.5	72.5	G1/4	G1/8
MS4-EE-1/8A4	42	35	79.5	72.5	G1/8	G1/4
MS4-EE-1/4A4	72	33	75.5	7 2.3	G1/4	01/4
MS6						
MS6-EE-1/4AG					G1/4	
MS6-EE-3/8AG	52	45	98	91	G3/8	_
MS6-EE-1/2AG					G1/2	
MS6-EE-1/4RG	-				G1/4	
MS6-EE-3/8RG	52	45	99.5	92.5	G3/8	-
MS6-EE-1/2RG					G1/2	
MS6-EE-1/4A8	_				G1/4	
MS6-EE-3/8A8	52	45	99.5	92.5	G3/8	G1/8
MS6-EE-1/2A8					G1/2	
MS6-EE-1/4A4					G1/4	
MS6-EE-3/8A4	52	45	99.5	92.5	G3/8	G1/4
MS6-EE-1/2A4					G1/2	

Dimensions - Pressure sensor

[AD1], [AD2], [AD3], [AD4] Pressure sensor with LCD display





→ Flow direction

[AD1]:

SDE1-D10-G2-MS...-L-P1-M8 with 3-pin plug M8x1, 1 switching output PNP

[AD2]:

SDE1-D10-G2-MS...-L-N1-M8 with 3-pin plug M8x1, 1 switching output NPN

Download CAD data → www.festo.com

Datasheets → Internet: sde1


[AD3]:


SDE1-D10-G2-MS...-L-PI-M12 with 4-pin plug M12x1, 1 switching output PNP and 4 ... 20 mA analogue

[AD4]:

SDE1-D10-G2-MS...-L-NI-M12 with 4-pin plug M12x1, 1 switching output NPN and 4 ... 20 mA analogue

[AD7], [AD8], [AD9], [AD10] Pressure sensor with status indicator





→ Flow direction

[AD7]:

SDE5-D10-O-...-P-M8 with 3-pin plug M8x1, threshold value comparator, 1 switching output PNP, N/O contact

[AD8]:

SDE5-D10-C-...-P-M8 with 3-pin plug M8x1, threshold value comparator, 1 switching output PNP, N/C contact

[AD9]:


SDE5-D10-O3-...-P-M8 with 3-pin plug M8x1, window comparator, 1 switching output PNP, N/O contact


Datasheets → Internet: sde5

[AD10]:

SDE5-D10-C3-...-P-M8 with 3-pin plug M8x1, window comparator, 1 switching output PNP, N/C contact

[AD11], [AD12] Pressure sensor with LCD display





[AD11]:

SPAU-P10R-MS...-L-PNLK-M12D with 4-pin plug M12x1 A-coded, switching output 2x PNP or 2x NPN switchable and 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA analogue

Datasheets → Internet: spau

[AD12]:

SPAU-P10R-MS...-L-PNLK-M8D with 4-pin plug M8x1 A-coded, switching output 2x PNP or 2x NPN switchable and 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA analogue

Туре	B2	В3	B4	B5	В6	D6	L5	L6
MS4								
MS4AD1, AD2	21	82.6	_	32	32.3	M8x1	35.1	46.7
MS4AD3, AD4	21	02.0	_	32	32.3	M12x1	33.1	55.8
MS4AD7, AD8, AD9, AD10	21	59.1	-	~32	16	M8x1	-	-
MS4AD11	21	81.2	73.3	32	32	M12x1	41.2	39
MS4AD12	21	81.2	/ 3.3	32	32	M8x1	37.9	39
MS6								
MS6AD1, AD2	24	102		51	22.2	M8x1	25.4	46.7
MS6AD3, AD4	31	103	_	51	32.3	M12x1	35.1	55.8
MS6AD7, AD8, AD9, AD10	31	79.1	-	~51	16	M8x1	-	-
MS6AD11	24	101.0	02.7	F.1	22	M12x1	41.2	20
MS6AD12	31	101.8	93.7	51	32	M8x1	37.9	39

Dimensions – Silencer [S] Silencer [EX2] EU certification

Туре	D2	L4				
MS4						
MS4-EES	20	55				
MS4-EESEX2	19	50.7				
MS6						
MS6-EES	28	108				
MS6-EESEX2	43	80				

★ Core Range

Ordering data						
Size	Connection	Supply voltage	Flow direction	Part no.	Туре	
MS4	G1/4	24 V DC	From left to right	★ 542578	MS4-EE-1/4-10V24	
MS6	G1/2	24 V DC	From left to right	★ 542582	MS6-EE-1/2-10V24	
With silencer						
MS4	G1/4	24 V DC	From left to right	★ 542598	MS4-EE-1/4-10V24-S	
MS6	G1/2	24 V DC	From left to right	★ 542602	MS6-EE-1/2-10V24-S	
Ordering data						
Size Size	Connection	Supply voltage	Flow direction	Part no.	Туре	
MS4	G1/8	24 V DC	From left to right	542580	MS4-EE-1/8-10V24	
	G1/4	24 V DC	From right to left	542579	MS4-EE-1/4-10V24-Z	
		110 V AC	From left to right	529535	MS4-EE-1/4-V110	
		230 V AC	From left to right	529537	MS4-EE-1/4-V230	
MS6	G1/4	24 V DC	From left to right	542584	MS6-EE-1/4-10V24	
	G3/8	24 V DC	From left to right	542586	MS6-EE-3/8-10V24	
	G1/2	24 V DC	From right to left	542583	MS6-EE-1/2-10V24-Z	
		110 V AC	From left to right	529823	MS6-EE-1/2-V110	
		230 V AC	From left to right	529825	MS6-EE-1/2-V230	
With silencer						
MS4	G1/8	24 V DC	From left to right	542600	MS4-EE-1/8-10V24-S	
	G1/4	24 V DC	From right to left	542599	MS4-EE-1/4-10V24-S-Z	
		110 V AC	From left to right	538719	MS4-EE-1/4-V110-S	
MS6	G1/4	24 V DC	From left to right	542604	MS6-EE-1/4-10V24-S	
	G3/8	24 V DC	From left to right	542606	MS6-EE-3/8-10V24-S	
	G1/2	24 V DC	From right to left	542603	MS6-EE-1/2-10V24-S-Z	
	1					

From left to right

538731

MS6-EE-1/2-V110-S

110 V AC

Ordering data – Modular product system

Grid dimension	[mm] 40	62	Conditions	Code	Enter code
Module no.	527709	527682			
Series	Standard			MS	MS
Size	4	6			
Function	On/off valve, electric			-EE	-EE
Pneumatic connection	Female thread G1/8	-	[1]	-1/8	
	Female thread G1/4	Female thread G1/4	[1]	-1/4	
	_	Female thread G3/8	[1]	-3/8	
	-	Female thread G1/2	[1]	-1/2	
	Connecting plate G1/8	-		-AGA	
	Connecting plate G1/4	Connecting plate G1/4		-AGB	
	Connecting plate G3/8	Connecting plate G3/8		-AGC	
	_	Connecting plate G1/2		-AGD	
	_	Connecting plate G3/4		-AGE	
	Connecting plate 1/8 NPT	-	[1]	-AQK	
	Connecting plate 1/4 NPT	Connecting plate 1/4 NPT	[1]	-AQN	
	Connecting plate 3/8 NPT	Connecting plate 3/8 NPT	[1]	-AQP	
	-	Connecting plate 1/2 NPT	[1]	-AQR	
	-	Connecting plate 3/4 NPT	[1]	-AQS	
Supply voltage	24 V DC (plug pattern to EN	175301)		-V24	
	4 14 bar	4 18 bar			
	24 V DC, M12x1 to ISO 204	01 in line with EN 61076-2-101	[1]	-V24P	
	4 14 bar	4 18 bar			
	24 V DC (plug pattern to EN	24 V DC (plug pattern to EN 175301), 4 10 bar,			
	manual override non-deten	ing			
	24 V DC (plug pattern to EN	24 V DC (plug pattern to EN 175301), 4 10 bar,			
	no manual override				
	24 V DC, M12x1 to ISO 204	[1] [2]	-10V24D		
		no manual override			
		24 V DC, M12x1 to ISO 20401 in line with EN 61076-2-101, 4 10 bar, manual override non-detenting 24 V DC, M12x1 to ISO 20401 in line with EN 61076-2-101, 4 10 bar, manual override			
	,	[1] [2]	-10V24P		
		non-detenting/detenting 110 V AC (plug pattern to EN 175301)			
	, ,,		[1]	-V110	
	4 14 bar	4 18 bar	[6]	Mana	
	230 V AC (plug pattern to El		[1]	-V230	
	4 14 bar	4 18 bar			

[1] 1/8; 1/4; 3/8; Not with EU EX2 certification.
1/2, AQK, AQN,
AQP, AQR, AQS,
V24P, 10V24,
10V24F, 10V24D,
10V24F, 10V24P,
V110, V230,
AD1 ... AD4,
AD7 ... AD12,

[2] 10V24, 10V24C, 10V24D, 10V24F, 10V24P


10V24, 10V24C, Max. operating pressure: 10 bar.

Ordering data – Modular product system

Ordering table						
Grid dimension	[mm]	40	62	Conditions	Code	Enter code
Silencer		None				
		Silencer		[3]	-S	
Pressure gauge/pressure gauge		None				
alternatives		MS pressure gauge, bar			-AG	
		Adapter for EN pressure gau	uge 1/8, without pressure gauge		-A8	
		Adapter for EN pressure gau	uge 1/4, without pressure gauge		-A4	
		Integrated pressure gauge, red/green scale			-RG	
		Pressure sensor with LCD display, M8 plug, 1 switching output PNP, 3-pin			-AD1	
		Pressure sensor with LCD display, M8 plug, 1 switching output NPN, 3-pin			-AD2	
		Pressure sensor with LCD display, Mo plug, 1 switching output NPN, 4-pin, analogue output 4 20 mA			-AD3	
		Pressure sensor with LCD display, plug M12, 1 switching output NPN, 4-pin, analogue output 4 20 mA			-AD4	
		Pressure sensor with status	indicator, plug M8, threshold value comparator, PNP, N/O contac	t [1] [4] t [1] [4]	-AD7	
		Pressure sensor with status indicator, plug M8, threshold value comparator, PNP, N/C contact			-AD8	
		Pressure sensor with status indicator, plug M8, window comparator, PNP, N/O contact			-AD9	
		Pressure sensor with status indicator, plug M8, window comparator, PNP, N/C contact			-AD10	
		Pressure sensor with LCD display, plug M12, 4-pin, IO-Link, PNP, NPN, 0 10 V, 1 5 V, 4 20 mA			-AD11	
		Pressure sensor with LCD display, plug M8, 4-pin, IO-Link, PNP, NPN, 0 10 V, 1 5 V, 4 20 mA			-AD12	
Alternative pressure gauge scale		None				
		psi		[5]	-PSI	
		MPa		[6]	-MPA	
Type of mounting		Without mounting bracket				
		Mounting bracket standard	design	[7]	-WP	
		Mounting bracket for attach	ing service unit components	[1] [7]	-WPM	
		Mounting bracket centrally quired	at rear (wall mounting top and bottom), connecting plates not re-		-WB	
		Mounting bracket centrally mounting top), connecting			-WBM	
U certification		None	•			
		II 3GD to EU Explosion Protection Directive (ATEX)			-EX2	
JL certification		None				
		cULus, ordinary location for	[8]	-UL1		
low direction		Flow direction from left to ri	ght			
		Flow direction from right to	left		-Z	

```
[1] 1/8; 1/4; 3/8;
                       Not with EU EX2 certification.
     1/2, AQK, AQN,
     AQP, AQR, AQS,
     V24P, 10V24,
     10V24C, 10V24D,
     10V24F, 10V24P,
     V110, V230,
     AD1 ... AD4,
     AD7 ... AD12,
     WPM
[3] S
                       Max. operating pressure 10 bar in combination with EU EX2 certification.
    AD1 ... AD4,
[4]
                        Measuring range max. 10 bar.
     AD7 ... AD12
[5]
    PSI
                        Only in combination with pressure gauge AG.
     MPA
                        Only in combination with pressure gauge AG or RG.
[7]
     WP, WPM
                        Only with connecting plate AGA, AGB, AGC, AGD, AGE, AQK, AQN, AQP, AQR or AQS.
     UL1
                        Not with supply voltage V110, V230.
```

Peripherals overview



- Note

Additional accessories:

- Module connector for combination with size MS4/MS6 or size MS9
 - → Internet: amv, rmv, armv
- Adapter for mounting on profiles
- → Internet: ipm-80, ipm-40-80, ipm-80-80

Peripherals overview

Moun	Mounting attachments and accessories					
		Order code	→ Page/Internet			
[1]	Soft-start valve	MS4/6-DL	38			
Can b	e ordered via the modular product system					
[3]	Mounting bracket	[WP]	44			
	Mounting bracket (not shown)	[WPM]				
[4]	Mounting bracket	[WB]				
[5]	Mounting bracket	[WBM]				
[8]	Connecting plate SET ¹⁾	[AG]				
	Connecting plate SET ¹⁾	[AQ]				
[10]	Pressure sensor SDE1 with LCD display	[AD1], [AD2], [AD3], [AD4]				
[11]	Pressure sensor SPAU with LCD display	[AD11], [AD12]				
[13]	Pressure sensor SDE5 with status indicator	[AD7], [AD8], [AD9], [AD10]				
[15]	Adapter for EN pressure gauge 1/8, 1/4	[A8], [A4]				
[18]	MS pressure gauge	[AG], [RG]				
Can b	e ordered as accessories					
[2]	Module connector	MS4/6-MV	ms4-mv, ms6-mv			
[3]	Mounting bracket	MS4/6-WP	ms4-wp, ms6-wp			
	Mounting bracket (not shown)	MS4/6-WPB/WPE/WPM	ms4-wp, ms6-wp			
[4]	Mounting bracket	MS4/6-WB	ms4-wb, ms6-wb			
[5]	Mounting bracket	MS4-WBM	ms4-wbm			
[6]	Cover cap	MS4/6-END	ms4-end, ms6-end			
[7]	Mounting plate ²⁾	MS4/6-AEND	ms4-aend, ms6-aend			
[8]	Connecting plate SET ²⁾	MS4/6-AG	ms4-ag, ms6-ag			
[9]	Connecting cable	NEBU-M8LE3, NEBU-M12LE4	103			
[12]	Connecting cable	NEBU-M8LE4, NEBU-M12LE4	103			
[14]	Connecting cable	NEBU-M8LE3	103			
[16]	Pressure gauge	MA	103			
[17]	Pressure sensor	SPAUT	102			

Module connector [2] is included in the scope of delivery.
 Module connector MS4/6-MV [2] or mounting bracket MS4/6-WP, WPB, WPE, WPM [3] is required for mounting.

Type codes

001	Series	
MS	MS series	
002	Size	
4	Grid dimension 40 mm	
003	Function	
DL	Soft-start valve, pneumatic	
004	Pneumatic connection	
004 1/8	Pneumatic connection Female thread G1/8	
1/8	Female thread G1/8	
1/8 1/4	Female thread G1/8 Female thread G1/4	
1/8 1/4 AGA	Female thread G1/8 Female thread G1/4 Sub-base G1/8	
1/8 1/4 AGA AGB	Female thread G1/8 Female thread G1/4 Sub-base G1/8 Sub-base G1/4	
1/8 1/4 AGA AGB AGC	Female thread G1/8 Female thread G1/4 Sub-base G1/8 Sub-base G1/4 Sub-base G3/8	

005	Pressure gauge alternatives	
	None	
AG	MS pressure gauge	
A8	Adapter for EN pressure gauge 1/8, without pressure gauge	
A8M	Adapter for EN pressure gauge 1/8, with precision pressure gauge	
A4	Adapter for EN pressure gauge 1/4, without pressure gauge	
RG	Integrated pressure gauge, red/green scale	
AD1	Pressure sensor with LCD display, M8 plug, PNP, 3-pin	
AD2	Pressure sensor with LCD display, M8 plug, NPN, 3-pin	
AD3	Pressure sensor with LCD display, M12 plug, PNP, 4-pin, analogue	
	output 4 20 mA	
AD4	Pressure sensor with LCD display, M12 plug, NPN, 4-pin, analogue	
	output 4 20 mA	
AD7	Pressure sensor with switching display, M8 plug, threshold value	
	comparator, PNP, N/O	
AD8	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C	
AD9	Pressure sensor with switching display, M8 plug, window comparator,	
	PNP, N/O	
AD10	Pressure sensor with operational status indicator, M8 plug, window	
	comparator, PNP, N/C	
AD11	Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP,	
	NPN, 010 V, 15 V, 420 mA	
AD12	Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP,	
	NPN, 010 V, 15 V, 420 mA	

006	Alternative pressure gauge scale	
	MS pressure gauge	
PSI	psi	
MPA	MPa	
007	Type of mounting	
	Without mounting bracket	
WP	Mounting bracket basic design	
WPM	Mounting bracket for hooking in service unit components	
WB	Mounting centrally at rear (wall mounting top and bottom), connecting	
	plates not required	
WBM	Mounting centrally at rear (wall mounting top), connecting plates not	
	required	
008	EU certification	
	None	
EX2	II 3GD to EU Explosion Protection Directive (ATEX)	
EX4	II 2GD	
009	UL certification	
	None	
UL1	cULus ordinary location for Canada and USA	
010	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	

Type codes

001	Series	
MS	MS series	
002	Size	
6	Grid dimension 62 mm	
003	Function	
DL	Soft-start valve, pneumatic	
004	Pneumatic connection	
1/4	Female thread G1/4	
3/8	Female thread G3/8	
1/2	Female thread G1/2	
AGB	Sub-base G1/4	
AGC	Sub-base G3/8	
AGD	Sub-base G1/2	
AGE	Sub-base G3/4	
AQN	Sub-base NPT1/4	
AQP	Sub-base NPT3/8	
AQR	Sub-base NPT1/2	
AQS	Sub-base NPT3/4	

005	Pressure gauge alternatives	Pressure gauge alternatives							
	None								
AG	MS pressure gauge								
A8	Adapter for EN pressure gauge 1/8, without pressure gauge								
A4	Adapter for EN pressure gauge 1/4, without pressure gauge								
RG	Integrated pressure gauge, red/green scale								
AD1	Pressure sensor with LCD display, M8 plug, PNP, 3-pin								
AD2	Pressure sensor with LCD display, M8 plug, NPN, 3-pin								
AD3	Pressure sensor with LCD display, M12 plug, PNP, 4-pin, analogue output 4 20 mA								
AD4	Pressure sensor with LCD display, M12 plug, NPN, 4-pin, analogue output 4 20 mA								
AD7	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/O								
AD8	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C								
AD9	Pressure sensor with switching display, M8 plug, window comparator, PNP, N/O								
AD10	Pressure sensor with operational status indicator, M8 plug, window comparator, PNP, N/C								
AD11	Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 010 V, 15 V, 420 mA								
AD12	Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 010 V, 15 V, 420 mA								

006	Alternative pressure gauge scale							
	MS pressure gauge							
PSI	psi							
MPA	MPa							
007	Type of mounting							
	Without mounting bracket							
WP	Mounting bracket basic design							
WPM	Mounting bracket for hooking in service unit components							
WB	Mounting centrally at rear (wall mounting top and bottom), connecting plates not required							
008	EU certification							
	None							
EX2	II 3GD to EU Explosion Protection Directive (ATEX)							
EX4	II 2GD							
009	UL certification							
	None							
UL1	cULus ordinary location for Canada and USA							
010	Flow direction							
	Flow direction from left to right							

Flow direction from right to left

Function



- N - Flow rate 1000 ... 6450 l/min
- N - Temperature range
-10 ... +60°C
- → Operating pressure

4 ... 18 bar



The duration of the pressure build-up is set using the restrictor attached to the valve cap.

The outlet pressure p2 rises slowly in accordance with the restrictor setting. The main seat opens when the switchthrough pressure is reached.

 Pneumatically actuated soft-start valve for slowly pressurising and exhausting pneumatic systems (for use with on/off valves EM1 and EE)

- The drives move slowly and reliably into the initial position
- Sudden and erratic movements are avoided
- Main seat opening at approx. 50% of operating pressure
- Adjustable switching time delay
- Optional pressure sensor
- Optional device variant EX4 for use in potentially explosive areas in zones 1, 2, 21 and 22

General technical data

General technical data		1	I			
Size		MS4	MS6			
Pneumatic connection 1, 2						
Female thread		G1/8 or G1/4	G1/4, G3/8 or G1/2			
Connecting plate [A	١G]	G1/8, G1/4 or G3/8	G1/4, G3/8, G1/2 or G3/4			
[A	(Q]	1/8 NPT, 1/4 NPT or 3/8 NPT	1/4 NPT, 3/8 NPT, 1/2 NPT or 3/4 NPT			
Design		Piston seat				
Type of mounting		With accessories				
		In-line installation				
Mounting position		Any ¹⁾				
Display pressure		Via pressure sensor for indicating the output pressure and electrical output via LCD display				
		Via pressure sensor for indicating the output pressure and electrical output via status indicator				
		Via pressure gauge for displaying the output pressure				
		Via pressure gauge with red/green scale for indicating the output pressure				
		Prepared for G1/8				
		Prepared for G1/4				
Valve function		2/2-way valve				
Exhaust air function		Can be throttled				
Reset method		Mechanical spring				
Type of control	·	Direct				
Pilot air supply		External				
Flow direction		Not reversible				

¹⁾ The soft-start valve must be mounted vertically when combined with a pressure sensor as condensate must not collect in the pressure sensor.

 $[\]mbox{\ensuremath{\mbox{\ensuremath}\ensuremat$

Characteristic flow rate values					
Size	MS4		MS6		
Pneumatic connection 1, 2	G1/8	G1/4	G1/4	G3/8	G1/2
Standard nominal flow rate qnN1) [l/m	in]				
In main flow direction 1 → 2	1000	2000	2800	5050	6450
In relief direction 2 → 1	1000	2000	2800	5050	6400
C value [l/s*min]					
In main flow direction 1 → 2	4.6	9.6	11.22	21.05	28.97
b value					
In main flow direction 1 → 2	0.5	0.45	0.54	0.48	0.39

¹⁾ Measured at p1 = 6 bar and p2 = 5 bar, Δ p = 1 bar.

Operating and environmental conditions								
Size		MS4		MS6				
Soft-start valve		Without pressure sensor	With pressure sensor	Without pressure sensor	With pressure sensor			
Operating pressure	[bar]	4 14 (4 10)1)	4 10	4 18 (4 10)1)	4 10			
Operating medium		Compressed air to ISO 8573-1	Compressed air to ISO 8573-1:2010 [7:4:4]					
		Inert gases	Inert gases					
Note on the operating/pilot m	edium	Lubricated operation possible (in which case lubricated operation will always be required)						
Ambient temperature	[°C]	-10 +60	0 +50	-10 +60	0 +50			
Temperature of medium	[°C]	-10 +60	0 +50	-10 +60	0 +50			
Corrosion resistance class CRC	2)	2						
Food-safe ³⁾		See supplementary material information						
UL certification ³⁾		c UL us - Recognized (OL)						

¹⁾ Value in brackets applies to MS4/MS6-DL with UL certification.

³⁾ Additional information: www.festo.com/catalogue/ms → Support/Downloads.

ATEX	
EU certification	[EX4]
ATEX category for gas	II 2G
Type of ignition protection for gas	Ex h IIC T6 Gb X
ATEX category for dust	II 2D
Type of ignition protection for dust	Ex h IIIC T60°C Db X
Explosion-proof ambient temperature	-10°C ≤ Ta ≤ +60°C
CE marking (see declaration of conformity) ¹⁾	To EU Explosion Protection Directive (ATEX)

Additional information: www.festo.com/catalogue/ms → Support/Downloads.


²⁾ Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

Weight [g]		
Size	MS4	MS6
Soft-start valve	213	650


Materials


Sectional view



Soft-	start valve	
[1]	Housing	Die-cast aluminium
[2]	Bottom	PET
[3]	End cover	PA PA
[4]	Plate	PA PA
[5]	Seat	Aluminium
[6]	Springs	Spring steel
_	Seals	NBR
Note	on materials	RoHS-compliant
		Free of copper and PTFE (not with MS pressure gauge with standard scale or pressure sensor)

$Switching\ point-Pressure\ p\ as\ a\ function\ of\ time\ t$





- [1] Tolerance range
- [2] Switching point
- [3] Filling time is adjustable via a restrictor

- 🏺 - Note


The +20%/-10% switching point tolerance refers to the operating pressure p1. Example: A switching point from 1.6 bar to 2.8 bar is permissible at an operating pressure of 4 bar.

· 🖢 - Note

The +20%/-20% switching point tolerance refers to the operating pressure p1. Example: A switching point from 1.2 bar to 2.8 bar is permissible at an operating pressure of 4 bar.

Dimensions – Basic version

With female thread, with cover plate



Download CAD data → www.festo.com

→ Flow direction


Туре	B1	B2	В3	D1	L1	L2		
MS4								
MS4-DL-1/8	40	21	54	G1/8	83.2	31.5		
MS4-DL-1/4	40	21		G1/4		51.5		
MS6								
MS6-DL-1/4				G1/4				
MS6-DL-3/8	62	31	76	G3/8	108	46		
MS6-DL-1/2				G1/2				

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions – Pressure gauge/pressure gauge alternatives

[AG] Integrated MS pressure gauge with standard scale


[RG] Integrated MS pressure gauge with red/green scale



Download CAD data → www.festo.com

[A8] Adapter for EN pressure gauge 1/8, without pressure gauge


[A4] Adapter for EN pressure gauge 1/4, without pressure gauge



Туре	B2	В3	D4
MS4			
MS4AG	21	57	-
MS4RG	21	58.5	-
MS4A8	21	58.5	G1/8
MS4A4	21	58.5	G1/4
MS6			
MS6AG	31	77	-
MS6RG	31	78.5	-
MS6A8	31	78.5	G1/8
MS6A4	31	78.5	G1/4

Dimensions - Pressure sensor

[AD1], [AD2], [AD3], [AD4] Pressure sensor with LCD display



[AD1]:

SDE1-D10-G2-MS...-L-P1-M8 with 3-pin plug M8x1, 1 switching output PNP

[AD2]:

SDE1-D10-G2-MS...-L-N1-M8 with 3-pin plug M8x1, 1 switching output NPN

Download CAD data → www.festo.com

Datasheets → Internet: sde1


[AD3]:


SDE1-D10-G2-MS...-L-PI-M12 with 4-pin plug M12x1, 1 switching output PNP and 4 ... 20 mA analogue

[AD4]:

SDE1-D10-G2-MS...-L-NI-M12 with 4-pin plug M12x1, 1 switching output NPN and 4 ... 20 mA analogue

[AD7], [AD8], [AD9], [AD10] Pressure sensor with status indicator





→ Flow direction

D6

[AD7]:

SDE5-D10-O-...-P-M8 with 3-pin plug M8x1, threshold value comparator, 1 switching output PNP, N/O contact

[AD8]:

SDE5-D10-C-...-P-M8 with 3-pin plug M8x1, threshold value comparator, 1 switching output PNP, N/C contact

Datasheets → Internet: sde5


[AD9]:


SDE5-D10-O3-...-P-M8 with 3-pin plug M8x1, window comparator, 1 switching output PNP, N/O contact

[AD10]:

SDE5-D10-C3-...-P-M8 with 3-pin plug M8x1, window comparator, 1 switching output PNP, N/C contact

[AD11], [AD12] Pressure sensor with LCD display





[AD11]:

SPAU-P10R-MS...-L-PNLK-M12D with 4-pin plug M12x1 A-coded, switching output 2x PNP or 2x NPN switchable and 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA analogue

Datasheets → Internet: spau

[AD12]:

SPAU-P10R-MS...-L-PNLK-M8D with 4-pin plug M8x1 A-coded, switching output 2x PNP or 2x NPN switchable and 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA analogue

Туре	B2	В3	B4	B5	В6	D6	L5	L6
MS4								
MS4AD1/AD2	21	82.6		32	32.3	M8x1	35.1	46.7
MS4AD3/AD4	21	02.0	_	52	32.3	M12x1	33.1	55.8
MS4AD7, AD8, AD9, AD10	21	59.1	-	~32	16	M8x1	-	-
MS4AD11	21	81.2	73.3	32	32	M12x1	41.2	39
MS4AD12	21	81.2	/ 3.3	32	32	M8x1	37.9	39
MS6								
MS6AD1/AD2	21	102		51	22.2	M8x1	25.1	46.7
MS6AD3/AD4	31	103	-	51	32.3	M12x1	35.1	55.8
MS6AD7, AD8, AD9, AD10	31	79.1	-	~51	16	M8x1	-	-
MS6AD11	31	101.9	02.7	F.1	22	M12x1	41.2	30
MS6AD12	31	101.8	93.7	51	32	M8x1	37.9	39

★ Core Range

Ordering data				
Size	Connection	Flow direction	Part no.	Туре
MS4	G1/4	From left to right	★ 529531	MS4-DL-1/4
MS6	G1/2	From left to right	★ 529817	MS6-DL-1/2

Ordering data	Ordering data				
Size	Connection	Flow direction	Part no.	Туре	
MS4	G1/8	From left to right	529533	MS4-DL-1/8	
	G1/4	From right to left	529532	MS4-DL-1/4-Z	
MS6	G1/4	From left to right	529819	MS6-DL-1/4	
	G3/8	From left to right	529821	MS6-DL-3/8	
	G1/2	From right to left	529818	MS6-DL-1/2-Z	

Ordering data – Modular product system

Grid dimension [mm]	40	62	Conditions	Code	Enter code
Module no.	527711	527684			
Series	Standard			MS	MS
Size	4	6			
Function	Soft-start valve, pneumatic			-DL	-DL
Pneumatic connection	Female thread G1/8	-	[1]	-1/8	
	Female thread G1/4	Female thread G1/4	[1]	-1/4	
	-	Female thread G3/8	[1]	-3/8	
	-	Female thread G1/2	[1]	-1/2	
	Connecting plate G1/8	-		-AGA	İ
	Connecting plate G1/4	Connecting plate G1/4		-AGB	
	Connecting plate G3/8	Connecting plate G3/8		-AGC	İ
	=	Connecting plate G1/2		-AGD	
	-	Connecting plate G3/4		-AGE	
	Connecting plate 1/8 NPT	-	[1]	-AQK	İ
	Connecting plate 1/4 NPT	Connecting plate 1/4 NPT	[1]	-AQN	
	Connecting plate 3/8 NPT	Connecting plate 3/8 NPT	[1]	-AQP	
	-	Connecting plate 1/2 NPT	[1]	-AQR	İ
	-	Connecting plate 3/4 NPT	[1]	-AQS	
Pressure gauge/pressure gauge	None				
alternatives	MS pressure gauge, bar			-AG	
	Adapter for EN pressure gauge 1/8, w	rithout pressure gauge		-A8	
	Adapter for EN pressure gauge 1/4, w	rithout pressure gauge		-A4	İ
	Integrated pressure gauge, red/greer	scale		-RG	
	Pressure sensor with LCD display, M8	plug, 1 switching output PNP, 3-pin	[1] [2]	-AD1	
	Pressure sensor with LCD display, M8	plug, 1 switching output NPN, 3-pin	[1] [2]	-AD2	
		g M12, 1 switching output PNP, 4-pin, analogue output	[1] [2]	-AD3	
	Pressure sensor with LCD display, plu 4 20 mA	g M12, 1 switching output NPN, 4-pin, analogue output	[1] [2]	-AD4	
	Pressure sensor with status indicator	, plug M8, threshold value comparator, PNP, N/O contact	[1] [2]	-AD7	
	Pressure sensor with status indicator	, plug M8, threshold value comparator, PNP, N/C contact	[1] [2]	-AD8	
	Pressure sensor with status indicator	, plug M8, window comparator, PNP, N/O contact	[1] [2]	-AD9	
	Pressure sensor with status indicator	, plug M8, window comparator, PNP, N/C contact	[1] [2]	-AD10	
	Pressure sensor with LCD display, plu 4 20 mA	g M12, 4-pin, IO-Link, PNP, NPN, 0 10 V, 1 5 V,	[1] [2]	-AD11	
	Pressure sensor with LCD display, plu 4 20 mA	g M8, 4-pin, IO-Link, PNP, NPN, 0 10 V, 1 5 V,	[1] [2]	-AD12	
Alternative pressure gauge scale	None				
	psi		[3]	-PSI	
	MPa		[4]	-MPA	

[1] 1/8; 1/4; 3/8; Not with EU EX4 certification. 1/2, AQK, AQN, AQP, AQR, AQS, AD1 ... AD4, AD7 ... AD12, WPM

[2] AD1 ... AD4, Measuring range max. 10 bar.

AD7 ... AD12

Only in combination with pressure gauge AG.
Only in combination with pressure gauge AG or RG.

3] PSI 0 4] MPA 0

Ordering data – Modular product system


Ordering table Grid dimension [mm]	40	62	Conditions	Code	Enter code
Type of mounting	Without mounting bracket				
	Mounting bracket standard design		[5]	-WP	
	Mounting bracket for attaching service unit com	ponents	[1] [5]	-WPM	
	Mounting bracket centrally at rear (wall mounting quired	ng top and bottom), connecting plates not re-		-WB	
	Mounting bracket centrally at rear (wall mounting top), connecting plates not required	-		-WBM	
EU certification	None				
	II 2GD to EU Explosion Protection Directive (ATE)	()		-EX4	
UL certification	None				
	cULus, ordinary location for Canada and USA			-UL1	
Flow direction	Flow direction from left to right				
	Flow direction from right to left			-Z	

[1] 1/8; 1/4; 3/8; Not with EU EX4 certification. 1/2, AQK, AQN, AQP, AQR, AQS, AD1 ... AD4, AD7 ... AD12,

WPM

[5] WP, WPM Only with connecting plate AGA, AGB, AGC, AGD, AGE, AQK, AQN, AQP, AQR or AQS.

Peripherals overview



- 🛔 -

- Note


Additional accessories:


- Module connector for combination with size MS4/MS6 or size MS9
 - → Internet: amv, rmv, armv
- Adapter for mounting on profiles
- → Internet: ipm-80, ipm-40-80, ipm-80-80

Peripherals overview

Supply voltage [V24], [10V24], [V110], [V230]

Supply voltage [10V24P





Moun	Mounting attachments and accessories						
		Order code	→ Page/Internet				
[1]	Soft-start valve	MS4/6-DE	50				
Can b	Can be ordered via the modular product system						
[3]	Mounting bracket	[WP]	56				
	Mounting bracket (not shown)	[WPM]					
[4]	Mounting bracket	[WB]					
[5]	Mounting bracket	[WBM]					
[8]	Connecting plate SET ¹⁾	[AG]					
	Connecting plate SET ¹⁾	[AQ]					
[10]	Pressure sensor SDE1 with LCD display	[AD1], [AD2], [AD3], [AD4]					
[11]	Pressure sensor SDE5 with status indicator	[AD7], [AD8], [AD9], [AD10]					
[13]	Adapter for EN pressure gauge 1/8, 1/4	[A8], [A4]					
[17]	MS pressure gauge	[AG], [RG]					
Can b	e ordered as accessories						
[2]	Module connector	MS4/6-MV	ms4-mv, ms6-mv				
[3]	Mounting bracket	MS4/6-WP	ms4-wp, ms6-wp				
	Mounting bracket (not shown)	MS4/6-WPB/WPE/WPM	ms4-wp, ms6-wp				
[4]	Mounting bracket	MS4/6-WB	ms4-wb, ms6-wb				
[5]	Mounting bracket	MS4-WBM	ms4-wbm				
[6]	Cover cap	MS4/6-END	ms4-end, ms6-end				
[7]	Mounting plate ²⁾	MS4/6-AEND	ms4-aend, ms6-aend				
[8]	Connecting plate SET ²⁾	MS4/6-AG	ms4-ag, ms6-ag				
[15]	Pressure sensor	SPAUT	102				
[14]	Pressure gauge	MA	103				
[12]	Connecting cable	NEBU-M8LE3	103				
[16]	Connecting cable	NEBU-M8LE4, NEBU-M12LE4	103				
[9]	Connecting cable	NEBU-M8LE3, NEBU-M12LE4	103				
[18]	Illuminating seal	MEB-LD	102				
[19]	Plug socket with cable	KMEB	102				
[20]	Plug socket ³⁾	MSSD-EB	102				
[21]	Locking clip	CPV18-HV	102				
[22]	Connecting cable	NEBU-M12G5	103				
[23]	Connecting cable	NEBU-M12W5	103				

Module connector [2] is included in the scope of delivery.
 Module connector MS4/6-MV [2] or mounting bracket MS4/6-WP, WPB, WPE, WPM [3] is required for mounting.

³⁾ For soft start valve MS...-V24-...-EX2, the plug socket is included in the scope of delivery.

Soft-start valves MS4/MS6-DE, MS series

Type codes

V24

001	Series	
MS	MS series	
002	Size	
4	Grid dimension 40 mm	
003	Function	
DE	Soft-start valve, electric	
004	Pneumatic connection	
1/8	Female thread G1/8	
1/4	Female thread G1/4	
AGA	Sub-base G1/8	
AGB	Sub-base G1/4	
AGC	Sub-base G3/8	
005	Supplyvoltage	
10V24	24 V DC, 10 bar, connection pattern to EN 175301	
10V24P	24 V DC, 10 bar, M12 plug socket adapter (connection pattern to EN 60947-5-2)	
V110	110 V AC (connection pattern to EN 175301)	
V230	230 V AC (connection pattern to EN 175301)	

006	Pressure gauge alternatives		
	None		
AG	MS pressure gauge		
A8	Adapter for EN pressure gauge 1/8, without pressure gauge		
A4	Adapter for EN pressure gauge 1/4, without pressure gauge		
RG	Integrated pressure gauge, red/green scale		
AD1	Pressure sensor with LCD display, M8 plug, PNP, 3-pin		
AD2	Pressure sensor with LCD display, M8 plug, NPN, 3-pin		
AD3	Pressure sensor with LCD display, M12 plug, PNP, 4-pin, analogue output 4 20 mA		
AD4	Pressure sensor with LCD display, M12 plug, NPN, 4-pin, analogue output 4 20 mA		
AD7 Pressure sensor with switching display, M8 plug, threshold va			
AD8	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C		
AD9	Pressure sensor with switching display, M8 plug, window comparator, PNP, N/O		
AD10	Pressure sensor with operational status indicator, M8 plug, window comparator, PNP, N/C		

24 V DC (connection pattern to EN 175301)

007	Alternative pressure gauge scale	
	MS pressure gauge	
PSI	psi	
MPA	MPa	
008	Type of mounting	
	Without mounting bracket	
WP	Mounting bracket basic design	
WPM	Mounting bracket for hooking in service unit components	
WB	Mounting centrally at rear (wall mounting top and bottom), connecting plates not required	
WBM	Mounting centrally at rear (wall mounting top), connecting plates not required	
009	EU certification	
	None	
EX2	II 3GD to EU Explosion Protection Directive (ATEX)	
010	UL certification	
	None	
UL1	cULus ordinary location for Canada and USA	
011	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	

Type codes

001	Series	
MS	MS series	
002	Size	
6	Grid dimension 62 mm	
003	Function	
DE	Soft-start valve, electric	
004	Pneumatic connection	
1/4	Female thread G1/4	
3/8	Female thread G3/8	
1/2	Female thread G1/2	
AGB	Sub-base G1/4	
AGC	Sub-base G3/8	
		
AGD	Sub-base G1/2	

AGE	Sub-base 63/4		
005	Supply voltage		
10V24	24 V DC, 10 bar, connection pattern to EN 175301		
10V24P	10V24P 24 V DC, 10 bar, M12 plug socket adapter (connection pattern to EN		
	60947-5-2)		
V110	110 V AC (connection pattern to EN 175301)		
V230	V230 230 V AC (connection pattern to EN 175301)		
V24	24 V DC (connection pattern to EN 175301)		

006	Pressure gauge alternatives	
	None	
AG	MS pressure gauge	
A4	Adapter for EN pressure gauge 1/4, without pressure gauge	
RG	Integrated pressure gauge, red/green scale	
AD1	Pressure sensor with LCD display, M8 plug, PNP, 3-pin	
AD2	Pressure sensor with LCD display, M8 plug, NPN, 3-pin	
AD3	Pressure sensor with LCD display, M12 plug, PNP, 4-pin, analogue	
AD4	output 4 20 mA	
AD4	Pressure sensor with LCD display, M12 plug, NPN, 4-pin, analogue output 4 20 mA	
AD7	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/O	
AD8	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C	
AD9	Pressure sensor with switching display, M8 plug, window comparator, PNP, N/O	
AD10	Pressure sensor with operational status indicator, M8 plug, window comparator, PNP, N/C	

007	Alternative pressure gauge scale				
	MS pressure gauge				
PSI	psi				
MPA	MPa				


800	Type of mounting						
	Without mounting bracket						
WP	Mounting bracket basic design						
WPM	Mounting bracket for hooking in service unit components						
WB	Mounting centrally at rear (wall mounting top and bottom), connecting plates not required						

	009 EU certification None				
		None			
Ī	EX2	II 3GD to EU Explosion Protection Directive (ATEX)			

010	UL certification	
	None	
UL1	cULus ordinary location for Canada and USA	

011	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	

Function



- N - Flow rate 1000 ... 6450 l/min
- N - Temperature range
-10 ... +60°C
- → Operating pressure
4 ... 18 bar




The duration of the pressure build-up is set using the restrictor attached to the valve cap.


The outlet pressure p2 rises slowly in accordance with the restrictor setting. While the solenoid valve is not actuated, only the flow rate of the flow control valve is available. The main seat is only opened when the solenoid valve is energised.

When the solenoid valve is switched off, the main seat is closed and only the flow rate of the flow control valve is available.

When exhausting a system, the solenoid valve should remain switched on; this increases the volume flow from 2 to 1 and shortens the exhausting time.



- The drives move slowly and reliably into the initial position
- Sudden and erratic movements are avoided
- With solenoid coil, without plug socket
- Choice of three voltage ranges



- The switching pressure can be precisely controlled with a solenoid valve
- Adjustable switching time delay
- Manual override: non-detenting and detenting (variant 10V24 non-detenting only)
- Solenoid actuator can be repositioned by 180°
- Optional pressure sensor
- Optional device variant EX2 for use in potentially explosive areas in zones 2 and 22

General technical data

Size		MS4 MS6				
Pneumatic connection 1, 2						
Female thread		G1/8 or G1/4	G1/4, G3/8 or G1/2			
Connecting plate	[AG]	G1/8, G1/4 or G3/8	G1/4, G3/8, G1/2 or G3/4			
	[AQ]	1/8 NPT, 1/4 NPT or 3/8 NPT	1/4 NPT, 3/8 NPT, 1/2 NPT or 3/4 NPT			
Design		Piston seat				
Type of mounting		With accessories				
		In-line installation				
Mounting position		Any ¹⁾				
Display pressure		Via pressure sensor for indicating the output pressure and electrical	output via LCD display			
		Via pressure sensor for indicating the output pressure and electrical output via status indicator				
		Via pressure gauge for displaying the output pressure				
		Via pressure gauge with red/green scale for indicating the output pressure				
		Prepared for G1/8 –				
		Prepared for G1/4				
Valve function		2/2-way valve				
Manual override						
With supply	[10V24]	Non-detenting Non-detenting				
voltage	[V24], [10V24P], [V110], [V230]	Non-detenting/detenting				
Reset method		Mechanical spring				
Signal status indication		With accessories				
Type of control	-	Piloted				
Pilot air supply		Internal				
Flow direction		Not reversible				

¹⁾ The soft-start valve must be mounted vertically when combined with a pressure sensor as condensate must not collect in the pressure sensor.

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Electrical data

Characteristic coil data	a	
With supply	[V24]	24 V DC: 1.5 W; permissible voltage fluctuations –25%/+10%
voltage	[10V24], [10V24P]	24 V DC: 1.8 W; permissible voltage fluctuations –15%/+10%
	[V110]	110 V AC: 50/60 Hz; pick-up power 3.0 VA; holding power 2.4 VA; permissible voltage fluctuations ±10%
	[V230]	230 V AC: 50/60 Hz; pick-up power 3.0 VA; holding power 2.4 VA; permissible voltage fluctuations –14%/+10%
Electrical connection		
With supply [V24], [10V24],		Plug, square design to EN 175301-803, type C
voltage	[V110], [V230]	
	[10V24P]	M12x1 to IEC 61076-2-101
		M12x1 to ISO 20401 in line with EN 61076-2-101
Degree of protection for	or solenoid coil	IP65
Duty cycle	[%]	100

Characteristic flow rate values								
Size	MS4		MS6					
Pneumatic connection 1, 2	G1/8	G1/4	G1/4	G3/8	G1/2			
Standard nominal flow rate qnN ¹⁾ [l/min]	Standard nominal flow rate qnN ¹ [l/min]							
In main flow direction 1 → 2	1000	2000	2700	5050	6450			
In relief direction 2 \rightarrow 1 ²⁾	1000	2000	2600	5050	6400			
C value [l/s*min]								
In main flow direction 1 → 2	4.6	9.6	11.22	21.05	28.97			
b value								
In main flow direction 1 → 2	0.5	0.45	0.54	0.48	0.39			

¹⁾ Measured at p1 = 6 bar and p2 = 5 bar, Δ p = 1 bar.

²⁾ With energised solenoid valve.

Operating and environmental conditions							
Size	MS4			MS6			
Soft-start valve	Without pressure sensor		With pressure sensor	Without pressure sensor		With pressure sensor	
Supply voltage	[V24], [V110], [V230]	[10V24], [10V24P]		[V24], [V110], [V230]	[10V24], [10V24P]		
Operating pressure [bar]	4 14 (4 10)1)	4 10	4 10	4 18 (4 10)1)	4 10	4 10	
Operating medium	Compressed air to ISO	8573-1:2010 [7:4:4]					
	Inert gases						
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)						
Ambient temperature [°C]	-10 +60	-10 +50	0 +50	-10 +60	-10 +50	0 +50	
Temperature of medium [°C]	-10 +60	-10 +50	0 +50	-10 +60	-10 +50	0 +50	
Corrosion resistance class CRC ²⁾	2						
Food-safe ³⁾	See supplementary material information (except for solenoid valve)						
UL certification ³⁾	c UL us - Recognized (OL)						
CE marking (see declaration of conformity) ³⁾	To EU EMC Directive						
	To EU Low Voltage Directive						
KC marking	_	_	KC EMC	-	-	KC EMC	

¹⁾ Value in brackets applies to MS4/MS6-DE with UL certification.

²⁾ Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

³⁾ Additional information: www.festo.com/catalogue/ms → Support/Downloads.


ATEX	
EU certification	[EX2]
ATEX category for gas	II 3G
Type of (ignition) protection for gas	Ex nA IICT4 X Gc
ATEX category for dust	II 3D
Type of (ignition) protection for dust	Ex tc IIIC T105°C X Dc IP65
Explosion-proof ambient temperature	-10°C≤Ta≤+60°C
CE marking (see declaration of conformity) ¹⁾	To EU Explosion Protection Directive (ATEX)
	To EU EMC Directive
	To EU Low Voltage Directive

 $^{1) \}quad \text{Additional information: www.festo.com/catalogue/ms} \rightarrow \text{Support/Downloads}.$

Weight [g]							
Size	MS4	MS6					
Soft-start valve	263	680					

Materials

Sectional view




Soft-s	Soft-start valve					
[1]	Housing	Die-cast aluminium				
[2]	Bottom	PET				
[3]	Valve tappet	Aluminium				
[4]	End cover	PA				
[5]	Plate	PA				
[6]	Seat	Aluminium				
[7]	Springs	Spring steel				
-	Seals	NBR				
Note on materials		RoHS-compliant				
		Free of copper and PTFE (not with supply voltage [10V24], [10V24P], MS pressure gauge with standard scale or pressure sensor)				

Manual override

[V24], [V110], [V230] Supply voltage






- [4] Manual override: non-detenting (as supplied)
- [5] Spool
- [6] Cover



For detenting manual override, remove the grey cover [6] and push the spool [5] downwards.

[10V24], [10V24P] Supply voltage



[7] Manual override: non-detenting and detenting ([10V24] non-detenting only)

Dimensions - Basic version Download CAD data → www.festo.com With female thread, with cover plate [V24], [10V24], [V110], [V230] Supply voltage [10V24P] Supply voltage ВЗ В2 В2 В1 1 = not assigned 3 1 2 = not assigned 3 = com(-)6 2 4 = Signal (+) solenoid page 14 0 B4_ B5 [1] Plug connection to [2] Solenoid actuator can be repos-[4] Electrical connection M12x1 to Flow direction EN 175301-803 itioned by 180°, i.e. solenoid ISO 20401 conforming to points to the front EN 61076-2-101, 4-pin version [3] PIN for solenoid actuators 110 $\rm V$ for connecting cable NEBU-M12 and 230 V only Туре В1 В4 B5 D1 [V24] [10V24] [V24] [10V24] [V110] [10V24P] [V110] [10V24P] [V230] [V230] MS4-... MS4-DE-1/8 G1/8 75.2 40 42.2 34.9 67.9 21 54 MS4-DE-1/4 G1/4 MS6-... MS6-DE-1/4 G1/4 MS6-DE-3/8 62 52 44 97 89 76 G3/8 31 MS6-DE-1/2 G1/2 Туре L2 L7 L8 L9 L1 [V24] [10V24] [10V24P] [V110] [V230] MS4-... MS4-DE-1/8 115.4 117.8 31.5 112.9 8.6 36.7 26.1 MS4-DE-1/4 MS6-...

149

147

MS6-DE-1/4 MS6-DE-3/8

MS6-DE-1/2

152

46

8.6

37

26

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions - Pressure gauge/pressure gauge alternatives Download CAD data → www.festo.com Integrated MS pressure gauge with standard scale Adapter for EN pressure gauge 1/8, without pressure gauge [A8] Integrated MS pressure gauge with red/green scale [A4] Adapter for EN pressure gauge 1/4, without pressure gauge В2 В2 5 Flow direction Flow direction Туре B2 ВЗ D1 D4 [10V24] [V24] [V24] [10V24] [V110] [10V24P] [V110] [10V24P] [V230] [V230] MS4-.. MS4-DE-1/8-...-AG G1/8 42.2 34.9 78.2 70.9 MS4-DE-1/4-...-AG G1/4 MS4-DE-1/8-...-RG G1/8 42.2 34.9 79.7 72.4 MS4-DE-1/4-...-RG G1/4 MS4-DE-1/8-...-A8 G1/8 G1/8 42.2 34.9 79.7 72.4 MS4-DE-1/4-...-A8 G1/4 G1/8 MS4-DE-1/8-...-A4 79.7 72.4 G1/4 42.2 34.9 MS4-DE-1/4-...-A4 G1/4

52

52

52

44

44

44

98

99.5

99.5

90

91.5

91.5

MS6-... MS6-DE-1/4-...-AG

MS6-DE-3/8-...-AG

MS6-DE-1/2-...-AG

MS6-DE-1/4-...-RG

MS6-DE-3/8-...-RG

MS6-DE-1/2-...-RG

MS6-DE-1/4-...-A4

MS6-DE-3/8-...-A4

MS6-DE-1/2-...-A4

G1/4

G1/4

G3/8

G1/2

G1/4

G3/8

G1/2


G1/4


G3/8

G1/2

Dimensions - Pressure sensor

[AD1], [AD2], [AD3], [AD4] Pressure sensor with LCD display





→ Flow direction

[AD1]:

SDE1-D10-G2-MS...-L-P1-M8 with 3-pin plug M8x1, 1 switching output PNP

[AD2]:

SDE1-D10-G2-MS...-L-N1-M8 with 3-pin plug M8x1, 1 switching output NPN

Download CAD data → www.festo.com

Datasheets → Internet: sde1


[AD3]:


SDE1-D10-G2-MS...-L-PI-M12 with 4-pin plug M12x1, 1 switching output PNP and 4 ... 20 mA analogue

[AD4]:

SDE1-D10-G2-MS...-L-NI-M12 with 4-pin plug M12x1, 1 switching output NPN and 4 ... 20 mA analogue

[AD7], [AD8], [AD9], [AD10] Pressure sensor with status indicator





→ Flow direction

[AD7]:

SDE5-D10-O-...-P-M8 with 3-pin plug M8x1, threshold value comparator, 1 switching output PNP, N/O contact

[AD8]:

SDE5-D10-C-...-P-M8 with 3-pin plug M8x1, threshold value comparator, 1 switching output PNP, N/C contact

[AD9]:

SDE5-D10-O3-...-P-M8 with 3-pin plug M8x1, window comparator, 1 switching output PNP, N/O contact

Datasheets → Internet: sde5

[AD10]:

SDE5-D10-C3-...-P-M8 with 3-pin plug M8x1, window comparator, 1 switching output PNP, N/C contact

Туре	B2	В3	B4	B5	В6	D6	L5	L6		
MS4	MS4									
MS4AD1, AD2	21	82.6		32	22.2	M8x1	25.1	46.7		
MS4AD3, AD4	21	82.0	_	32	32.3	M12x1	35.1	55.8		
MS4AD7, AD8, AD9, AD10	21	59.1	_	~32	16	M8x1	-	ı		
MS6										
MS6AD1, AD2	21	102		51	22.2	M8x1	25.1	46.7		
MS6AD3, AD4	31	31	31 103	103	103 –	21	32.3	M12x1	35.1	55.8
MS6AD7, AD8, AD9, AD10	31	79.1	-	~51	16	M8x1	-	-		

Ordering data

Size	Connection	Supply voltage	Flow direction	Part no.	Туре
MS4	G1/4	24 V DC	From left to right	542558	MS4-DE-1/4-10V24
		110 V AC	From left to right	529519	MS4-DE-1/4-V110
		230 V AC	From left to right	529521	MS4-DE-1/4-V230
MS6	G1/4	24 V DC	From left to right	542564	MS6-DE-1/4-10V24
	G3/8	24 V DC	From left to right	542566	MS6-DE-3/8-10V24
	G1/2	24 V DC	From left to right	542562	MS6-DE-1/2-10V24
		110 V AC	From left to right	529799	MS6-DE-1/2-V110
		230 V AC	From left to right	529801	MS6-DE-1/2-V230

Soft-start valves MS4/MS6-DE, MS series

Ordering data – Modular product system

Ordering table					
Grid dimension	[mm] 40	62	Conditions	Code	Enter code
Module no.	527713	527686			
Series	Standard			MS	MS
Size	4	6			
Function	Soft-start valve, electric	·		-DE	-DE
Pneumatic connection	Female thread G1/8	-	[1]	-1/8	
	Female thread G1/4	Female thread G1/4	[1]	-1/4	
	-	Female thread G3/8	[1]	-3/8	
	-	Female thread G1/2	[1]	-1/2	
	Connecting plate G1/8	-		-AGA	
	Connecting plate G1/4	Connecting plate G1/4		-AGB	
	Connecting plate G3/8	Connecting plate G3/8		-AGC	İ
	-	Connecting plate G1/2		-AGD	
	-	Connecting plate G3/4		-AGE	
	Connecting plate 1/8 NPT	-	[1]	-AQK	
	Connecting plate 1/4 NPT	Connecting plate 1/4 NPT	[1]	-AQN	
	Connecting plate 3/8 NPT	Connecting plate 3/8 NPT	[1]	-AQP	
	_	Connecting plate 1/2 NPT	[1]	-AQR	
	-	Connecting plate 3/4 NPT	[1]	-AQS	
Supply voltage	24 V DC (plug pattern to EN 175301)			-V24	
	4 14 bar	4 18 bar			
	24 V DC (plug pattern to EN 175301)		[1] [2]	-10V24	
	4 10 bar	4 10 bar			
	24 V DC, M12 to IEC 61076-2-101		[1] [2]	-10V24P	
	4 10 bar	4 10 bar			
	110 V AC (plug pattern to EN 175301)		[1]	-V110	
	4 14 bar	4 18 bar			
	230 V AC (plug pattern to EN 175301)		[1]	-V230	
	4 14 bar	4 18 bar			

[1] 1/8; 1/4; 3/8; 1/2, AQK, AQN, AQP, AQR, AQS, 10V24, 10V24P, V110, V230, AD1 ... AD4, AD7 ... AD10, WPM

Not with EU EX2 certification.

[2] 10V24, 10V24P Max. operating pressure: 10 bar.

Ordering data – Modular product system

Ordering table						
Grid dimension	[mm]	40	62	Conditions	Code	Enter code
Pressure gauge/pressure gauge		None				
alternatives		MS pressure gauge, bar			-AG	
		Adapter for EN pressure gauge 1/8, without pressure gauge	-		-A8	
		Adapter for EN pressure gauge 1/4, without pre	ssure gauge		-A4	
		Integrated pressure gauge, red/green scale			-RG	
		Pressure sensor with LCD display, M8 plug, 1 sv	vitching output PNP, 3-pin	[1] [3]	-AD1	
		Pressure sensor with LCD display, M8 plug, 1 sv	vitching output NPN, 3-pin	[1] [3]	-AD2	
		Pressure sensor with LCD display, plug M12, 1 9 4 20 mA	switching output PNP, 4-pin, analogue output	[1] [3]	-AD3	
		Pressure sensor with LCD display, plug M12, 1 s 4 20 mA	switching output NPN, 4-pin, analogue output	[1] [3]	-AD4	
		Pressure sensor with status indicator, plug M8,	[1] [3]	-AD7		
		Pressure sensor with status indicator, plug M8,	[1] [3]	-AD8		
		Pressure sensor with status indicator, plug M8,	[1] [3]	-AD9		
		Pressure sensor with status indicator, plug M8,	window comparator, PNP, N/C contact	[1] [3]	-AD10	
Alternative pressure gauge scale		None				
		psi		[4]	-PSI	
		MPa		[5]	-MPA	
Type of mounting		Without mounting bracket				
		Mounting bracket standard design		[6]	-WP	
		Mounting bracket for attaching service unit com	ponents	[1] [6]	-WPM	
		Mounting bracket centrally at rear (wall mounting quired	ng top and bottom), connecting plates not re-		-WB	
		Mounting bracket centrally at rear (wall mounting top), connecting plates not required	-		-WBM	
EU certification		None				
		II 3GD to EU Explosion Protection Directive (ATE	X)		-EX2	
UL certification		None				
		cULus, ordinary location for Canada and USA		[7]	-UL1	
Flow direction		Flow direction from left to right				
		Flow direction from right to left			-Z	

[1] 1/8; 1/4; 3/8; 1/2, AQK, AQN, AQP, AQR, AQS, 10V24, 10V24P, V110, V230, AD1 ... AD4, AD7 ... AD10, WPM

Not with EU EX2 certification.

[3] AD1 ... AD4,

Measuring range max. 10 bar.


AD7 ... AD10 PSI

Only in combination with pressure gauge AG. Only in combination with pressure gauge AG or RG.

[5] MPA [6] WP, WPM Only with connecting plate AGA, AGB, AGC, AGD, AGE, AQK, AQN, AQP, AQR or AQS.

[7] UL1 Not with supply voltage V110, V230.

Peripherals overview



Peripherals overview

Moun	Mounting attachments and accessories						
		Order code	→ Page/Internet				
[1]	On/off valve	MS9-EM	61				
Can b	e ordered via the modular product system						
[3]	Mounting bracket ²⁾	[WP]	66				
[4]	Mounting bracket ²⁾	[WPB]					
[5]	Mounting bracket	[WPM]					
[7]	Connecting plate SET ¹⁾	[AG]					
	Connecting plate SET ¹⁾	[AQ]					
[8]	Cover plate	[VS]					
[9]	Adapter for EN pressure gauge 1/4	[A4]					
[13]	MS pressure gauge	[AG], [RG]					
[14]	Silencer	[S]					
Can b	e ordered as accessories						
[2]	Module connector	MS9-MV	ms9-mv				
[3]	Mounting bracket ²⁾	MS9-WP	ms9-wp				
[4]	Mounting bracket ²⁾	MS9-WPB	ms9-wp				
[5]	Mounting bracket	MS9-WPM	ms9-wp				
[6]	Padlock	LRVS-D	103				
[7]	Connecting plate SET	MS9-AG	ms9-ag				
	Connecting plate SET	MS9-AQ	ms9-aq				
[10]	Pressure gauge	MA	103				
[11]	Pressure sensor	SPAUT-R14M	102				
[12]	Connecting cable	NEBU-M8LE4, NEBU-M12LE4	103				
[14]	Silencer	U	103				

¹⁾ Module connector [2] is included in the scope of delivery.

²⁾ The screws for the wall bracket on the reverse side are partially covered by the housing of this service unit component. Depending on the configuration of the service unit combination, the screws will no longer be accessible. The mounting bracket MS9-WPM is therefore recommended for wall mounting. It can be used to attach a fully assembled combination to the pre-mounted wall bracket.

On/off valves MS9-EM, MS series

Type codes

001	Series			
MS	MS series			
002	Size			
9	Grid dimension 90 mm			
003	Function			
EM	On/off valve, manual			
004	Pneumatic connection			
3/4	Female thread G3/4			
1	Female thread G1			
AGD	Sub-base G1/2			
AGE	Sub-base G3/4			
AGF	Sub-base G1			
AGG	Connecting plate G1 1/4			
AGH	Connecting plate G1 1/2			
N3/4	Female thread 3/4 NPT			
N1	Female thread 1 NPT			
AQR	Sub-base 1/2 NPT			
AQS	Sub-base 3/4 NPT			
AQT	Sub-base 1 NPT			
AQU	Sub-base 1 1/4 NPT			
AQV	Sub-base 1 1/2 NPT			
G	Module without connecting thread, without sub-base			
NG	Module without connecting thread, without sub-base (inch)			
005	Silencer			
	None			
S	Silencer			

006	Pressure gauge alternatives	
	None	
AG	MS pressure gauge	
VS	Cover plate	
A8	Adapter for EN pressure gauge 1/8, without pressure gauge	
A4	Adapter for EN pressure gauge 1/4, without pressure gauge	
RG	Integrated pressure gauge, red/green scale	
AD7	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/O	
AD8	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C	
AD9	Pressure sensor with switching display, M8 plug, window comparator, PNP, N/O	
AD10	Pressure sensor with operational status indicator, M8 plug, window comparator, PNP, N/C	
007	Alternative pressure gauge scale	
	MS pressure gauge	
PSI	psi	
BAR	bar	
MPA	MPa	
008	Valve function	
	Standard	
2	2/2-way valve	
009	Type of mounting	
	Without mounting bracket	
WP	Mounting bracket basic design	
WPB	Mounting bracket for large wall gap	
WPM	Mounting bracket for hooking in service unit components	
010	UL certification	
	None	
UL1	cULus ordinary location for Canada and USA	
011	Flow direction	
	Flow direction from left to right	

Flow direction from right to left

2/2-way valve, bistable



3/12-way valve, bistable



 Manually actuated on/off valve for pressurising and exhausting pneumatic systems

• Ducted exhaust possible via a threaded connection with silencer

Flow rate 8000 ... 18000 l/min

Temperature range −10 ... +60°C

Operating pressure0 ... 20 bar



• The switching position is immediately recognisable

Actuator secured by locking the rotary knob



• Optional pressure gauge

• Optional pressure sensor



 Optional device variant EX4 for use in potentially explosive areas in zones 1, 2, 21 and 22

General technical data

Pneumatic connection 1,	2		
Female thread		G3/4, G1, 3/4 NPT or 1 NPT	
Connecting plate	[AG]	G1/2, G3/4, G1, G1 1/4 or G1 1/2	
	[AQ]	1/2 NPT, 3/4 NPT, 1 NPT, 1 1/4 NPT or 1 1/2 NPT	
Module without	[G], [NG]	-	
connecting			
thread/connecting			
plate			
Pneumatic connection 3			
Pneumatic con-	[3/4], [1],	G1	
nection 1, 2	[AG], [G]		
	[N3/4], [N1], [AQ],	G1 with silencer [S]	
	[NG]	1 NPT without silencer [S]	
Design		Piston spool	
Type of mounting		With accessories	
		In-line installation	
Mounting position		Any ¹⁾	
Actuator lock		Rotary knob with latch	
Display pressure		Via pressure sensor for indicating the output pressure and electrical output via status indicator	
		Via pressure gauge for displaying the output pressure	
		Via pressure gauge with red/green scale for indicating the output pressure	
		Prepared for G1/4	
Valve function		2/2-way valve, bistable	
		3/2-way valve, bistable	
Exhaust air function		Cannot be throttled	
Reset method		Force-pilot operated	
Type of control		Direct	
Sealing principle		Soft	

 $^{1) \}quad \text{The on/off valve must be mounted vertically when combined with a pressure sensor as condensate must not collect in the pressure sensor.} \\$

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Characteristic flow rate values								
Pneumatic connection 1, 2	Female thread	Female thread		Connecting plate				None
	[3/4], [N3/4]	[1], [N1]	[AGD], [AQR]	[AGE], [AQS]	[AGF], [AQT]	[AGG], [AQU]	[AGH], [AQV]	[G], [NG]
Standard nominal flow rate qnN1) [l/m	nin]							
In main flow direction 1 → 2	14500	18000	8000	14000	18000	18000	18000	18000
In relief direction 2 → 3	14900	14100	16500	14400	13800	13200	13200	14100
C value [l/s*min]								
In main flow direction 1 → 2	59.59	76.90	32.75	57.50	75.65	75.51	75.17	-
In relief direction 2 → 3	55.11	53.54	56.22	54.07	52.73	51.06	51.36	-
b value	<u> </u>		<u> </u>	<u> </u>	<u> </u>	<u> </u>	<u> </u>	<u> </u>
In main flow direction 1 → 2	0.41	0.37	0.45	0.39	0.38	0.39	0.38	-
In relief direction 2 → 3	0.50	0.48	0.60	0.49	0.47	0.45	0.44	_

¹⁾ Measured at p1 = 6 bar and p2 = 5 bar, $\Delta p = 1$ bar.

Operating and environmental con	Operating and environmental conditions					
		Without pressure sensor	Pressure sensor			
Operating pressure	[bar]	0 20	010			
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]				
Note on the operating/pilot mediu	m	Lubricated operation possible (in which case lubricated operation will	l always be required)			
Ambient temperature	[°C]	-10 +60	0+50			
Temperature of medium	[°C]	-10 +60	0+50			
Corrosion resistance class CRC ¹⁾		2				
Noise level	[dB (A)]	93 ²⁾ with silencer				
UL certification ³⁾		c UL us - Recognized (OL)				

¹⁾ Corrosion resistance class CRC 2 to Festo standard FN 940070 Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

³⁾ Additional information: www.festo.com/catalogue/ms \rightarrow Support/Downloads.

ATEX	
EU certification	[EX4]
ATEX category for gas	II 2G
Type of ignition protection for gas	Ex h IIC T6 Gb X
ATEX category for dust	2D
Type of ignition protection for dust	Ex h IIIC T60°C Db X
Explosion-proof ambient temperature	-10°C≤Ta≤+60°C
CE marking (see declaration of conformity) ¹⁾	To EU Explosion Protection Directive (ATEX)

 $^{1) \}quad \text{Additional information: www.festo.com/catalogue/ms} \, {\color{red} \rightarrow} \, \text{Support/Downloads}.$

Weight [g]	
On/off valve	2200
On/off valve with silencer	2400


²⁾ Exhaust at 10 bar at a distance of 1 m.

Download CAD data → www.festo.com

Datasheet

Materials

Sectional view



On/of	On/off valve					
[1]	Housing	Die-cast aluminium				
[2]	Piston spool	POM				
-	Seals	NBR				
Note	on materials	RoHS-compliant				


Dimensions – Basic version

[G], [NG] Module without connecting thread, without connecting plate

[VS] Cover plate

[] 3/2-way valve


[2] 2/2-way valve





Silencer

[S]




→ Flow direction


Туре	B1	B2	В3	D5	L1	L2	L3	L	6
								[S]	[S]+[EX4]
MS9-EM-G, NG-VS	90	4.5	109	C1	242	159	23	189	138
MS9-EM-G, NG-VS-2	90	45	109	G1	242	159	30	-	-

Dimensions – Female thread/connecting plate

[3/4], [1], [N3/4], [N1] Female thread



[1] Retaining screw M6xmin. 90 to DIN 912 (not included in the scope of delivery) for wall mounting without mounting bracket




Туре	В4	B5	B6	В	7	В8	D1	D6	D7	L4	L7	T1	= ©
					[EX4]						[EX4]		
MS9-EM-3/4	90	104	91.5				G3/4	11	6.5	66		6	
MS9-EM-1	90	104	91.5	_	_	_	G1	11	0.5	00	_	0	_
MS9-EM-AGD						132	G1/2						30
MS9-EM-AGE						132	G3/4						36
MS9-EM-AGF	-	_	-	112	122	142	G1	-	-	-	35	-	41
MS9-EM-AGG						162	G1 1/4						50
MS9-EM-AGH						176	G1 1/2						55
MS9-EM-N3/4	00	107	01.5				3/4 NPT	11	(5			,	
MS9-EM-N1	90	104	91.5	_	_	_	1 NPT	11	6.5	66	_	6	_
MS9-EM-AQR						132	1/2 NPT						30
MS9-EM-AQS						132	3/4 NPT						36
MS9-EM-AQT	-	_	_	112	_	142	1 NPT	-	_	_	_	_	41
MS9-EM-AQU						162	1 1/4 NPT	1					50
MS9-EM-AQV						176	1 1/2 NPT						55

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions - Pressure gauges/adapters


[AG] Integrated MS pressure gauge with standard scale

[RG] Integrated MS pressure gauge with red/green scale



Download CAD data → www.festo.com


[A4] Adapter for EN pressure gauge 1/4, without pressure gauge



Туре	B2	B3	B9	D2
MS9-EMAG, RG	4.5	109	-	-
MS9-EMA4	45	-	110	G1/4

Dimensions - Pressure sensor

[AD7], [AD8], [AD9], [AD10] Pressure sensor with status indicator



[AD7]:

SDE5-D10-O-...-P-M8 with 3-pin plug M8x1, threshold value comparator, 1 switching output PNP, N/O contact

[AD8]:

SDE5-D10-C-...-P-M8 with 3-pin plug M8x1, threshold value comparator, 1 switching output PNP, N/C contact

Download CAD data → www.festo.com

Datasheets → Internet: sde5

[AD9]:

SDE5-D10-O3-...-P-M8 with 3-pin plug M8x1, window comparator, 1 switching output PNP, N/O contact

[AD10]:

SDE5-D10-C3-...-P-M8 with 3-pin plug M8x1, window comparator, 1 switching output PNP, N/C contact

Туре	B2	B11	D4
MS9-EMAD7, AD8, AD9, AD10	45	112	M8

Ordering data

3/2-way valve, silence	r, cover plate				
Size	Connection 1, 2	Connection 3	Flow direction	Part no.	Туре
MS9	Without connecting	G thread	From left to right	562952	MS9-EM-G-S-VS
	thread	G thread	From left to right	562954	MS9-EM-NG-S-VS

Ordering data – Modular product system

Ordering table				
Grid dimension [m	m] 90	Conditions	Code	Enter
				code
Module no.	562178			
Series	Standard		MS	MS
Size	9		9	9
-unction	On/off valve, manual		-EM	-EM
Pneumatic connection	Female thread G3/4	[1]	-3/4	
	Female thread G1	[1]	-1	
	Connecting plate G1/2		-AGD	
	Connecting plate G3/4		-AGE	
	Connecting plate G1		-AGF	
	Connecting plate G1 1/4		-AGG	
	Connecting plate G1 1/2		-AGH	
	Female thread 3/4 NPT	[1]	-N3/4	
	Female thread 1 NPT	[1]	-N1	
	Connecting plate 1/2 NPT	[1]	-AQR	
	Connecting plate 1/2 M P	[1]	-AQS	
	Connecting plate 3/4 NPT	[1]	-AQ3	
	Connecting plate 1 1/4 NPT	[1]	-AQU	
	Connecting plate 1 1/4 MT	[1]	-AQV	
	Module without connecting thread, without connecting plate	[1]	-AQV	
	Module without connecting thread, without connecting plate (connection 3 in NPT)	[1]	-NG	
Potony knob solour		[1]	-NO	
Rotary knob colour	Standard (black/blue) Red		-R	
Cilanan			-K	
Silencer	None		-	
D	Silencer		-S	-
Pressure gauge/adapter	MS pressure gauge, bar		-AG	
	Cover plate		-VS	
	Adapter for EN pressure gauge 1/4, without pressure gauge	(-)	-A4	
	Integrated pressure gauge, red/green scale	[2]	-RG	
	Pressure sensor with status indicator, plug M8, threshold value comparator, PNP, N/O contact	[1] [3]	-AD7	
	Pressure sensor with status indicator, plug M8, threshold value comparator, PNP, N/C contact	[1] [3]	-AD8	
	Pressure sensor with status indicator, plug M8, window comparator, PNP, N/O contact	[1] [3]	-AD9	
	Pressure sensor with status indicator, plug M8, window comparator, PNP, N/C contact	[1] [3]	-AD10	
Alternative pressure gauge scale	None	[4]		
	psi	[5]	-PSI	
	MPa	[5]	-MPA	
	bar	[5]	-BAR	
Valve function	Standard (3/2-way valve)			
	2/2-way valve	[6]	-2	
Type of mounting	Without mounting bracket			
	Mounting bracket standard design	[7]	-WP	
	Mounting bracket for attaching service unit components	[1] [7]	-WPM	
	Mounting bracket for large wall gap	[7]	-WPB	
U certification	None			
	II 2GD to EU Explosion Protection Directive (ATEX)		-EX4	
JL certification	None			
	cULus, ordinary location for Canada and USA		-UL1	
Flow direction	Flow direction from left to right			
	Flow direction from right to left		-Z	

```
      [1]
      3/4; 1, N3/4, N1,
      Not with EU EX4 certification.

      AQR, AQS, AQT,
      AQU, AQV, G, NG,
      ADT ... AD10,

      WPM
      WPM

      [2]
      RG
      Not with alternative pressure gauge scale PSI, PSI scale serves only as an auxiliary scale.

      [3]
      AD7 ... AD10
      Measuring range max. 10 bar.


      [4]
      -
      Not with pressure gauge AG, RG.

      [5]
      PSI, MPA, BAR
      Not with adapter VS, A4, AD7, AD8, AD9, AD10.

      [6]
      2
      Not with silencer S.

      [7]
      WP, WPM, WPB
      Not with pneumatic connection G, NG.
```

Peripherals overview






Additional accessories:

- Module connector for combination with size MS6, MS9 or MS12
 - → Internet: rmv, armv

Peripherals overview

Supply voltage V24, V110, V230 Supply voltage V24P



Mour	ting attachments and accessories		
		Order code	→ Page/Internet
[1]	On/off valve	MS9-EE	71
Can b	e ordered via the modular product system		
[3]	Mounting bracket ²⁾	[WP]	76
[4]	Mounting bracket ²⁾	[WPB]	
[5]	Mounting bracket	[WPM]	
[6]	Connecting plate SET ¹⁾	[AG]	
	Connecting plate SET ¹⁾	[AQ]	
[8]	Adapter for EN pressure gauge 1/4	[A4]	
[7]	Cover plate	[VS]	
[12]	Pressure sensor SDE5 with status indicator	[AD7]	
[14]	MS pressure gauge	[AG], [RG]	
[15]	Silencer	[S]	
Can b	e ordered as accessories		
[2]	Module connector	MS9-MV	ms9-mv
[3]	Mounting bracket ²⁾	MS9-WP	ms9-wp
[4]	Mounting bracket ²⁾	MS9-WPB	ms9-wp
[5]	Mounting bracket	MS9-WPM	ms9-wp
[6]	Connecting plate SET	MS9-AG	ms9-ag
	Connecting plate SET	MS9-AQ	ms9-aq
[9]	Pressure gauge	MA	103
[10]	Pressure sensor	SPAUT-R14M	102
[11]	Connecting cable	NEBU-M8LE4, NEBU-M12LE4	103
[13]	Connecting cable	NEBU-M8LE3	103
[15]	Silencer	U	103
[16]	Illuminating seal	MC-LD	102
[17]	Connecting cable	KMC	102
[18]	Plug socket	MSSD-C	102
[19]	Connecting cable	NEBU-M12G5	103
[20]	Connecting cable	NEBU-M12W5	103
[21]	Sensor socket	SIE-GD	103
[22]	Angled plug socket	SIE-WD	103

 $^{1) \}qquad \hbox{Module connector [2] is included in the scope of delivery.}$

²⁾ The screws for the wall bracket on the reverse side are partially covered by the housing of this service unit component. Depending on the configuration of the service unit combination, the screws will no longer be accessible. The mounting bracket MS9-WPM is therefore recommended for wall mounting. It can be used to attach a fully assembled combination to the pre-mounted wall bracket.

On/off valves MS9-EE, MS series


Type codes

001	Series	
MS	MS series	
002	Size	
9	Grid dimension 90 mm	
003	Function	
EE	On/off valve, electric	
004	Pneumatic connection	
3/4	Female thread G3/4	
1	Female thread G1	
AGD	Sub-base G1/2	
AGE	Sub-base G3/4	
AGF	Sub-base G1	
AGG	Connecting plate G1 1/4	
AGH	Connecting plate G1 1/2	
N3/4	Female thread 3/4 NPT	
N1	Female thread 1 NPT	
AQR	Sub-base 1/2 NPT	
AQS	Sub-base 3/4 NPT	
AQT	Sub-base 1 NPT	
AQU	Sub-base 1 1/4 NPT	
AQV	Sub-base 1 1/2 NPT	
G	Module without connecting thread, without sub-base	
NG	Module without connecting thread, without sub-base (inch)	
005	Supply voltage	
V110	110 V AC (connection pattern to EN 175301)	
V24	24 V DC (connection pattern to EN 175301)	
V230	230 V AC (connection pattern to EN 175301)	
V24P	24 V DC plug (connection pattern M12 to DESINA)	
006	Silencer	
	None	
S	Silencer	


007	Pressure gauge alternatives	
	None	
AG	MS pressure gauge	
VS	Cover plate	
A8	Adapter for EN pressure gauge 1/8, without pressure gauge	
A4	Adapter for EN pressure gauge 1/4, without pressure gauge	
RG	Integrated pressure gauge, red/green scale	
AD7	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/O	
008	Alternative pressure gauge scale	
	MS pressure gauge	
PSI	psi	
BAR	bar	
MPA	MPa	
009	Valve function	
	Standard	
2	2/2-way valve	
010	Type of mounting	
	Without mounting bracket	
WP	Mounting bracket basic design	
WPB	Mounting bracket for large wall gap	
WPM	Mounting bracket for hooking in service unit components	
011	EU certification	
	None	
EX2	II 3GD	
012	UL certification	
	None	_
UL1	cULus ordinary location for Canada and USA	
013	Flow direction	
	Flow direction from left to right	


Flow direction from right to left

2/2-way valve, closed, single solenoid




3/2-way valve, closed, single solenoid











- Electrically actuated on/off valve for pressurising and exhausting pneumatic systems
- Ducted exhaust possible via a threaded connection with silencer



- With solenoid coil, without plug socket
- Choice of three voltage ranges
- Detenting and non-detenting manual override
- Optional pressure gauge
- Optional device variant EX2 for use in potentially explosive areas in zones 2 and 22 (plug socket MSSD-C-24V-EX included in scope of delivery)

General technical data		
Pneumatic connection 1	, 2	
Female thread		G3/4, G1, 3/4 NPT or 1 NPT
Connecting plate	[AG]	G1/2, G3/4, G1, G1 1/4 or G1 1/2
	[AQ]	1/2 NPT, 3/4 NPT, 1 NPT, 1 1/4 NPT or 1 1/2 NPT
Module without	[G, NG]	-
connecting		
thread/connecting plate		
Pneumatic connection 3		
Pneumatic con- nection 1, 2	[3/4], [1]/ [AG], [G]	G1
	[N3/4], [N1], [AQ], [NG]	G1 with silencer [S]
	[N3/4], [N1], [AQ]]	1 NPT without silencer [S]
Design		Piston spool
Type of mounting		With accessories
		In-line installation
Mounting position		Any
Display pressure		Via pressure sensor for indicating the output pressure and electrical output via status indicator
		Via pressure gauge for displaying the output pressure
		Via pressure gauge with red/green scale for indicating the output pressure
		Prepared for G1/4
Valve function		2/2-way valve, closed, single solenoid
		3/2-way valve, closed, single solenoid
Exhaust air function		Cannot be throttled
Manual override		Non-detenting/detenting
Reset method	,	Mechanical spring
Type of control		Piloted
Pilot air supply		Internal
Sealing principle		Soft

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Electrical data

Characteristic coil dat	a	
With supply	[V24], [V24P]	24 V DC: 4.5 W, permissible voltage fluctuations ±10%
voltage	[V110]	110 V AC: 50 Hz, pick-up power 11.5 W, holding power 8.9 W, permissible voltage fluctuations ±10%
		110 V AC: 60 Hz, pick-up power 9.5 W, holding power 6.2 W, permissible voltage fluctuations ±10%
	[V230]	230 V AC: 50 Hz, pick-up power 11.5 W, holding power 9.1 W, permissible voltage fluctuations ±10%
		230 V AC: 60 Hz, pick-up power 9.5 W, holding power 6.4 W, permissible voltage fluctuations ±10%
Electrical connection		
With supply	[V24], [V110],	Plug, square design to EN 175301-803, type A
voltage	[V230]	
	[V24P]	Plug M12, 4-pin to DESINA
Degree of protect	tion for solenoid coil	IP65
Duty cycle	[%]	100

Characteristic flow rate values								
Pneumatic connection	Female thread		Connecting p	late				None
	G3/4/3/4 NPT	G1/1 NPT	AGD/AQR	AGE/AQS	AGF/AQT	AGG/AQU	AGH/AQV	G, NG
Standard nominal flow rate qnN ¹⁾ [l/m	nin]							
In main flow direction 1 → 2	14500	18000	8000	14000	18000	18000	18000	18000
In relief direction 2 → 3	14900	14100	16500	14400	13800	13200	13200	14100
C value [l/s*min]								
In main flow direction 1 → 2	59.59	76.90	32.75	57.50	75.65	75.51	75.17	-
In relief direction 2 → 3	55.11	53.54	56.22	54.07	52.73	51.06	51.36	-
b value								
In main flow direction 1 → 2	0.41	0.37	0.45	0.39	0.38	0.39	0.38	-
In relief direction 2 → 3	0.50	0.48	0.60	0.49	0.47	0.45	0.44	-

¹⁾ Measured at p1 = 6 bar and p2 = 5 bar, $\Delta p = 1$ bar.

Operating and environmental conditions			
Operating pressure	[bar]	3.5 16	
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/		Lubricated operation possible (in which case lubricated operation will always be required)	
pilot medium			
Ambient temperature	[°C]	-10 +60	
Temperature of medium	[°C]	-10 +60	
Corrosion resistance class CRC ¹⁾		2	
Noise level	[dB (A)]	93 ²⁾ with silencer	
UL certification ³⁾		c UL us - Recognized (OL)	

¹⁾ Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

³⁾ Additional information: www.festo.com/catalogue/ms → Support/Downloads.

ATEX	
EU certification	EX2
ATEX category for gas	II 3G
Type of (ignition) protection for gas	Ex nA IIC T5 X Gc
ATEX category for dust	II 3D
Type of (ignition) protection for dust	Ex tc IIICT85°CX Dc IP65
Explosion-proof ambient temperature	-10°C ≤ Ta ≤ +50°C
CE marking (see declaration of conformity) ¹⁾	To EU Explosion Protection Directive (ATEX)


¹⁾ Additional information: www.festo.com/catalogue/ms \rightarrow Support/Downloads.

²⁾ Exhaust at 10 bar at a distance of 1 m.


Weight [g]	
On/off valve	2100
On/off valve with silencer S	2300

Materials

Sectional view



On/off valve				
[1]	Housing	Die-cast aluminium		
[2]	Piston spool	POM		
-	Seals	NBR		
Note o	n materials	RoHS-compliant		



109

M12x1

MS9-EE-G, NG-V24, V110, V230

MS9-EE-G, NG-V24P

161

G1

2/2-way valve 3/2-way valve

23

30

36

39


12

10

189


Dimensions – Female thread/connecting plate

[3/4], [1], [N3/4], [N1] Female thread



Flow direction

[1] Retaining screw M6xmin. 90 to DIN 912 (not included in the scope of delivery) for wall mounting without mounting bracket




Туре	В4	B5	В6	В	7	В8	D1	D6	D7	L6	L7	T1	=©
					EX2						EX2		
MS9-EE-3/4	90	104	91.5				G3/4	11	6.5	66			
MS9-EE-1	90	104	91.5	_	_	_	G1] 11	0.5	00	_	6	_
MS9-EE-AGD						132	G1/2						30
MS9-EE-AGE						132	G3/4						36
MS9-EE-AGF	_	-	_	112	122	142	G1] –	-	-	35	_	41
MS9-EE-AGG						162	G1 1/4						50
MS9-EE-AGH						176	G1 1/2						55
MS9-EE-N3/4	90	104	91.5	_	_	_	3/4 NPT	11	6.5	66	_	6	
MS9-EE-N1	90	104	91.5	_	_	_	1 NPT	111	0.5	66	_		-
MS9-EE-AQR						132	1/2 NPT						30
MS9-EE-AQS						132	3/4 NPT]					36
MS9-EE-AQT	_	_	_	112	_	142	1 NPT] -	-	-	_	_	41
MS9-EE-AQU						162	1 1/4 NPT]					50
MS9-EE-AQV						176	1 1/2 NPT]					55

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions - Pressure gauge/pressure gauge alternatives


[AG] Integrated MS pressure gauge with standard scale

[RG] Integrated MS pressure gauge with red/green scale



Download CAD data → www.festo.com

[A4] Adapter for EN pressure gauge 1/4, without pressure gauge




Туре	B2	В3	В9	D3
MS9-EEAG, RG		109	-	-
MS9-EEA4	45	-	110	G1/4

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions – Pressure gauge/pressure gauge alternatives

[AD7] Pressure sensor with status indicator



[AD7]:

SDE5-D10-O-...-P-M8 with 3-pin plug M8x1, threshold value comparator, 1 switching output PNP, N/O contact

Flow direction

Download CAD data → www.festo.com

Туре	B2	B11	D4
MS9-EEAD7	45	112	M8x1

Ordering data					
3/2-way valve, with silencer, supply voltage 24	V DC				
Size Part no. Type					
Cover plate					
MS9	562940	MS9-EE-G-V24-S-VS			
Pneumatic connection 3 in NPT, cover plate					
MS9	562946	MS9-EE-NG-V24-S-VS			

On/off valves MS9-EE, MS series

Ordering data – Modular product system

Ordering table				
Grid dimension [mm]	90	Conditions	Code	Enter
				code
Module no.	562177			
Series	Standard		MS	MS
ize	9		9	9
unction	On/off valve, electric		-EE	-EE
neumatic connection	Female thread G3/4	[1]	-3/4	
	Female thread G1	[1]	-1	
	Connecting plate G1/2		-AGD	
	Connecting plate G3/4		-AGE	
	Connecting plate G1		-AGF	
	Connecting plate G1 1/4		-AGG	
	Connecting plate G1 1/2		-AGH	
	Female thread 3/4 NPT	[1]	-N3/4	
	Female thread 1 NPT	[1]	-N1	
	Connecting plate 1/2 NPT	[1]	-AQR	
	Connecting plate 3/4 NPT	[1]	-AQS	
	Connecting plate 1 NPT	[1]	-AQT	
	Connecting plate 1 1/4 NPT	[1]	-AQU	
	Connecting plate 1 1/2 NPT	[1]	-AQV	
	Module without connecting thread, without connecting plate	[1]	-G	
	Module without connecting thread, without connecting plate (connection 3 in NPT)	[1]	-NG	
upply voltage	24 V DC (plug pattern to EN 175301), 16 bar		-V24	
	24 V DC plug (plug pattern M12 to DESINA), 16 bar	[1]	-V24P	
	110 V AC (plug pattern to EN 175301), 16 bar	[1]	-V110	
	230 V AC (plug pattern to EN 175301), 16 bar	[1]	-V230	

^{[1] 3/4; 1,} N3/4, N1, Not with EU EX2 certification.

AQR, AQS, AQT, AQU, AQV, G, NG,

V24P, V110,

V230,

V230, AD7,

WPM

Ordering data – Modular product system

Ordering table Grid dimension [mm]	90	Conditions	Code	Enter
Silencer	Silencer		-S	code
Pressure gauge/pressure gauge	MS pressure gauge, bar		-AG	
alternatives	Cover plate		-VS	
	Adapter for EN pressure gauge 1/4, without pressure gauge		-A4	
	Integrated pressure gauge, red/green scale	[2]	-RG	
	Pressure sensor with status indicator, plug M8, threshold value comparator, PNP, N/O contact	[1] [3]	-AD7	
Alternative pressure gauge scale	psi	[4]	-PSI	
	MPa	[4]	-MPA	
	bar	[4]	-BAR	
Valve function	Standard (3/2-way valve)		-	
	2/2-way valve	[5]	-2	
Type of mounting	Mounting bracket standard design	[6]	-WP	
	Mounting bracket for attaching service unit components	[1] [6]	-WPM	
	Mounting bracket for large wall gap	[6]	-WPB	
EU certification	II 3GD to EU Explosion Protection Directive (ATEX)		-EX2	
UL certification	cULus, ordinary location for Canada and USA	[7]	-UL1	
Flow direction	Flow direction from right to left		-Z	

[1] 3/4; 1, N3/4, N1, Not with EU EX2 certification. AQR, AQS, AQT,

AQU, AQV, G, NG, V24P, V110, V230, AD7, WPM


[2] RG Not with alternative pressure gauge scale PSI, PSI scale serves only as an auxiliary scale.

[3] [4] [5] [6] [7] AD7 Measuring range max. 10 bar. PSI, MPA, BAR Not with adapter VS, A4, AD7. Not with silencer S.

WP, WPM, WPB Not with pneumatic connection G, NG. UL1 Not with supply voltage V110, V230.

Peripherals overview

On/off valve MS12-EM



Moun	ting attachments and accessories		
		Order code	→ Page/Internet
[1]	On/off valve	MS12-EM	80
Can b	e ordered via the modular product system		
[3]	Mounting bracket	[WP]	83
[5]	Connecting plate SET ¹⁾	[AG]	
[6]	Adapter for EN pressure gauge 1/4	[A4]	
[10]	MS pressure gauge	[AG]	
[11]	Silencer	[S]	
Can b	e ordered as accessories		
[2]	Padlock	LRVS-D	103
[3]	Mounting bracket	MS12-WP	ms12-wp
[4]	Module connector	MS12-MV	ms12-mv
[5]	Connecting plate SET	MS12-AG	ms12-ag
[7]	Pressure gauge	MA	103
[8]	Pressure sensor	SPAUT-R14M	102
[9]	Connecting cable	NEBU-M8LE4, NEBU-M12LE4	103
[11]	Silencer	U	103

¹⁾ Module connector [4] is included in the scope of delivery.

Type codes


001	Series	
MS	MS series	
002	Size	
12	Grid dimension 124 mm	
003	Function	
EM	On/off valve, manual	
004	Pneumatic connection	
AGF	Sub-base G1	
AGG	Connecting plate G1 1/4	
AGH	Connecting plate G1 1/2	
AGI	Sub-base G2	
	And the following of the first of the first	
G	Module without connecting thread, without sub-base	
G	Silencer	

006	Pressure gauge alternatives	
	None	
AG	MS pressure gauge	
A4	Adapter for EN pressure gauge 1/4, without pressure gauge	
007	Alternative pressure gauge scale	
	MS pressure gauge	
PSI	psi	
MPA	MPa	
008	Type of mounting	
	Without mounting bracket	
WP	Mounting bracket basic design	
009	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	

On/off valves MS12-EM, MS series

Datasheet

Function:



Flow rate 25000 ... 32000 l/min

Temperature range -10 ... +60°C

Operating pressure 0 ... 20 bar

- www.festo.com



- Manually actuated on/off valve for pressurising and exhausting pneumatic systems
- Ducted exhaust possible via a threaded connection with silencer
- The switching position is immediately recognisable
- Actuator secured by locking the rotary knob
- Commercially available padlock can be used for security

General technical data		
Pneumatic connection 1, 2		
Connecting plate	[AG]	G1, G1 1/4, G1 1/2 or G2
Module without connecting thread/connecting plate	[G]	-
Pneumatic connection 3		G1
Design		Piston spool
Type of mounting		With accessories
		In-line installation
Mounting position		Any
Valve function		3/2-way valve, bistable
Exhaust air function		Cannot be throttled
Switching position indication		Knob actuator direction = flow direction
Type of control		Direct
Flow direction		Not reversible

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Standard nominal flow rate qnN ¹⁾ [l/min]	
In main flow direction 1 → 2	25000 32000
In relief direction 2 → 3	13000

¹⁾ Measured at p1 = 6 bar and $\Delta p = 1$ bar.


Operating and environmental	Operating and environmental conditions	
Operating pressure	[bar]	020
Operating medium		Compressed air to ISO 8573-1:2010 [-:-:-]
Ambient temperature	[°C]	-10 +60
Temperature of medium	[°C]	-10 +60
Corrosion resistance class	CRC ¹⁾	2

¹⁾ Corrosion resistance class CRC 2 to Festo standard FN 940070 Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

Weight [g]	
On/off valve	3900
On/off valve with silencer S	4000

Materials


Sectional view




On/o	ffvalve	
[1]	Housing	Die-cast aluminium
[2]	Top cover	Aluminium
[3]	Bottom cover	Aluminium
[4]	Valve tappet	Stainless steel, POM, NBR
_	Springs	Steel
_	Covers/cover plates	PA
-	Seals	NBR
-	Connecting plate, module connector, mounting bracket	Die-cast aluminium
Note	on materials	Free of copper and PTFE (not with variant AG)

Dimensions - Basic version

Module without connecting thread, without connecting plate G, with cover plate






Download CAD data → www.festo.com

Flow direction

Туре	B1	B2	В3	B4	L1	L2	L3	D5
MS12-EM-G	124	122	61	148	255	148	228	G1

Dimensions - Silencer

Download CAD data → www.festo.com





Туре	D2 Ø	L4
MS12-EMS	47.8	165.5


Dimensions - Pressure gauge/pressure gauge alternatives


Download CAD data → www.festo.com

[AG] Integrated MS pressure gauge with standard scale, display unit [bar]









Туре	В3	B4	D4
MS12-EMAG	61	148	-
MS12-EMA4	61	148	G1/4

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Ordering data		
Size	Part no.	Туре
MS12	541495	MS12-EM-G

Ordering data – Modular product system


Ordering table				
Grid dimension [mm]	124	Conditions	Code	Enter code
Module no.	535031			
Series	Standard		MS	MS
Size	12		12	12
Function	On/off valve, manual		-EM	-EM
Pneumatic connection	Connecting plate G1		-AGF	
	Connecting plate G1 1/4		-AGG	
	Connecting plate G1 1/2		-AGH	
	Connecting plate G2		-AGI	
	Module without connecting thread, without connecting plate		-G	
Silencer	Silencer		-S	
Pressure gauge/pressure gauge	MS pressure gauge, bar		-AG	
alternatives	Adapter for EN pressure gauge 1/4, without pressure gauge		-A4	
Alternative pressure gauge scale	psi	[1]	-PSI	
	MPa	[1]	-MPA	
Type of mounting	Mounting bracket standard design	[2]	-WP	
Flow direction	Flow direction from right to left		-Z	

Only with pressure gauge AG

^[1] PSI, MPA [2] WP Only with connecting plate AGF, AGG, AGH or AGI.

Peripherals overview

On/off valve MS12-EE



Moun	ting attachments and accessories		
Wiouii	ting attachments and accessories	Order code	→ Page/Internet
[1]	On/off valve	MS12-EE	86
Can b	e ordered via the modular product system		
[6]	Mounting bracket	[WP]	89
[8]	Connecting plate SET ¹⁾	[AG]	
[9]	Adapter for EN pressure gauge 1/4	[A4]	
[13]	MS pressure gauge	[AG]	
[14]	Silencer	[S]	
Can b	e ordered as accessories		
[2]	Connecting cable	NEBU-M12LE4	103
[3]	Illuminating seal	MC-LD	102
[4]	Connecting cable	KMC	102
[5]	Plug socket	MSSD-C	102
[6]	Mounting bracket	MS12-WP	ms12-wp
[7]	Module connector	MS12-MV	ms12-mv
[8]	Connecting plate SET	MS12-AG	ms12-ag
[10]	Pressure gauge	MA	103
[11]	Pressure sensor	SPAUT-R14M	102
[12]	Connecting cable	NEBU-M8LE4, NEBU-M12LE4	103
[14]	Silencer	U	103


¹⁾ Module connector [7] is included in the scope of delivery.

Type codes

001	Series	
MS	MS series	
002	Size	
12	Grid dimension 124 mm	
003	Function	
EE	On/off valve, electric	
004	Pneumatic connection	
AGF	Sub-base G1	
AGG	Connecting plate G1 1/4	
AGH	Connecting plate G1 1/2	
AGI	Sub-base G2	
G	Module without connecting thread, without sub-base	
005	Supply voltage	
V110		
1	110 V AC (connection pattern to EN 175301)	
V230	230 V AC (connection pattern to EN 175301)	
	·	

006	Silencer
	None
S	Silencer
007	Pressure gauge alternatives
	None
AG	MS pressure gauge
A4	Adapter for EN pressure gauge 1/4, without pressure gauge
008	Alternative pressure gauge scale
	MS pressure gauge
PSI	psi
MPA	MPa
009	Type of mounting
	Without mounting bracket
WP	Mounting bracket basic design
010	Flow direction
	Flow direction from left to right
Z	Flow direction from right to left

Function:



Flow rate 25000 ... 32000 l/min

Temperature range −10 ... +50°C

Operating pressure 3 ... 16 bar

- www.festo.com



- Electrically actuated on/off valve for pressurising and exhausting pneumatic systems
- With solenoid coil, without plug socket
- Choice of three voltage ranges
- Ducted exhaust possible via a threaded connection with silencer
- Detenting and non-detenting manual override

General technical data		
Pneumatic connection 1, 2		
Connecting plate	[AG]	G1, G1 1/4, G1 1/2 or G2
Module without connecting thread/connecting plate	[G]	-
Pneumatic connection 3		G1
Design		Piston spool
Type of mounting		With accessories
		In-line installation
Mounting position		Any
Valve function		3/2-way valve, single solenoid, closed
Exhaust air function		Cannot be throttled
Reset method		Mechanical spring
Switching position indication		With accessories
		LED (with variant V24P)
Type of control		Piloted
Pilot air supply		Internal
Flow direction		Not reversible

 $[\]mid$ Note: This product conforms to ISO 1179-1 and ISO 228-1.

Electrical data

Characteristic coil data	1					
With supply [V24], [V24P] 24 V DC: 4.5 W, permissible voltage fluctuations ±10%						
voltage [V110] 110 V AC: 50 Hz, pick-up power 11.5 W, holding power 8.9 W, permissible voltage fluctuations ±10%						
		110 V AC: 60 Hz, pick-up power 9.5 W, holding power 6.2 W, permissible voltage fluctuations ±10%				
	[V230]	230 V AC: 50 Hz, pick-up power 11.5 W, holding power 9.1 W, permissible voltage fluctuations ±10%				
	230 V AC: 60 Hz, pick-up power 9.5 W, holding power 6.4 W, permissible voltage fluctuations ±10%					
Electrical connection						
With supply	[V24], [V110],	Plug, square design to EN 175301-803, type A				
voltage	[V230]					
	[V24P]	Plug M12, 4-pin to DESINA				
Degree of protection for solenoid coil		IP65				
Duty cycle	[%]	100				

Standard nominal flow rate qnN ¹⁾ [l/min]				
In main flow direction 1 → 2	25000 32000			
In relief direction 2 → 3	8900			

¹⁾ Measured at p1 = 6 bar and Δp = 1 bar.

Operating and environmental conditions					
Operating pressure	[bar]	316			
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]			
		Inert gases			
Note on the operating/pilot med	dium	Lubricated operation possible (in which case lubricated operation will always be required)			
Ambient temperature	[°C]	-10 +50			
Temperature of medium	[°C]	-10 +50			
Corrosion resistance class	CRC ¹⁾	2			


¹⁾ Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

Weight [g]	
On/off valve	3800
On/off valve with silencer S	3900

Materials

Sectional view





On/of	On/off valve				
[1]	Housing	Die-cast aluminium			
[2]	Top cover	Aluminium			
[3]	Bottom cover	Aluminium			
[4]	Valve tappet	Stainless steel, POM, NBR			
[5]	Springs	Steel			
-	Covers/cover plates	PA			
-	Seals	NBR			
-	Connecting plate, module connector, mounting bracket	Die-cast aluminium			
Note (on materials	Free of copper and PTFE (not with variant AG)			

Dimensions - Basic version


[G] Module without connecting thread, without connecting plate, with cover plate

[V24], [V110], [V230] Supply voltage





[V24P] Supply voltage





- 1 = Connected to 2 2 = Connected to 1
- 3 = com(-)

Download CAD data → www.festo.com


4 = Signal (+)

[1] Plug connection to EN 175301-803 [2] Plug connection M12, 4-pin to DESINA for connecting cable NEBU-M12 → Flow direction

Туре	B1	B2	В3	B4	L1	L2	L3	L4	L5	D5
MS12-EE-G-V24, V110, V230	124	122	61	148	237	130	162	35.7	12.3	G1
MS12-EE-G-V24P								36	10	

Dimensions - Silencer







Туре	D2 Ø	L4
MS12-EES	47.8	165.5


Dimensions – Pressure gauge/pressure gauge alternatives


Download CAD data → www.festo.com

[AG] Integrated MS pressure gauge with standard scale, display unit [bar]









Туре	В3	B4	D4
MS12-EEAG	61	148	-
MS12-EEA4	61	148	G1/4

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Ordering data					
Size	Supply voltage 2	upply voltage 24 V DC			
	Part no.	Туре			
MS12	541496	MS12-EE-G-V24			

Ordering data – Modular product system


Ordering table				
Grid dimension [mm]	124	Conditions	Code	Enter code
Module no.	535032			
Series	Standard		MS	MS
Size	12		12	12
Function	On/off valve, electric		-EE	-EE
Pneumatic connection	Connecting plate G1		-AGF	
	Connecting plate G1 1/4		-AGG	
ries e nction eumatic connection pply voltage encer essure gauge/pressure gauge ernatives	Connecting plate G1 1/2		-AGH	
	Connecting plate G2		-AGI	
	Module without connecting thread, without connecting plate		MS 12 -EE -AGF -AGG -AGH	
Supply voltage	24 V DC (plug pattern to EN 175301), 16 bar		-V24	
	24 V DC plug (plug pattern M12 to DESINA), 16 bar		-V24P	
	110 V AC (plug pattern to EN 175301), 16 bar		-V110	
	230 V AC (plug pattern to EN 175301), 16 bar		-V230	
Silencer	Silencer		-S	
Pressure gauge/pressure gauge	MS pressure gauge, bar		-AG	
alternatives	Adapter for EN pressure gauge 1/4, without pressure gauge		-A4	
Alternative pressure gauge scale	psi	[1]	-PSI	
	MPa	[1]	-MPA	
Type of mounting	Mounting bracket standard design	[2]	-WP	
Flow direction	Flow direction from right to left		-Z	

Only with pressure gauge AG

^[1] PSI, MPA [2] WP Only with connecting plate AGF, AGG, AGH or AGI.

Peripherals overview

Soft-start valve MS12-DL



Moun	Mounting attachments and accessories						
		Order code	→ Page/Internet				
[1]	Soft-start valve	MS12-DL	92				
Can b	e ordered via the modular product system						
[2]	Mounting bracket	[WP]	95				
[4]	Connecting plate SET ¹⁾	[AG]					
[5]	Adapter for EN pressure gauge 1/4	[A4]					
[9]	MS pressure gauge	[AG]					
Can b	Can be ordered as accessories						
[2]	Mounting bracket	MS12-WP	ms12-wp				
[3]	Module connector	MS12-MV	ms12-mv				
[4]	Connecting plate SET	MS12-AG	ms12-ag				
[6]	Pressure gauge	MA	103				
[7]	Pressure sensor	SPAUT-R14M	102				
[8]	Connecting cable	NEBU-M8LE4, NEBU-M12LE4	103				

¹⁾ Module connector [3] is included in the scope of delivery.

Type codes

001	Series	
MS	MS series	
002	Size	
12	Grid dimension 124 mm	
003	Function	
DL	Soft-start valve, pneumatic	
004	Pneumatic connection	
AGF	Sub-base G1	
ACC	Connecting plate G1 1/4	
AGG	Connecting plate of 1/4	
AGH	Connecting plate G1 1/2	
	<u> </u>	
AGH	Connecting plate G1 1/2	
AGH AGI	Connecting plate G1 1/2 Sub-base G2	
AGH AGI G	Connecting plate G1 1/2 Sub-base G2 Module without connecting thread, without sub-base	
AGH AGI G	Connecting plate G1 1/2 Sub-base G2 Module without connecting thread, without sub-base Pressure gauge alternatives	

006	Alternative pressure gauge scale	
	MS pressure gauge	
PSI	psi	
MPA	MPa	
007	Type of mounting	
	Without mounting bracket	
WP	Mounting bracket basic design	
008	UL certification	
	None	
UL1	cULus ordinary location for Canada and USA	
009	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	

Function:



- N - Flow rate 25000 ... 42000 l/min

Temperature range -10 ... +60°C

Operating pressure 2 ... 20 bar



The duration of the pressure build-up is set using the restrictor attached to the valve cap.

The outlet pressure p2 rises slowly in accordance with the restrictor setting. The main seat opens when the switch-through pressure is reached.

- Pneumatically actuated soft-start valve for slowly pressurising and exhausting pneumatic systems (for use with on/off valves EM and EE)
- The drives move slowly and reliably into the initial position



- Sudden and erratic movements are avoided
- Main seat opening at approx. 50% of operating pressure
- Adjustable switching time delay

General technical data		
Pneumatic connection 1, 2		
Connecting plate [[AG]	G1, G1 1/4, G1 1/2 or G2
Module without connecting [thread/connecting plate	[G]	-
Design		Piston seat
Type of mounting		With accessories
		In-line installation
Mounting position		Any
Valve function		2/2-way valve
Exhaust air function		Can be throttled
Reset method		Mechanical spring
Type of control		Direct
Pilot air supply		Internal
Flow direction		Not reversible

 $[\]mbox{\ }\mbox{\ }\$

Standard nominal flow rate qnN ¹⁾ [l/min]		
In main flow direction 1 → 2	25000 42000	
In relief direction 2 → 1	25000 42000	

¹⁾ Measured at p1 = 6 bar and p2 = 5 bar, $\Delta p = 1$ bar.


Operating and environmental conditions				
Operating pressure [bar]		2 20		
Operating medium		Compressed air to ISO 8573-1:2010 [7:-:-]		
Ambient temperature [°C]		-10 +60		
Temperature of medium	[°C]	-10 +60		
Corrosion resistance class	CRC ¹⁾	2		

¹⁾ Corrosion resistance class CRC 2 to Festo standard FN 940070 Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

Weight [g]	
Soft-start valve	3600


Materials

Sectional view



Soft-	Soft-start valve						
[1]	Housing	Die-cast aluminium					
[2]	Top cover	Aluminium					
[3]	Bottom cover	Aluminium					
[4]	Valve tappet	Aluminium, NBR					
[5]	Springs	Steel					
-	Covers/cover plates	PA					
_	Seals	NBR					
_	Connecting plate, module connector, mounting bracket	Die-cast aluminium					
Note	on materials	Free of copper and PTFE (not with variant AG)					

Switching point – Pressure p as a function of time t




- [1] Tolerance range
- [2] Switching point
- [3] Filling time is adjustable via a restrictor




The +25%/–20% switching point tolerance refers to the operating pressure p1. Example: A switching point from 1.2 bar to 3.0 bar is permissible at an operating pressure of 4 bar.

Dimensions - Basic version

[G] Module without connecting thread, without connecting plate, with cover plate





Download CAD data → www.festo.com


Flow direction


Download CAD data → www.festo.com


Туре	B1	B2	В3	B4	L1	L2	L3
MS12-DL-G	124	122	61	148	178	82	162


Dimensions – Pressure gauge/pressure gauge alternatives

[AG] Integrated MS pressure gauge with standard scale, display unit [bar]









Туре	В3	B4	D4
MS12-DLAG	61	148	-
MS12-DLA4	61	148	G1/4

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Ordering data					
Size	Part no.	Туре			
MS12	541497	MS12-DL-G			

Ordering data – Modular product system


Ordering table				
Grid dimension [mm]	124	Conditions	Code	Enter code
Module no.	535033			
Series	Standard		MS	MS
Size	12		12	12
Function	Soft-start valve, pneumatic		-DL	-DL
Pneumatic connection	Connecting plate G1		-AGF	
	Connecting plate G1 1/4		-AGG	
	Connecting plate G1 1/2		-AGH	
	Connecting plate G2		-AGI	
	Module without connecting thread, without connecting plate		-G	
Pressure gauge/pressure gauge	MS pressure gauge, bar		-AG	
alternatives	Adapter for EN pressure gauge 1/4, without pressure gauge		-A4	
Alternative pressure gauge scale	psi	[1]	-PSI	
	MPa	[1]	-MPA	
Type of mounting	Mounting bracket standard design	[2]	-WP	
Flow direction	Flow direction from right to left		-Z	

[1] PSI, MPA [2] WP

Only with pressure gauge AG
Only with connecting plate AGF, AGG, AGH or AGI.

Peripherals overview

Soft-start valve MS12-DE



Moun	Mounting attachments and accessories					
		Order code	→ Page/Internet			
[1]	Soft-start valve	MS12-DE	98			
Can b	e ordered via the modular product system					
[6]	Mounting bracket	[WP]	101			
[8]	Connecting plate SET ¹⁾	[AG]				
[9]	Adapter for EN pressure gauge 1/4	[A4]]			
[13]	MS pressure gauge	[AG]	1			
Can b	e ordered as accessories					
[2]	Connecting cable	NEBU-M12LE4	103			
[3]	Illuminating seal	MC-LD	102			
[4]	Connecting cable	KMC	102			
[5]	Plug socket	MSSD-C	102			
[6]	Mounting bracket	MS12-WP	ms12-wp			
[7]	Module connector	MS12-MV	ms12-mv			
[8]	Connecting plate SET	MS12-AG	ms12-ag			
[10]	Pressure gauge	MA	103			
[11]	Pressure sensor	SPAUT-R14M	102			
[12]	Connecting cable	NEBU-M8LE4, NEBU-M12LE4	103			


¹⁾ Module connector [7] is included in the scope of delivery.

Type codes


001	Series	
MS	MS series	
1	l	
002	Size	
12	Grid dimension 124 mm	
003	Function	
DE	Soft-start valve, electric	
004	Pneumatic connection	
AGF	Sub-base G1	
AGG	Connecting plate G1 1/4	
AGH	Connecting plate G1 1/2	
AGI	Sub-base G2	
G	Module without connecting thread, without sub-base	
005	Supply voltage	
V110	110 V AC (connection pattern to EN 175301)	
		_
V230	230 V AC (connection pattern to EN 175301)	
V230 V24	230 V AC (connection pattern to EN 175301) 24 V DC (connection pattern to EN 175301)	

006	Pressure gauge alternatives	
	None	
AG	MS pressure gauge	
A4	Adapter for EN pressure gauge 1/4, without pressure gauge	
007	Alternative pressure gauge scale	
	MS pressure gauge	
PSI	psi	
MPA	MPa	
008	Type of mounting	
	Without mounting bracket	
WP	Mounting bracket basic design	
009	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	

Function:



Flow rate 25000 ... 42000 l/min








www.festo.com

The duration of the pressure build-up is set using the restrictor attached to the valve cap.


The outlet pressure p2 rises slowly in accordance with the restrictor setting. While the solenoid valve is not actuated, only the flow rate of the flow control valve is available. The main seat is only opened when the solenoid valve is energised.

When the solenoid valve is switched off, the main seat is closed and only the flow rate of the flow control valve is available.

When exhausting a system, the solenoid valve should remain switched on; this increases the volume flow from 2 to 1 and shortens the exhausting time.



- The drives move slowly and reliably into the initial position
- Sudden and erratic movements are avoided



- The switching pressure can be precisely controlled with a solenoid valve
- Adjustable switching time delay
- Choice of three voltage ranges
- Detenting and non-detenting manual override

General technical data	
Pneumatic connection 1, 2	
Connecting plate [AG.	.] G1, G1 1/4, G1 1/2 or G2
Module without connecting [G] thread/connecting plate	-
Pneumatic connection 3	G1
Design	Piston seat
Type of mounting	With accessories
	In-line installation
Mounting position	Any
Valve function	2/2-way valve
Exhaust air function	Can be throttled
Reset method	Mechanical spring
Signal status indication	With accessories
	LED (with variant V24P)
Type of control	Piloted
Pilot air supply	Internal
Flow direction	Not reversible

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Electrical data

Characteristic coil da	ta	
With supply	[V24]	24 V DC: 8.4 W
voltage		42 V AC: 50 Hz, pick-up power 14 VA, holding power 10 VA
		42 V AC: 60 Hz, pick-up power 12 VA, holding power 7 VA
	[V24P]	24 V DC
	[V110]	110 V AC
	[V230]	230 V AC
Electrical connection		
With supply	[V24], [V110],	Plug, square design to EN 175301-803, type A
voltage	[V230]	
	[V24P]	Plug M12, 4-pin to DESINA
Degree of protec	tion for solenoid coil	IP65
Duty cycle	[%]	100

Standard nominal flow rate qnN ¹⁾ [l/min]	
In main flow direction 1 → 2	25000 42000
In relief direction $2 \rightarrow 1^{2}$	25000 42000

- 1) Measured at p1 = 6 bar and p2 = 5 bar, Δp = 1 bar.
- 2) With energised solenoid valve.

Operating and environmental co	nditions	
Operating pressure	[bar]	316
Operating medium		Compressed air to ISO 8573-1:2010 [-:-:-]
Ambient temperature	[°C]	-10 +50
Temperature of medium	[°C]	-10 +50
Corrosion resistance class	CRC ¹⁾	2


¹⁾ Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

Weight [g]	
Soft-start valve	3800

Materials


Sectional view




Soft-st	art valve	
[1]	Housing	Die-cast aluminium
[2]	Top cover	Aluminium
[3]	Bottom cover	Aluminium
[4]	Valve tappet	Aluminium, NBR
[5]	Springs	Steel
-	Covers/cover plates	PA
_	Seals	NBR
-	Connecting plate, module connector, mounting bracket	Die-cast aluminium
Note o	n materials	Free of copper and PTFE (not with variant AG)


Dimensions - Basic version

[G] Module without connecting thread, without connecting plate, with cover plate





[V24P] Supply voltage





1 = Connected to 2

2 = Connected to 1

3 = com(-)

Download CAD data → www.festo.com

4 = Signal(+)

[1] Plug connection to EN 175301-803


[2] Plug connection M12, 4-pin to DESINA for connecting cable NEBU-M12


Flow direction


Туре	B1	B2	В3	B4	L1	L2	L3	L4	L5
MS12-DE-G-V24, V110, V230	124	122	(1	140	226	120	1/2	35.7	12.3
MS12-DE-G-V24P	124	122	91	148	226	130	162	36	10

Dimensions - Pressure gauge/pressure gauge alternatives

[AG] Integrated MS pressure gauge with standard scale, display unit [bar]







Download CAD data → www.festo.com

Туре	В3	B4	D4
MS12-DEAG	61	148	-
MS12-DEA4	61	148	G1/4

 $[\]mid \! \! \mid \cdot \! \! \mid$ Note: This product conforms to ISO 1179-1 and ISO 228-1.

Ordering data		
Size	Supply voltage 2	4 V DC
	Part no.	Туре
MS12	541498	MS12-DE-G-V24

Ordering data – Modular product system

Ordering table				
Grid dimension [mm]	124	Conditions	Code	Ente code
Module no.	535034			
Series	Standard		MS	MS
Size	12		12	12
Function	Soft-start valve, electric		-DE	-DE
Pneumatic connection	Connecting plate G1		-AGF	
	Connecting plate G1 1/4		-AGG	
	Connecting plate G1 1/2		-AGH	
	Connecting plate G2		-AGI	
	Module without connecting thread, without connecting plate		-G	
Supply voltage	24 V DC (plug pattern to EN 175301), 16 bar		-V24	
	24 V DC plug (plug pattern M12 to DESINA), 16 bar		-V24P	
	110 V AC (plug pattern to EN 175301), 16 bar		-V110	
	230 V AC (plug pattern to EN 175301), 16 bar		-V230	
Pressure gauge/pressure gauge	MS pressure gauge, bar		-AG	
alternatives	Adapter for EN pressure gauge 1/4, without pressure gauge		-A4	
Alternative pressure gauge scale	psi	[1]	-PSI	
	MPa	[1]	-MPA	
Type of mounting	Mounting bracket standard design	[2]	-WP	
Flow direction	Flow direction from right to left		-Z	

^[1] PSI, MPA [2] WP

Only with pressure gauge AG Only with connecting plate AGF, AGG, AGH or AGI.

Accessories

	Ordering data − Plug socket MSSD Datasheets → Internet: mssd										
		Description		Electrical connection	Cable connection	Part no.	Туре				
		For MS4/6-EE/DE	_	3-pin	Screw terminal	★ 151687	MSSD-EB				
			For use in explosion protection areas 4-pin	4-pin	Insulation displacement connector	192745	MSSD-EB-S-M14				
				3-pin	Screw terminal	570367	MSSD-EB-M12-24VDC-SD-EX				
		For MS9-EE, for MS12-EE/DE	<u>-</u>	3-pin	Screw terminal	34583	MSSD-C				
				4-pin	Insulation displacement connector	192748	MSSD-C-S-M16				

Ordering data - Plug	Datasheets → Internet: kmeb, kmc						
	Description	Operating voltage	Electrical connection	Switching status indication	Cable length [m]	Part no.	Туре
	For MS4/6-EE/DE	24 V DC	2-pin	LED	2.5	547268	KMEB-3-24-2.5-LED
		230 V AC			5	547269	KMEB-3-24-5-LED
				-	2.5	547270	KMEB-3-24-2.5
					5	547271	KMEB-3-24-5
			3-pin	LED	2.5	★ 151688	KMEB-1-24-2.5-LED
					5	151689	KMEB-1-24-5-LED
					10	193457	KMEB-1-24-10-LED
			3-pin	-	2.5	151690	KMEB-1-230AC-2.5
					5	151691	KMEB-1-230AC-5
	For MS9-EE, for MS12-EE/DE	-EE/DE	3-pin	LED	2.5	30931	KMC-1-24DC-2.5-LED
					5	30933	KMC-1-24DC-5-LED
					10	193459	KMC-1-24-10-LED
(10%)			3-pin -	-	2.5	30932	KMC-1-230AC-2.5
					5	30934	KMC-1-230AC-5

Ordering data – Illuminating seal MEB-LD/MC-LD Datasi							
	Description	Operating voltage range	Part no.	Туре			
	For plug socket with cable KMEB and plug	12 24 V DC	151717	MEB-LD-12-24DC			
	socket MSSD-EB	230 V DC/AC ±10%	151718	MEB-LD-230AC			
	For connecting cable KMC and plug socket	12 24 V DC	19145	MC-LD-12-24DC			
	MSSD-C	230 V DC/AC ±10%	19146	MC-LD-230AC			

Ordering data – Loc	Datasheets → Internet:	Datasheets → Internet: cpv18-hv			
	Description	Part no.	Туре	PU ¹⁾	
	For MS4/6-EE/DEV24	Cover for the manual override, the clip prevents actuation	530056	CPV18-HV	10

[1] Packaging unit

0	rdering data – Press	Datasheets → Internet: spau							
		Pneumatic connection	Display type	Switching output	Electrical connection	Part no.	Туре		
F	For direct mounting on adapter with connecting thread 1/8 or 1/4, pressure measuring range 0 10 bar, relative pressure measurement								
	\^\@\	Male thread R1/8	Illuminated LCD	2x PNP or 2x NPN	M8x1, 4-pin	8001203	SPAU-P10R-T-R18M-L-PNLK-PNVBA-M8D		
switchable					M12x1, 4-pin	8001206	SPAU-P10R-T-R18M-L-PNLK-PNVBA-M12D		
		Male thread R1/4			M8x1, 4-pin	8001209	SPAU-P10R-T-R14M-L-PNLK-PNVBA-M8D		
					M12x1, 4-pin	8001208	SPAU-P10R-T-R14M-L-PNLK-PNVBA-M12D		

Accessories

Ordering data – Co	onnecting cable NEBU-Ma	3				Datasheets → Internet: nebu
	Electrical connection	Number of v	wires	Cable length [m]	Part no.	Туре
	M8x1, straight socker	3		2.5	★ 541333	NEBU-M8G3-K-2.5-LE3
NE TOTAL STREET				5	★ 541334	NEBU-M8G3-K-5-LE3
	M8x1, angled socket	3		2.5	★ 541338	NEBU-M8W3-K-2.5-LE3
Carried States				5	★ 541341	NEBU-M8W3-K-5-LE3
Ordering data – Co	onnecting cable NEBU-M	12			!	Datasheets → Internet: nebu
oracimg acta	Electrical connection	Number of v	wires	Cable length [m]	Part no.	Type
	M12x1, straight sock	et 4		2.5	★ 550326	NEBU-M12G5-K-2.5-LE4
TO THE STATE OF TH				5	★ 541328	NEBU-M12G5-K-5-LE4
	M12x1, angled socke	t 4		2.5	550325	NEBU-M12W5-K-2.5-LE4
				5	541329	NEBU-M12W5-K-5-LE4
ordering data – Se	ensor socket SIE-GD Electrical connection				Part no.	Datasheets → Internet: sie-gd Type
	M12x1, 4-pin				18494	SIE-GD
Ordering data – Ar	ngled plug socket SIE-WD					Datasheets → Internet: sie-wd
ordering data 74	Electrical connection				Part no.	Type
9	M12x1, 4-pin				12956	SIE-WD-TR
Ordering data – Si	lencer U					Datasheets → Internet: u
g	Description		Pneumatic connec	ction	Part no.	Туре
	For MS4-EM1/EE		G1/4		6842	U-1/4-B
	For MS6-EM1/EE		G1/2		6844	U-1/2-B
	For MS9/12-EM/EE		G1		151990	U-1-B
Ordering data – Pr	1	1	1		1	1
	Nominal size	Pneumatic connection	Display range [bar]	[psi]	Part no.	Туре
	Pressure gauge MA,	EN 837-1	[20.]	fb2.1		Datasheets → Internet: ma
	40	R1/4	0 16	0 232	187080	MA-40-16-R1/4-EN
		G1/4	0 16	0 232	183901	MA-40-16-G1/4-EN
	Pressure gauge MA,	EN 837-1, with red/green range	<u> </u>			Datasheets → Internet: ma
	40	R1/8	0 16	-	525726	MA-40-16-R1/8-E-RG
	50	R1/4	0 16	-	525729	MA-50-16-R1/4-E-RG
Ordering data – Pa	dlock LRVS-D Weight [g]				Part no.	Туре
\sim	120				193786	LRVS-D
~ ~						