

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Trade name : PRECISION SILICONE Spray
UFI : GV00-X0KF-2009-OSTU
Vaporizer : Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Industrial use, Professional use
Industrial/Professional use spec : Industrial
For professional use only
Use of the substance/mixture : Lubricants, Greases and Release Products

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Manufacturer

ROCOL a division of ITW Ltd
Rocol House
Wakefield Rd, Swillington
LS26 8BS Leeds - United Kingdom
T +44 (0)113 232 2600
customer.service@rocol.com - www.rocol.com

1.4. Emergency telephone number

Emergency number : +44 (0)113 232 2600

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH Birmingham	0344 892 0111	

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Aerosol, Category 1 H222;H229
Skin corrosion/irritation, Category 2 H315
Hazardous to the aquatic environment — Chronic Hazard, Category 3 H412
Full text of H statements : see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



PRECISION SILICONE Spray

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

	GHS02	GHS07
Signal word (CLP)	: Danger	
Hazard statements (CLP)	: H222 - Extremely flammable aerosol. H229 - Pressurised container: May burst if heated. H315 - Causes skin irritation. H412 - Harmful to aquatic life with long lasting effects.	
Precautionary statements (CLP)	: P410+P412 - Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F. P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 - Do not spray on an open flame or other ignition source. P251 - Do not pierce or burn, even after use. P271 - Use only outdoors or in a well-ventilated area. P280 - Wear protective gloves/protective clothing/eye protection/face protection/hearing protection. P302+P352 - IF ON SKIN: Wash with plenty of water.	

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE) substance with national workplace exposure limit(s) (GB)	(CAS-No.) 68476-85-7 (EC-No.) 270-704-2	≥ 70	Flam. Gas 1, H220 Press. Gas (Liq.), H280 Flam. Liq. 1, H224 Muta. Not classified Carc. Not classified
HEPTANE & ISOMERS	(CAS-No.) 64742-49-0 (EC-No.) 927-510-4 (REACH-no) 01-2119475515-33	15 – 30	Flam. Liq. 2, H225 Skin Irrit. 2, H315 STOT SE 3, H336 Asp. Tox. 1, H304 Aquatic Chronic 2, H411

Product subject to CLP Article 1.1.3.7. The disclosure rules of the components is modified in this case.

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
First-aid measures after inhalation	: Allow affected person to breathe fresh air. Allow the victim to rest.
First-aid measures after skin contact	: Wash with plenty of water/... Wash contaminated clothing before reuse. If skin irritation occurs: Get medical advice/attention.
First-aid measures after eye contact	: Rinse immediately with plenty of water. Obtain medical attention if pain, blinking or redness persists.
First-aid measures after ingestion	: Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after skin contact	: Causes skin irritation.
-------------------------------------	---------------------------

PRECISION SILICONE Spray

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Foam. Dry powder. Carbon dioxide. Water spray. Sand.
Unsuitable extinguishing media : Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

No additional information available

5.3. Advice for firefighters

Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment.
Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures : Evacuate unnecessary personnel.

6.1.2. For emergency responders

Protective equipment : Equip cleanup crew with proper protection.
Emergency procedures : Ventilate area.

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters. Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials.

6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour.
Hygiene measures : Wash hands, forearms and face thoroughly after handling.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Keep container closed when not in use.
Incompatible products : Strong bases. Strong acids.
Incompatible materials : Sources of ignition. Direct sunlight.

7.3. Specific end use(s)

No additional information available

PRECISION SILICONE Spray

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE) (68476-85-7)	
United Kingdom - Occupational Exposure Limits	
Local name	Liquefied petroleum gas
WEL TWA (OEL TWA) [1]	1750 mg/m ³
WEL TWA (OEL TWA) [2]	1000 ppm
WEL STEL (OEL STEL)	2180 mg/m ³
WEL STEL (OEL STEL) [ppm]	1250 ppm
Remark (WEL)	Carc (Capable of causing cancer and/or heritable genetic damage (only applies if LPG contains more than 0.1% of buta-1,3-diene))
Regulatory reference	EH40/2005 (Fourth edition, 2020). HSE

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

No additional information available

8.1.5. Control banding

No additional information available

8.2. Exposure controls

8.2.1. Appropriate engineering controls

No additional information available

8.2.2. Personal protection equipment

Personal protective equipment:

Avoid all unnecessary exposure.

8.2.2.1. Eye and face protection

Eye protection:
Chemical goggles or safety glasses

8.2.2.2. Skin protection

Skin and body protection:
Wear suitable protective clothing

Hand protection:
Wear protective gloves. Nitrile rubber gloves

8.2.2.3. Respiratory protection

Respiratory protection:
In case of inadequate ventilation wear respiratory protection. Wear a respirator conforming to EN140 with Type A filter or better

8.2.2.4. Thermal hazards

PRECISION SILICONE Spray

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

No additional information available

8.2.3. Environmental exposure controls

Other information:

Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: Colourless.
Odour	: Characteristic odour.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: < 0 °C
Flash point	: < -100 °C
Auto-ignition temperature	: > 200 °C
Decomposition temperature	: No data available
Flammability (solid, gas)	: Non flammable.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: ≈ 0.6
Solubility	: insoluble in water.
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

VOC content : 546 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

Extremely flammable aerosol.

10.2. Chemical stability

Not established.

10.3. Possibility of hazardous reactions

Not established.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

PRECISION SILICONE Spray

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity (oral) : Not classified
Acute toxicity (dermal) : Not classified
Acute toxicity (inhalation) : Not classified

HEPTANE & ISOMERS (64742-49-0)	
LD50 oral rat	5840 mg/kg
LD50 dermal rat	2800 – 3100 mg/kg bodyweight Animal: rat
LC50 Inhalation - Rat	> 23.3 mg/l air Animal: rat, Guideline: OECD Guideline 403 (Acute Inhalation Toxicity)

HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE) (68476-85-7)	
LC50 Inhalation - Rat (Vapours)	> 20 mg/l/4h

Skin corrosion/irritation : Causes skin irritation.
Serious eye damage/irritation : Not classified
Additional information : Based on available data, the classification criteria are not met
Respiratory or skin sensitisation : Not classified
Additional information : Based on available data, the classification criteria are not met
Germ cell mutagenicity : Not classified
Additional information : Based on available data, the classification criteria are not met
Carcinogenicity : Not classified
Additional information : Based on available data, the classification criteria are not met

Reproductive toxicity : Not classified
Additional information : Based on available data, the classification criteria are not met

STOT-single exposure : Not classified
Additional information : Based on available data, the classification criteria are not met

HEPTANE & ISOMERS (64742-49-0)	
STOT-single exposure	May cause drowsiness or dizziness.

STOT-repeated exposure : Not classified
Additional information : Based on available data, the classification criteria are not met

HEPTANE & ISOMERS (64742-49-0)	
LOAEC (inhalation, rat, vapour, 90 days)	16.6 mg/l air Animal: rat, Animal sex: male
NOAEC (inhalation, rat, vapour, 90 days)	3.3 mg/l air Animal: rat, Animal sex: male

Aspiration hazard : Not classified
Additional information : Based on available data, the classification criteria are not met

PRECISION SILICONE Spray	
Vaporizer	Aerosol

Potential adverse human health effects and symptoms : Based on available data, the classification criteria are not met

PRECISION SILICONE Spray

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 12: Ecological information

12.1. Toxicity

Ecology - water : Harmful to aquatic life with long lasting effects.
Hazardous to the aquatic environment, short-term (acute) : Not classified
Hazardous to the aquatic environment, long-term (chronic) : Harmful to aquatic life with long lasting effects.

HEPTANE & ISOMERS (64742-49-0)	
LC50 - Fish [1]	> 13.4 mg/l
EC50 - Crustacea [1]	3 mg/l
LOEC (chronic)	0.32 mg/l Test organisms (species): Daphnia magna Duration: '21 d'
NOEC (chronic)	0.17 mg/l Test organisms (species): Daphnia magna Duration: '21 d'

12.2. Persistence and degradability

PRECISION SILICONE Spray	
Persistence and degradability	May cause long-term adverse effects in the environment.

HEPTANE & ISOMERS (64742-49-0)	
Persistence and degradability	98 % biodegradation 28 days.

12.3. Bioaccumulative potential

PRECISION SILICONE Spray	
Bioaccumulative potential	Not established.

HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE) (68476-85-7)	
Partition coefficient n-octanol/water (Log Pow)	2.3 – 2.8

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

Additional information : Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations. Dispose of contents/container to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation.
Ecology - waste materials : Avoid release to the environment.






SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

PRECISION SILICONE Spray

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
UN 1950	UN 1950	UN 1950	UN 1950	UN 1950
14.2. UN proper shipping name				
AEROSOLS	AEROSOLS	Aerosols, flammable	AEROSOLS	AEROSOLS
Transport document description				
UN 1950 AEROSOLS, 2.1, (D)	UN 1950 AEROSOLS, 2.1	UN 1950 Aerosols, flammable, 2.1	UN 1950 AEROSOLS, 2.1	UN 1950 AEROSOLS, 2.1
14.3. Transport hazard class(es)				
2.1	2.1	2.1	2.1	2.1
				
14.4. Packing group				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.5. Environmental hazards				
Dangerous for the environment : No	Dangerous for the environment : No Marine pollutant : No	Dangerous for the environment : No	Dangerous for the environment : No	Dangerous for the environment : No
No supplementary information available				

14.6. Special precautions for user

Overland transport

Classification code (ADR)	: 5F
Special provisions (ADR)	: 190, 327, 344, 625
Limited quantities (ADR)	: 1I
Excepted quantities (ADR)	: E0
Packing instructions (ADR)	: P207, LP200
Special packing provisions (ADR)	: PP87, RR6, L2
Mixed packing provisions (ADR)	: MP9
Transport category (ADR)	: 2
Special provisions for carriage - Packages (ADR)	: V14
Special provisions for carriage - Loading, unloading and handling (ADR)	: CV9, CV12
Special provisions for carriage - Operation (ADR)	: S2
Tunnel restriction code (ADR)	: D

Transport by sea

Special provisions (IMDG)	: 63, 190, 277, 327, 344, 381, 959
Packing instructions (IMDG)	: P207, LP200
Special packing provisions (IMDG)	: PP87, L2
EmS-No. (Fire)	: F-D
EmS-No. (Spillage)	: S-U
Stowage category (IMDG)	: None
Stowage and handling (IMDG)	: SW1, SW22
Segregation (IMDG)	: SG69

Air transport

PCA Excepted quantities (IATA)	: E0
PCA Limited quantities (IATA)	: Y203
PCA limited quantity max net quantity (IATA)	: 30kgG
PCA packing instructions (IATA)	: 203
PCA max net quantity (IATA)	: 75kg

PRECISION SILICONE Spray

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

CAO packing instructions (IATA)	: 203
CAO max net quantity (IATA)	: 150kg
Special provisions (IATA)	: A145, A167, A802
ERG code (IATA)	: 10L

Inland waterway transport

Classification code (ADN)	: 5F
Special provisions (ADN)	: 190, 327, 344, 625
Limited quantities (ADN)	: 1 L
Excepted quantities (ADN)	: E0
Equipment required (ADN)	: PP, EX, A
Ventilation (ADN)	: VE01, VE04
Number of blue cones/lights (ADN)	: 1

Rail transport

Classification code (RID)	: 5F
Special provisions (RID)	: 190, 327, 344, 625
Limited quantities (RID)	: 1L
Excepted quantities (RID)	: E0
Packing instructions (RID)	: P207, LP200
Special packing provisions (RID)	: PP87, RR6, L2
Mixed packing provisions (RID)	: MP9
Transport category (RID)	: 2
Special provisions for carriage – Packages (RID)	: W14
Special provisions for carriage - Loading, unloading and handling (RID)	: CW9, CW12
Colis express (express parcels) (RID)	: CE2
Hazard identification number (RID)	: 23

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

VOC content : 546 g/l

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

PRECISION SILICONE Spray

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Full text of H- and EUH-statements:	
Aquatic Chronic 2	Hazardous to the aquatic environment — Chronic Hazard, Category 2
Asp. Tox. 1	Aspiration hazard, Category 1
Carc. Not classified	Carcinogenicity Not classified
Flam. Gas 1	Flammable gases, Category 1
Flam. Liq. 1	Flammable liquids, Category 1
Flam. Liq. 2	Flammable liquids, Category 2
Muta. Not classified	Germ cell mutagenicity Not classified
Press. Gas (Liq.)	Gases under pressure : Liquefied gas
Skin Irrit. 2	Skin corrosion/irritation, Category 2
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Narcosis
H220	Extremely flammable gas.
H222	Extremely flammable aerosol.
H224	Extremely flammable liquid and vapour.
H225	Highly flammable liquid and vapour.
H229	Pressurised container: May burst if heated.
H280	Contains gas under pressure; may explode if heated.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.