

Impact driver LXT®

DTD157

18V • 1/4" • 140 Nm • 0 – 3 000 min⁻¹

Extra-compact brushless impact driver with assist mode and three power settings for quick driving.

A compact and light impact wrench with a hex. 1/4" drive shank. A compact tool with a max. torque of 140 Nm. 3-mode operation for A-mode / Hard mode / Soft mode for multiple applications. Handy LED light.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Brushless Motor	✓
No load speed	0 - 1300 / 3000 min ⁻¹
Max Fastening Torque Impact Drill	140 Nm
Impacts per Minute (IPM)	0 - 2000 / 4100 min ⁻¹
Tightening Capacity Standard Bolt	M5 - M14
Driving Shank	1/4 "
Sound Power Level (L _{WA})	106 dB(A)
Sound Pressure Level (L _{pA})	98 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Impact Tightening of Fasteners of the Maximum Capacity of the Tool	11,5 m/s ²
Vibration Uncertainty (K Factor), Impact Tightening of Fasteners of the	1,5 m/s ²

User benefits

- Brushless motor is electronically controlled to optimise battery energy use for longer run time per charge
- LED light illuminates the work site
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Anti wobbling bit structure
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing