




Product Datasheet

ENGLISH

# POLYPROPYLENE TERMINAL BLOCKS



## Specification

**HOUSING: POLYPROPYLENE (PP)**

**INSERTS: BRASS**

**SCREWS: GALVANISED STEEL**

**TEMP.: 85°C**

**COLOR: WHITE OR BLACK**


**Standard: CE (BS EN 60998)**

## Feature:

**SEMI-RIGID & LOW-COST**

**FLAME RETARDANT**

**ALL SCREWS ARE CAPTIVE & RAISED FOR EASY WIRING**



**Dimensions**

ART. NO.	SIZE	COLOUR	RATED VOLTAGE	RATED CURRENT	DIMENSIONS						
					L	W	Φ1	Φ2	D	H	d
7033814	2.5 MM <sup>2</sup>	WHITE	400 V	3~24 A	93.7	16	2.8	2.1	8	15	8.1
7033833		BLACK			93.7	16	2.8	2.1	8	15	8.1
7033818	4 MM <sup>2</sup>	WHITE	400 V	5~32 A	116.5	20.5	3.3	3.1	10	17	10
7033836		BLACK			116.5	20.5	3.3	3.1	10	17	10
7033827	6 MM <sup>2</sup>	WHITE	400 V	10~57 A	139.5	23.5	4.5	3.6	12	20	12
7033830		BLACK			139.5	23.5	4.5	3.6	12	20	12
7033849	10 MM <sup>2</sup>	BLACK	400 V	10~57 A	130.5	20.7	4.3	2.8	11	16	11.4
7033820	16 MM <sup>2</sup>	WHITE	400 V	30~76 A	175.5	25.3	5.5	4.1	15	23	15
7033842		BLACK			175.5	25.3	5.5	4.1	15	23	15
7033824	25 MM <sup>2</sup>	WHITE	500 V	40~101 A	228.5	35.2	7.1	4.1	19.5	34	19.5

**CROSS SECTION: RATED FOR RIGID WIRES AND CABLES (IF FOR FLEXIBLE WIRES, IT SHOULD BE REDUCED ONE-SIZE, I.E. 6 MM<sup>2</sup> TO 4 MM<sup>2</sup> .**

**THE DATA OF "d" IS DISTANCE OF TWO FIXING HOLES.**

**Φ1 WIRE ENTRY HOLE DIAMETER**

**Φ2 FIXING HOLE DIAMETER**