



AMP CT

TE Internal #: 292157-6
Connector Assembly, Plug to Plug Relay Header, Wire-to-Panel, 6
Position, 2 mm [.078 in] Centerline, 1 Row, White, Signal, Panel
Mount, AMP CT

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Connector Assembly**
Connector & Housing Type: **Plug to Plug Relay Header**
Connector System: **Wire-to-Panel**
Number of Positions: **6**
Centerline (Pitch): **2 mm [.078 in]**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Plug to Plug Relay Header
Connector System	Wire-to-Panel
Sealable	No

Configuration Features

Number of Positions	6
Number of Rows	1

Electrical Characteristics

Operating Voltage	125 V
-------------------	-------

Body Features

Primary Product Color	White
-----------------------	-------

Contact Features

Contact Retention Within Housing	Without
----------------------------------	---------



Contact Base Material	Brass
Contact Type	Pin
Contact Current Rating (Max)	2 A

Mechanical Attachment

Panel Mount Feature Type	Latches
Strain Relief	Without
Panel Mount Feature	With
Mating Retention	Without
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	Nylon 66
Centerline (Pitch)	2 mm[.078 in]

Dimensions

Panel Thickness (Recommended)	.81 – 1.6 mm[.032 – .063 in]
Connector Height	12 mm[.472 in]
Connector Length	21.4 mm[.842 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL

Packaging Features

Packaging Method	Bag & Box
Packaging Quantity	400

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM7017-C7671
Common Termination Contacts —
POWER TRIPLE LOCK



TE Part # CAT-AM7017-H8172
AMP COMMON TERMINATION
HOUSINGS

Also in the Series | AMP CT



Connector Contacts(8)



Connector Hardware(46)




PCB Headers & Receptacles(756)



Rectangular Connector Housings(72)




[Rectangular Power Connectors\(906\)](#)



[Standard Rectangular Connectors\(158\)](#)




[Wire-to-Board Connector Assemblies & Housings\(97\)](#)



[Wire-to-Board Headers & Receptacles \(756\)](#)


Customers Also Bought




TE Part #176270-4
[UNIV POWER PLUG HSG 1P F/H](#)



TE Part #176765-1
[AMP LATTICE CONN 28P COVER KIT](#)



TE Part #1981379-1
[HYBRID MINI DRAWER](#)




TE Part #1-292237-0
[1.5 MINI CT H/CUR. HYBRID DRAW](#)



TE Part #2-175133-6
[CT DOUBLE ROW 26P HOLDER NATU.](#)




TE Part #3-292248-4
[1.5 MINI CT LATTICE CABLE KIT](#)




TE Part #6-292215-2
[MINI CT SGL RELAY 12P BLUE](#)



TE Part #292157-2
[CT RELAY W/COMMONING BAR 2P NA](#)



TE Part #176763-1
[AMP LATTICE 28P PLUG HSG](#)



TE Part #1-353581-2
[DRAWER CONN TAB CONT REREELING](#)

Documents

Product Drawings

[CT RELAY W/COMMONING BAR 6P NA](#)

English

CAD Files

[3D PDF](#)

English

Customer View Model

[ENG_CVM_292157-6_O.3d_igs.zip](#)

292157-6

Connector Assembly, Plug to Plug Relay Header, Wire-to-Panel, 6 Position, 2 mm [.078 in] Centerline, 1 Row, White, Signal, Panel Mount, AMP CT



English

Customer View Model

[ENG_CVM_292157-6_O.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_292157-6_O.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English