
## KEMET Part Number: T520D227M010ATE040



T520, Tantalum, Polymer Tantalum, 220 uF, 20%, 10 VDC, SMD, Polymer, Molded, Low ESR, Non-Combustible, 40 mOhms, 7343, Height Max = 3.1mm



Dimensions		
Footprint	7343	
L	7.3mm +/-0.3mm	
W	4.3mm +/-0.3mm	
Н	2.8mm +/-0.3mm	
Т	0.13mm REF	
S	1.3mm +/-0.3mm	
F	2.4mm +/-0.1mm	
Α	3.6mm MIN	
В	0.5mm +/-0.15mm	
Р	0.9mm REF	
R	1mm REF	
Х	0.1mm +/-0.1mm	

General Information		
Series:	T520	
Dielectric:	Polymer Tantalum	
Style:	SMD Chip	
Description:	SMD, Polymer, Molded, Low ESR, Non-Combustible	
Features:	Low ESR	
RoHS:	Yes	
Termination:	Tin	
Shelf Life:	52 Weeks	
MSL:	3	

Specifications		
Capacitance:	220 uF	
Capacitance Tolerance:	20%	
Voltage DC:	10 VDC (105C)	
Temperature Range:	-55/+105C	
Rated Temperature:	105°C	
Humidity:	60C, 90% RH, 500 Hours, No Load	
Dissipation Factor:	10.00% 120Hz 25C	
Failure Rate:	N/A	
Resistance:	40 mOhms (100kHz 25C)	
Ripple Current:	2400 mA (100kHz 45C), 1680 mA (85C), 600 mA (105C)	
Leakage Current:	220 uA (5min 25C)	

Packaging Specifications		
Weight:	434.83 mg	
Packaging:	T&R, 178mm	
Packaging Quantity:	500	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

