

SACC-DSI-M12FSL-4FE-M16XL-L180 - Device connector rear mounting



1415338
<https://www.phoenixcontact.com/gb/products/1415338>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, Power, 5-position, Socket, straight, M12, coding: L, Rear mounting, M16 x 1.5, Wave soldering, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239091

Your advantages

- Easy PCB assembly: one-piece connectors for wave soldering
- For compact devices: transmit high power in a confined space
- Easy-to-install, optimized XL housing contour with wrench size 19
- Mechanical tightening limitation for long-term-stable gasket

Commercial data

Item number	1415338
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	ABQEHN
Product key	ABQEHN
GTIN	4055626055794
Weight per piece (including packing)	18.135 g
Weight per piece (excluding packing)	17.322 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSI-M12FSL-4FE-M16XL-L180 - Device connector rear mounting



1415338

<https://www.phoenixcontact.com/gb/products/1415338>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Notes on operation	FE not connected to metal parts that can be touched, no protective function
Order information:	Lock nut is included in the scope of delivery

Mounting

Mounting type	Rear mounting M16 x 1.5 With flat nut
Assembly note	With flat nut

Product properties

Product type	Circular connectors (device side)
Application	Power
Sensor type	Power
Number of positions	5
Connection profile	4+FE
No. of power contacts	4
Shielded	no
Coding	L
Thread type	M12

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Rated voltage in acc. with IEC 61076-2-101	630 V
Rated surge voltage	1.5 kV
Nominal voltage U_N	63 V DC

SACC-DSI-M12FSL-4FE-M16XL-L180 - Device connector rear mounting



1415338

<https://www.phoenixcontact.com/gb/products/1415338>

Nominal current I_N	16 A
-----------------------	------

Connection data

Conductor connection

Connection method	Wave soldering
Contact connection type	Socket

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	L

Cable/line

Signal type/category	Power
----------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
	IP65/IP67
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
	-40 °C ... 85 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-111


SACC-DSI-M12FSL-4FE-M16XL-L180 - Device connector rear mounting

1415338

<https://www.phoenixcontact.com/gb/products/1415338>

Drawings

Schematic diagram



Pin assignment of M12 socket, 5-pos., L-coded, socket side view


SACC-DSI-M12FSL-4FE-M16XL-L180 - Device connector rear mounting



1415338
<https://www.phoenixcontact.com/gb/products/1415338>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1415338>

	cULus Recognized Approval ID: E468743-20180113			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	63 V	16 A	-	-

SACC-DSI-M12FSL-4FE-M16XL-L180 - Device connector rear mounting



1415338

<https://www.phoenixcontact.com/gb/products/1415338>

Classifications

ECLASS

ECLASS-13.0	27440110
-------------	----------

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSI-M12FSL-4FE-M16XL-L180 - Device connector rear mounting



1415338

<https://www.phoenixcontact.com/gb/products/1415338>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	0cd0c1a3-3429-4356-88cc-fdc633ec431c

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk