







EX260, Integrated Type (For Output) Serial Transmission System EX260-SPL1

Datasheet

- Centralised & compact serial transmission system for output
- Compatible protocols: Ethernet POWERLINK, PROFINET, EtherNet/IPTM, EtherCAT®, PROFIBUS DP, DeviceNetTM, CC-Link, IO-Link, CANopen, Modbus, AS-Interface
- Up to 32 solenoids, up to 24 stations
- Applicable valve series: new SY, VQC, S0700, SV
- Up to IP67 enclosure compliant.

Protocol	PL (EtherNet POWERLINK)
Output Polarity/Communication Connector	1 [32 Outputs, -COM (PNP), M12 Connector]
Maximum ambient temperature	50 °C
Minimum ambient temperature	-10 °C
General power supply	24 VDC
Conform to the European RoHS Directive	Conform
Approvals	CE marking, UL (CSA) compatible
Operating humidity range	35 to 85% RH (No condensation)
Type of electrical connector	M12
Version	EPSP DS 301 Version 1.2.0
Number of outputs	32
SI unit output polarity	Source/PNP (Negative common)
Communication speed	100 Mbps
Enclosure	IP67
Weight	0.200 Kg

Dimensions



Additional information

Catalogue

[EX260-C_EU.pdf](#)