

AI 0,25-8 VT - Ferrule



2100147

<https://www.phoenixcontact.com/gb/products/2100147>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, Length contact range: 8 mm, sleeve length: 12.5 mm, color: violet

Your advantages

- The AI 0,25.. ferrules can also be used to process 0.14 mm² conductors
- The AI 0,25.. ferrules can also be used to process 0.14 mm² conductors

Commercial data

Item number	2100147
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BH3411
Product key	BH3411
GTIN	4067923213135
Weight per piece (including packing)	0.058 g
Weight per piece (excluding packing)	0.058 g
Customs tariff number	85369010
Country of origin	DE

AI 0,25-8 VT - Ferrule

2100147

<https://www.phoenixcontact.com/gb/products/2100147>

Technical data

Product properties


Product type	Cable end sleeve
Product property	UL certified
	Made from soft tin-plated electrolytic copper
	Correspond to the requirements of DIN 46228-1 and UL 486F in terms of size
	Plastic collar made of polypropylene
	Halogen-free
	Long/short-term temperature: +105°C/+120°C

Connection data

Conductor connection

Conductor cross section flexible max.	0.25 mm ²
Conductor cross section AWG max.	24
Stripping length	10 mm

Dimensions

Dimensional drawing	
Sleeve length	12.5 mm
Length contact range	8 mm
Maximum stripping length	10 mm
Ferrule diameter	0.8 mm
Sleeve wall thickness	0.15 mm
Insulating collar thickness	0.25 mm
Inner dimensions of the insulating collar	2 mm

Material specifications

Color	violet (RAL 4005)
Material	CU-DHP
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen

Mechanical properties

Technical data

Sleeve length	12.5 mm
---------------	---------

AI 0,25-8 VT - Ferrule



2100147

<https://www.phoenixcontact.com/gb/products/2100147>

Environmental and real-life conditions

Ambient conditions


Permanent temperature	105 °C (-40 °C no load / 0 °C dynamic load)
Short-term temperature	120 °C

Standards and regulations

Design according to standard	Special color
------------------------------	---------------

Drawings

Dimensional drawing



Sleeve length (b), length contact range (h), insulating collar inner dimension (d), sleeve diameter (k), insulating collar thickness (i), sleeve wall thickness (j)


AI 0,25-8 VT - Ferrule



2100147

<https://www.phoenixcontact.com/gb/products/2100147>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2100147>



cULus Listed

Approval ID: E488001

AI 0,25-8 VT - Ferrule



2100147

<https://www.phoenixcontact.com/gb/products/2100147>

Classifications

ECLASS

ECLASS-13.0	27400201
-------------	----------

ETIM

ETIM 9.0	EC000005
----------	----------

AI 0,25-8 VT - Ferrule



2100147

<https://www.phoenixcontact.com/gb/products/2100147>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk