



**FAG****62304-A-2RSR-C3**

Deep groove ball bearing

Deep groove ball bearing 623...-A-2RSR,  
single row, steel sheet metal cage

## Technical information



## Your current product variant

Changed internal design	A	Design variant A
Sealing	2RSR	Contact seal on both sides
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Lubricating grease	
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Bore type	Z	Cylindrical

## Main Dimensions &amp; Performance Data

d	20 mm	Bore diameter
D	52 mm	Outside diameter
B	21 mm	Width
C <sub>r</sub>	15,940 N	Basic dynamic load rating, radial
C <sub>0r</sub>	7,880 N	Basic static load rating, radial
C <sub>ur</sub>	560 N	Fatigue load limit, radial
n <sub>G</sub>	8,900 1/min	Limiting speed
≈m	0.2 kg	Weight



Mounting dimensions

$d_{a\ min}$	27 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	45 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	1 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1.1 mm	Minimum chamfer dimension
$D_1$	42.2 mm	Shoulder diameter outer ring
$D_2$	45.1 mm	Caliber diameter outer ring
$d_1$	30 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

Calculation factors

$f_0$	12.4	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides