



## Main

Network rated voltage	400 V AC 50 Hz 415 V AC 50 Hz
Reactive power rating	50 kvar
Operating mode	Fixed
Range	PowerLogic
Device short name	fixed capacitor bank with detuned reactor
Product or component type	Capacitor bank






## Complementary

Network pollution level	Polluted
[Gh/Sn] harmonic pollution rate	25...50 %
[THDU] total harmonic distortion of voltage	4...7 %
Tuning factor	4.2
Tuning frequency	210 Hz
Power per step	50 kvar
Step composition	50
Location of connection	Bottom
Capacitor technology	PowerLogic PFC Capacitor + Detuned Reactor
Poles description	3P
Capacitance tolerance	- 5 % to 10 %
[Ui] rated insulation voltage	690 V
[Uimp] rated impulse withstand voltage	8 kV
Maximum permissible voltage	1.1 x Un (8 hours over 24 hours) conforming to IEC 60831
[Imp] maximum permanent current	Capacitor: 1.8 x In at 480 V conforming to IEC 60831 Battery: 1.31 x In at 400 V conforming to IEC 61439-2 Battery: 1.19 x In at 415 V conforming to IEC 61439-2
Main incomer protection	Circuit breaker protection
Breaking capacity	Icu 50 kA
Control type	Rotary handle
Accessibility for operation	Front
Colour	Grey (RAL 7035)
Maximum weight	320 kg
Height	1400 mm
Width	800 mm
Depth	600 mm
Provided equipment	Auxiliary transformer
Internal voltage transformer	400/230 V - 100 VA
Function available	GenSet shedding contact Alarm contact

## Environment

Standards	IEC 61439-2 IEC 61921 IEC 61439-1
Product certifications	EAC[RETURN]ASEFA[RETURN]CE
Mounting location	Indoor
IP degree of protection	Environment: IP31 Safety: IPxx B
IK degree of protection	IK10
Relative humidity	0...95 %
Operating altitude	<= 2000 m
Ambient air temperature for operation	-5...45 °C
Average ambient air temperature for operation	35 °C (annual) 45 °C (over 24 hours)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins