3-640602-5 ✔ ACTIVE


MTA 156

TE Internal #: 3-640602-5


5 Position, Receptacle, Connector Assembly, Insulation Displacement (IDC), Wire-to-Board, Tin (Sn), UL 94V-2, 3.96 mm [.156 in] Centerline, MTA 156

View on TE.com >

Connectors > Rectangular Connectors > Standard Rectangular Connectors







Connector Product Type: **Connector Assembly**

Mating Alignment: **Without**

Connector & Housing Type: **Receptacle**

Mating Retention Type: **Locking Ramp**

Connector System: **Wire-to-Board**

Features

Product Type Features

Compatible With Discrete Wire Type	Stranded
Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	5
Number of Rows	1
Number of Power Positions	5

Electrical Characteristics

Operating Voltage	600 VAC

Body Features

Primary Product Color	White

Cable Exit Angle	90 °

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	30 µm[.762 µin]
Contact Layout	Inline
Contact Base Material	Copper Alloy
Wire Contact Termination Area Plating Thickness	2.03 – 5.08 µm[80 – 200 µin]
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material	Tin (Sn)
Contact Retention Within Housing	With
Contact Current Rating (Max)	7 A
Contact Type	Receptacle
Wire Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	2.03 µm[80 µin]

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)

Mechanical Attachment

Strain Relief	With
Panel Mount Feature	Without
Contact Retention Type Within Housing	Locking Lance
Mating Alignment	Without
Mating Retention Type	Locking Ramp
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Wire & Cable IDC Installation Type	Feed Through
Centerline (Pitch)	3.96 mm[.156 in]
Housing Material	Nylon

Dimensions

Compatible Insulation Diameter Range	2.41 mm[.095 in]
Connector Height	9.78 mm[.385 in]
Connector Length	19.81 mm[.78 in]

Wire Size	.2 mm²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Circuit Application	Power & Signal

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
CSA Rating	Certified, LR 7189
UL Flammability Rating	UL 94V-2
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	250
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products

will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 3-644617-5
05P MTA156 HDR ASY PO RA FB LF




TE Part # 59804-1
MAINTENANCE TOOL




TE Part # 640643-5
05P MTA156 COVER F/T




TE Part # 644751-5
05P MTA156 HDR ASSY R/A




TE Part # 644749-5
05P MTA156 HDR ASSY STR SQ SN




TE Part # 643071-5
05P MTA156 FD-THRU COVER



TE Part # 640388-5
05P MTA156 HDR ASSY RN STR F/L



TE Part # 58443-1
MTA 156 CRIMP HEAD PRODUCTION FEED THRU



TE Part # 644752-5
05P MTA156 HDR ASSY SQ STR F/L




TE Part # 643495-4
05P MTA156 HDR ASSY W/O#3




TE Part # 2-647125-5
05P MTA156 SHRD HDR ASSY LF



TE Part # 2-647127-5
05P MTA156 SHRD HDR ASSY LF




TE Part # 644753-5
05P MTA156 HDR ASSY RN STR F/L



TE Part # 640551-5
05P MTA156 COVER




TE Part # 58074-1
MTA 50/100/156 MANUAL TOOL FRAME




TE Part # 643495-2
05P MTA156 HDR ASSY W/O#2&4




TE Part # 2-647123-5
05P MTA156 SHRD HDR ASSY SQ SN



TE Part # 3-644611-5
05P MTA156 HDR POL WO PEGS LF



TE Part # 3-644613-5
05P MTA156 HDR RA PO WO PEG LF



TE Part # 3-644615-5
05P MTA156 POL HDR ASSY LF


Also in the Series | MTA 156



Connector Caps & Covers(89)




Connector Contacts(4)



Connector Hardware(2)



Insertion & Extraction Tools(1)




PCB Headers & Receptacles(677)



Power Contacts(3)




Rectangular Power Connectors(1178)



Wire-to-Board Headers & Receptacles (677)

Customers Also Bought




TE Part #195271-000
RT-1145-OX-27-0




TE Part #205209-7
RECP ASSY SIZE 4



TE Part #205842-1
CPC PLUG ASSEMBLY SIZE 23-63




TE Part #207473-1
CABLE CLAMP KIT,SZ 4



TE Part #640384-4
04P MTA156 HDR ASSY STR RND SN




TE Part #1-640385-0
10P MTA156 HDR ASSY SQ R/A



TE Part #4-640601-0
10P MTA156 CONN ASSY 22AWG LF



TE Part #3-640602-4
04P MTA156 CONN ASSY 24AWG LF



TE Part #1586315-1
VAL-U-LOK SKT BR SN 24-18 LP



TE Part #5205208-1
CRIMP SNAP PLUG ASSY, 25 POS

Documents

Product Drawings

05P MTA156 CONN ASSY 24AWG LF

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-640602-5_V.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-640602-5_V.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-640602-5_V.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_3-640602-5_Z.3d_igs.zip

English

Customer View Model

ENG_CVM_3-640602-5_Z.3d_stp.zip

English

Customer View Model

ENG_CVM_3-640602-5_Z.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

English

Application Specification

Japanese

Application Specification

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

Japanese

Agency Approvals

Agency Approval Document

English