




Connectors > Connector Accessories > Heat Sinks



Device Type: BGA

Fin Style: Radial Fin

Number of Fins: 2

Power Rating: 5 W, 10 W, 15 W

Features

Product Type Features

Device Type	BGA
-------------	-----

Configuration Features

Number of Fins	2
----------------	---

Electrical Characteristics

Power Rating	5 W, 10 W, 15 W
--------------	-----------------

Body Features

Primary Product Material	Aluminum
Primary Product Plating Material	Black Anodized
Fin Style	Radial Fin

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2025
(250)

Candidate List Declared Against: JAN 2021
(211)

SVHC > Threshold:

Pb (.33% in Component Part)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | ALCOSWITCH PKA



Switch Knobs(4)

Also in the Series | CGS HS



Automotive Housings(1)




Automotive Signal & Power Connector Housings(1)



Card Edge Connector Housings(1)




Chassis Mount Resistors(1069)



FFC Connectors(1)

Customers Also Bought



TE Part #CAT-C8114-F299A
Single Phase Filters, Corcom FB Series



TE Part #2321926-3
RECEPTACLE HOUSING PANEL MOUNT 3PIN



TE Part #2364569-1
AVH19 FLT SS MT NO LED 26A



TE Part #2364570-8
AVH19 FLT SS LK RNG RED 24V16A



TE Part #1-2364570-9
AVH19 FLT SS MT RNG BLU 24V16A



TE Part #2364684-1
AVH22 FLT SS MT NO LED 16A



TE Part #6609020-8
5EB3=F7105 S0



TE Part #6609027-3
2EK1=F7083 S0

Documents

Product Drawings

[HTS191-P=25MM HS ASSY PPA CLIP](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_5-1542000-6_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-1542000-6_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-1542000-6_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

