



## Datasheet

# RS 899-8494 - LED Flood - 200W

ENGLISH

### Features

LED flood lights - the future of energy-saving illumination for global industrial applications. It is over 50% more energy-efficient than traditional light. It has low maintenance cost and low emissions of CO<sup>2</sup>. With its cutting-edge technology and unique optical design, its performance is much better than traditional lights.

- Flexible modular design.
- Advanced air flow thermal management.
- 0~265°rotatable
- Surface coating treatment, can withstand extreme weather conditions.
- IP65

### Technical Parameters


- Input Voltage: AC100-277V /50/60Hz
- Max Current: 2.3A
- LED type: Bridgelux(COB)
- Output Power: 200W
- Shell color: Black as standard / White on request
- Net weight: 8.4 KG
- Gross weight:9.5 KG
- Inner box size: 490\*390\*170mm (1PCS per box)



### Applications

- Bars, restaurants, clubs, hotels and stages
- Historical and modern buildings
- Museums and art galleries
- Sculptures and plastic arts

## 5 Year Warranty






## Specification

ENGLISH

Model	CCT	LED Type	Lumens (±10%)	CRI	Beam Angle	Power (W) (±10%)	Voltage (V)	PF	Weight (KG)
112206	4000K - 4500K	COB	15550	≥70	120°	200	AC100-277V 50/60Hz	≥0.9	8.4

## Dimensions (Unit mm)



0-265° rotatable

## Installation

