

Eaton 136169

Catalog Number: 136169

Eaton Moeller® series E57 Proximity switch, E57 Premium+ Short-Series, 1 NC, 2-wire, 40 - 250 V AC, 20 - 250 V DC, M30 x 1.5 mm, Sn= 15 mm, Non-flush, NPN/PNP, Stainless steel, 2 m connection cable

General specifications



Product Name	Catalog Number
Eaton Moeller® series E57 Proximity switch	136169
	EAN
	4015081329625
Product Length/Depth	Product Height
157.48 mm	50.8 mm
Product Width	Product Weight
127 mm	0.25 kg

Certifications

UL Category Control No.: NRKH, NRKH7

CSA
CE
CSA-C22.2 No. 14
UL 508
UL File No.: E166051
CSA File No.: 50513
UL
CSA Class No.: 3211-03
IEC/EN 60947-5-2

Product specifications

Type

Inductive sensor

Electric connection type

Cable

Enclosure material finishing

Other

Actuation type

Metallic Target

Enclosure material

Metal

Enclosure type

Cylinder, screw-thread

Category (EN 954-1)

B

Explosion safety category for dust

None

Explosion safety category for gas

None

Safety performance level (EN ISO 13849-1)

None

SIL (IEC 61508)

None

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-25 °C

Diameter sensor

30 mm

Number of contact energized outputs with signalling function

0

Number of contacts (normally closed contacts)

1

Number of outputs (protected contact energized)

0

Resources

Brochures

[eaton-sensors-brochure-br053001en-en-us.pdf](#)

Catalogs

[Product Range Catalog Sensors – products, basic information, applications](#)

Declarations of conformity

[DA-DC-00004656.pdf](#)

[DA-DC-00004651.pdf](#)

Drawings

[1360DRW-93](#)

Installation instructions

[IL05301003Z](#)

Multimedia

[We make what matters](#)

Number of outputs (protected semiconductor)

0

Number of outputs (semiconductor with signaling function)

1

Output current at protected output - max

0 mA

Rated control supply voltage (Us) at AC, 50 Hz - max

250 V

Voltage type

AC

Mounting method

Non-flush mounting

Material

Stainless steel

Connection type

2-wire

2 m connection cable

Installation type

Not flat

Degree of protection

IP67

NEMA 4X, 6, 13

Interface type

None

LED indicator

Status indication of Switching state: Red LED

Switch function type

Breaker contact

Load current

5 - 250 mA (I_e, at 25 °C)

5 - 200 mA (I_e, 70 °C)

Residual current

2 mA (through the load in the blocked state at 230 V AC and 24 V DC)

Shock resistance

30 g, Mechanical, Shock duration 11 ms

Switching frequency

20 Hz

Voltage rating - max

250 V

Width sensor

0 mm

Product category

E57 Premium+ Short-Series

Switching output type

PNP/NPN

Temperature drift of sn

10 %

Rated control supply voltage (Us) at AC, 50 Hz - min

20 V

Rated control supply voltage (Us) at AC, 60 Hz - max

250 V

Rated control supply voltage (Us) at AC, 60 Hz - min

20 V

Rated control supply voltage (Us) at DC - max

0 V

Rated control supply voltage (Us) at DC - min

0 V

Rated switching distance (Sn) - max

15 mm

Repeatability

3 %

Sensor height

0 mm

Sensor length

45 mm

Supply voltage - max

250 V

Supply voltage - min

20 V

Switching hysteresis of Sn

20 %

Voltage drop (Ud)

12 V



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)