



WAGO-I/O-CHECK is an easy-to-use Windows application for operating and displaying a WAGO I/O System 750's node without connecting to a fieldbus system. The software reads the configuration from the node and displays it graphically on the screen. This graphic can be printed together with a configuration list as documentation. With WAGO-I/O-CHECK, it is possible to display and specify the process data of the I/O modules. The field wiring, including all sensors and actuators, can thus be checked before startup. For some types of interface, Pt100 and thermocouple modules, application-specific settings can be made, such as the baud rate or sensor types. The coupler must be connected to a free serial or USB port of the PC using the communication cable supplied in the set with the system to enable communication between WAGO-I/O-CHECK and the node.

System requirements	
Supported operating systems	Windows 7 Windows 10
Processor	1 GHz or higher, with 32 bits (x86) or 64 bits (x64)
Memory	Min. 1 GB RAM 2 GB RAM or more (recommended)
Hard disk space	min. 150 MB
Graphics resolution	1024 x 786 (min.), 1280 x 1024 or higher (recommended)

Delivery	
Delivery type	Installation file (CD-ROM)
Scope of delivery	CD-ROM with software and USB communication cable (750-923)

Commercial data	
eCl@ss 10.0	27-24-25-90
eCl@ss 9.0	27-24-25-90
ETIM 8.0	EC001435
ETIM 7.0	EC001435
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454877583
Customs tariff number	85234920009



Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 759-302/000-923	

Documentation

Manual			
Product Manual WAGO-I/O-CHECK Commissioning Tool for WAGO-I/O-SYSTEM 750	V 1.2.0	pdf 1158.70 KB	

System Description			
Software – General Product Information		pdf 368.80 KB	

Bid Text			
759-302/000-923	19.02.2019	xml 4.80 KB	
759-302/000-923	10.01.2019	docx 16.33 KB	