

Product data sheet

Specifications



Floor-Standing Server Rack 24U W600D1000 Fixed 19" Perf. Door R9011

NSYVDS24U610N

Main

Range	Actassi
Product name	Actassi VDS
Product or component type	19" enclosure
Device application	Server
Applications	To mount server components To protect network connectivity equipment To mount 19" equipment
Enclosure type	Server cabinet
Support equipment	4 x 19" uprights recessed of 120 mm from the front (pitch 25 mm)
Front face	Microperforated door
Door type	Front microperforated door - with 2 points locking system (key: 333) - reversible opening at 180 ° Rear microperforated door - with 2 points locking system (key: 333) - reversible opening at 180 °
Accessibility for operation	Front Top Rear Side
Removable parts	Front door removable toolless Bottom blanking plate Rear door removable toolless Top blanking plate equipped with brush gasket Side panels
Colour	Door: black (RAL 9011) Panels: black (RAL 9011) Top and bottom: black (RAL 9011) Structure: black (RAL 9011)

Complementary

Device composition	2 x panels side 1 x assembled structure CBLX torx 1 x roof with removable blanking plate top 4 x levelling feets 4 x 19" uprights 1 x microperforated door (airflow 80%) front 1 x microperforated door (airflow 80%) rear
Load rating	750 kg static
Back face	Microperforated door
Side face	Panel
Number of cut-out	1 cut-outbottom 1 cut-outtop side panel 1 cut-outtop - split in 3 parts
Installation mode	Floor-standing

Material	Sheet steel: structure Sheet steel: door Sekurit glass: door Galvanized steel: upright Sheet steel: panel
Surface finish	Epoxy-polyester powder
Width	600 mm
Height	1200 mm
Depth	1000 mm
Net weight	82 kg
Number of rack unit	24U
Targeted region	Europe

Environment

IK degree of protection	IK08 conforming to IEC 62262
IP degree of protection	IP20 conforming to IEC 60529
Standards	EIA-310D IEC 60297-3-100

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	80.0 kg
Package 1 Height	133 cm
Package 1 width	69 cm
Package 1 Length	105 cm
Unit Type of Package 2	PAL
Number of Units in Package 2	1
Package 2 Weight	80.0 kg
Package 2 Height	133 cm
Package 2 width	69 cm
Package 2 Length	105 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------