Product datasheet

Specifications



energy meter, PowerLogic EM3712, 1-5Amps current transformer, class 0.5S / class 1, pulse output

METSEEM3712

EAN Code: 3606487294733

Main

Range	PowerLogic
range of product	PowerLogic EM3000
Product or component type	Energy meter
Device short name	EM3712

Complementary

Poles description	3P + N 1P + N 3P
Type of measurement	Active energy total Active energy per phase Active energy partial
Metering type	Active energy (signed, two quadrant)
Device application	Partial meter Sub billing
Accuracy class	Class 1 active energy conforming to IEC 62053-21 Class 0.5S active energy conforming to IEC 62053-21
input type	Current transformer 1 A or 5 A
[In] rated current	5 A 1 A
Rated voltage	100…277 V 173…480 V
Network frequency	60 Hz 50 Hz
Technology type	Electronic
Display type	LCD display
Sampling rate	32 samples/cycle
Measurement current	1…32767 A
Maximum value measured	99999999.9 MWh
Communication port protocol	-
Local signalling	Green indicator light: power ON Yellow flashing LED: accuracy checking
Number of outputs	1 pulse
mounting mode	Clip-on
Mounting support	DIN rail
Connections - terminals	Current circuit: screw terminals 6 mm² cable(s) Voltage circuit: screw terminals 2.5 mm² cable(s)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Overvoltage category	III
Standards	BS EN 61557-12:2021 IEC 61557-12:2021 EN 61557-12:2021 BS EN 61326-1 IEC 61326-1 EN 61326-1 BS EN 62052-11:2020 IEC 62052-11:2020 EN 62052-11:2020 BS EN 62053-21 IEC 62053-21 EN 62053-21 BS EN 62052-31:2015 IEC 62052-31:2015 EN 62052-31:2015 BS EN 61010-1:2010 EN 61010-1:2010 IEC 61010-1:2010 BS EN 61010-2-30 IEC 61010-2-30 EN 61010-2-30 UL 61010-2-30 ANSI C12.20
Product certifications	CE conforming to IEC 61010-1 (safety) CE conforming to EN 61557-12 (power monitor) CE conforming to EN/IEC 61326-1 (EMC) UKCA conforming to BS EN 61010-1 (safety) UKCA conforming to BS EN 61557-12 (power monitor) UKCA conforming to BS EN 61326-1 (EMC) CULus conforming to UL 61010-1 (safety) CULus conforming to EN 61010-1 (safety)

Environment

IP degree of protection	IP40 front panel: conforming to IEC 60529 IP20 body: conforming to IEC 60529
Pollution degree	2
Relative humidity	5…95 % at 50 °C
Ambient air temperature for operation	-25…70 °C - IEC
Ambient air temperature for storage	-40…85 °C
Operating altitude	< 2000 m
Colour	White
9 mm pitches	10
Width	90 mm
Height	95 mm
Depth	69 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.500 cm
Package 1 Width	9.500 cm
Package 1 Length	10.500 cm
Package 1 Weight	326.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	25

Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.592 kg

Logistical informations

Country of origin	CN

Contractual warranty

Warranty (in months)	18

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Total lifecycle Carbon footprint	**35 kg CO2 eq.**
Carbon footprint of the manufacturing phase [A1 to A3]	**10 kg CO2 eq.**
Carbon footprint of the distribution phase [A4]	**0.8 kg CO2 eq.**
Carbon footprint of the installation phase [A5]	**0 kg CO2 eq.**
Carbon footprint of the use phase [B2, B3, B4, B6]	**24 kg CO2 eq.**
Carbon footprint of the end-of-life phase [C1 to C4]	**0.7 kg CO2 eq.**
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	**No**
Packaging without single use plastic	**No**
EU RoHS Directive	Compliant By Exemption
REACh Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer

Lifetime extension

Repair	**No**

Use Again

Repack and remanufacture

Recyclability potential, in %	**21**
End of life manual availability	End of Life Information
Take-back	**No**
WEEE Label	**The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins**