

RoHS Compliant

REV	SIGN	DATE	DESCRIPTION	APPROVED
A		2023.12.19	Initial Release	Yours
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

Material:

- Item ④ Terminal Body: PA66,
- Item ⑤ Terminal lever: PBT ,
- Item ⑥ Terminal Cover: PA66 ,
- Item ⑦ Spring: Stainless
- Item ⑧ Terminal Contact: Copper alloy.

Electrical:

UL1059 Group B.G Group D Group F

- | | | | |
|---------------------------|------------------|------|------|
| ● Voltage rating: | 300 V | 300V | 250V |
| ● Current rating: | 16A | 10A | 16A |
| ● Wire range: | | | |
| Solid wire: | 24-12AWG | | |
| Stranded wire: | 24-12AWG | | |
| ● Wire strip length: | 11-13 mm | | |
| ● Withstanding Voltage: | 1.6KV AC | | |
| ● Insulation Resistance: | DV500V 500MΩ min | | |
| ● Operating temperature: | -20°C to +105°C | | |
| ● Assembling temperature: | -5°C to +105°C | | |
| ● Safety Approval: | CE, RoHS | | |

Part No. QT xx A SB x x H xxxx G

NO. OF POLES
02: 2 POLES
03: 3 POLES
... ..
24: 24 POLE

RoHS compliant
(lead<4%)
In copper Alloy





00x0: "@ " Logo (Standard)
00xA: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

Body color

0: Black
1: Natural color
2: Red
3: Orange
4: Yellow
5: Green (RAL6005)
6: Blue
8: Grey (標準色)
9: White
C: Green
(RAL 6018/U)

Lever color

0: Black
1: Natural color
2: Red
3: Orange (標準色)
4: Yellow
T) 5: Green (RAL6018/T)
6: Blue
8: Grey
9: White
C: Green
(RAL 6018/U)



Amphenol **ANYTEK**

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		QT series pitch 5.0mm PCB terminal block,							
PART NO.		QTxxASBxxHxxxxG				DWG NO.		8QT0003	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance		
Roy 2024.11.07		Roy 2024.11.07		Yours 2023.12.19				UNIT: mm	X. ±0.50
								SCALE: 2:1	X.X ±0.30
								SHEET: 01/01	X.XX ±0.10
						REV: A0	X° ±1°		