

Drill Driver LXT®

DDF485

18V • 50 Nm • 0 – 1 900 min⁻¹

A powerful, brushless general-use drill for screwdriving and drilling

A powerful brushless tool with two speeds for screwdriving and drilling for professional use. Max. torque of 50 / 25 Nm. A versatile tool for fitters, builders and maintenance staff. Integrated LED light.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Brushless Motor	✓
No load speed	0 - 500 / 0 - 1900 min ⁻¹
Max. fastening torque Hard/Soft	50 / 27 Nm
Max Torque	60 Nm
Torque setting	21
Max. Drilling Diameter in Wood	38 mm
Max. Drilling Diameter in Steel	13 mm
Driving Shank	1/2"-20UNF "
Drill Chuck Capacity	1,5 - 13 mm
Drilling Capacity Wood (Auger Bit)	38 mm
Drilling Capacity Wood (Self-feed bit)	76 mm
Vibration Level, Drilling into metal	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Drilling into metal	1,5 m/s ²
Sound Pressure Level (L _{pA})	77 dB(A)

User benefits

- Low power consumption thanks to brushless motor
- All metal gear construction ensures high transmission durability
- The rubber coating on the handle ensures a firm working grip
- LED light illuminates the work site
- Battery protection system automatically shuts off power when the battery level is low
- Electronic overload protection protects the user and the device
- Mechanical 2-speed gearing; High speed mode for speedy drilling in light duty applications; Low speed mode for heavy duty applications requiring high torque
- Highly efficient and compact machine for professional use

Link to product - www.makitauk.com



Related products

Optional AC

821550-0

Makpac case (2)



837916-4

MakPac (2) Inlay



B-49432

Drill Bit Set, TCT, M-Force, 18 pcs



D-42204

COUNTERSINK 6PC SET



D-47363

Forstner Drill Bit Set, 5 pcs



E-07076

Screw bit set 32 pcs



E-08698

Flat bit set 8 pcs



Other

User manual

Parts drawing