


Tricopren® 723



APPLICATION

- › removal of contaminated parts from dipping baths
- › handling of contaminated heavy parts
- › cleaning and maintenance in chemical plants
- › chemical industry
- › working with oily and greasy parts

QUALITIES AND ADVANTAGES

- › broad chemical resistance
- › high mechanical resistance
- › sure grip when handling wet parts due to palm profile
- › high user comfort for long working periods without operator fatigue
- › flexible in warmth and cold
- › good dexterity

CHEMICAL PROTECTIVE GLOVES



Article no.	723
Name	Tricopren® 723
Material	chloroprene, cotton
Description	seamless cotton liner cuff, fully coated, palm profile
Length (mm)	290 - 310
Total thickness (mm)	1,3 ± 0,2
Coating thickness (mm)	0,4
Colour	grey
Size	8, 9, 10, 11
Classification	category III
	<div> <div>EN 388:2016</div> <div>2121X</div> </div> <div> <div>EN 374-1/Type A</div> <div>AJ KLMS</div> </div> <div> <div>EN 374-5</div> <div>Virus</div> </div>



FEATURES

- › AQL < 0,65
- › free from natural latex
- › seamless cotton liner
- › cotton liner is fixed later to the finished glove to ensure maximum protection



www.kcl.de
sales@kcl.de



by Honeywell

KCL GmbH

Industriepark Rhoe
Am Kreuzacker 9
36124 Eichenzell
Germany
Phone +49 6659 87-300
Fax +49 6659 87-318

Honeywell