

## CPG1500 0...700 bar gauge G 1/2 B

### CPG1500 0...700 bar gauge G 1/2 B

Item number: 46885349

Quantity: 1 pcs.

Order code: CPG1500-ST-Z-S-BG570-GDTZ-53-CLHZ-Z-ZZZZ Z W  
CERT-PR-DE1-AP03C1C-Z-C12-ZZ-Z 1

Overview: CPG1500 0...700 bar gauge G 1/2 B  
Precision digital pressure gauge - Model CPG1500  
Specifications according to data sheet: CT 10.51  
Explosion protection: without  
Measuring range: 0...700 bar gauge  
Process connection: G 1/2 B  
Wetted parts: stainless steel, Elgiloy Sensor  
Accuracy: 0.05 % FS  
Type of certificate: Acceptance test certificate 3.1 in accordance with DIN EN 10204  
Communication: Bluetooth®  
Info Bluetooth®: Please bear in mind the relevant radio approvals in your country.  
Integrated data logger  
incl. protective housing cap

#### Calibration of pressure measuring instruments

Type of certificate: Acceptance test certificate 3.1 in accordance with DIN EN 10204  
Type of device under test: Electrical measuring device with display (digital pressure gauge, pressure controller, etc.)  
Accuracy: > 0,02 % ... < 0,1 %  
Numbers of measurement series: 2  
Number of measuring points per measurement series: 9  
Pressure type - pressure: Relative pressure (over- or underpressure)  
Calibration range - pressure: > 400 bar ... <= 1.600 bar

#### Documentation: Calibration (documentation of the values)

1. Language of certificate: DE
2. Language of certificate: GB

Details: CPG1500 0...700 bar gauge G 1/2 B  
Precision digital pressure gauge - Model CPG1500  
Specifications according to data sheet: CT 10.51  
Explosion protection: without  
Measuring range: 0...700 bar gauge  
Process connection: G 1/2 B  
Wetted parts: stainless steel, Elgiloy Sensor  
Accuracy: 0.05 % FS

Type of certificate: Acceptance test certificate 3.1 in accordance with DIN EN 10204

Communication: Bluetooth®

Info Bluetooth®: Please bear in mind the relevant radio approvals in your country.

Integrated data logger

incl. protective housing cap

Calibration of pressure measuring instruments

Type of certificate: Acceptance test certificate 3.1 in accordance with DIN EN 10204

Type of device under test: Electrical measuring device with display (digital pressure gauge, pressure controller, etc.)

Accuracy:  $> 0,02 \% \dots < 0,1 \%$

Numbers of measurement series: 2

Number of measuring points per measurement series: 9

Pressure type - pressure: Relative pressure (over- or underpressure)

Calibration range - pressure:  $> 400 \text{ bar} \dots \leq 1.600 \text{ bar}$

Documentation: Calibration (documentation of the values)

1. Language of certificate: DE

2. Language of certificate: GB