

Product datasheet

Specifications



passive filter - 32 A - 460 V - 60 Hz - for variable speed drive

VW3A46163

EAN Code: 3606480652615

Main

Product or component type	Passive filter
Product specific application	Reduction of current harmonics

Complementary

Range compatibility	Altivar Process ATV600 Altivar Process ATV900 Altivar 61 Altivar 71
[Us] rated supply voltage	480 V +/- 10 %
power supply frequency	60 Hz +/- 2 %
Quantity per drive	1 filter per drive for variable speed drive ATV61W motor: 18.5 kW/25 hp 1 filter per drive for variable speed drive ATV61H motor: 18.5 kW/25 hp 1 filter per drive for variable speed drive ATV71H motor: 18.5 kW/25 hp 1 filter per drive for variable speed drive ATV71W motor: 18.5 kW/25 hp 1 filter per drive for variable speed drive ATV650 wall mount, motor: 18.5 kW/25 hp 1 filter per drive for variable speed drive ATV630 wall mount, motor: 18.5 kW/25 hp 1 filter per drive for variable speed drive ATV950 wall mount, motor: 18.5 kW/25 hp 1 filter per drive for variable speed drive ATV930 wall mount, motor: 18.5 kW/25 hp
[In] rated current	31 A for input 32 A for output
Network number of phases	3 phases
THDI	10 % for variable speed drive ATV61H motor: 18.5 kW/25 hp 10 % for variable speed drive ATV71H motor: 18.5 kW/25 hp 10 % for variable speed drive ATV71W motor: 18.5 kW/25 hp 5 % for variable speed drive ATV61W motor: 18.5 kW/25 hp 5 % for variable speed drive ATV650 motor: 18.5 kW/25 hp 5 % for variable speed drive ATV630 motor: 18.5 kW/25 hp 5 % for variable speed drive ATV950 motor: 18.5 kW/25 hp 5 % for variable speed drive ATV930 motor: 18.5 kW/25 hp
Max current	1.5 x nominal current (duration = 60 s)
Efficiency	98 %
Thermal losses	335 W
Cos phi	1 (150 % of line current) 0.85 (75 % of line current) 0.99 (100 % of line current)
Electrical connection	A, B terminal, connection capacity: 2.5 mm² X1-1...X2-3 terminal, connection capacity: 1.5...25 mm²
Electrical insulation class	Class F
Net weight	52 kg

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

IP degree of protection	IP20 IP55 (enclosure mounting)
Vibration resistance	2 mm peak to peak (f= 5...13.2 Hz) conforming to IEC 60068-2-6 0.7 gn (f= 13.2...150 Hz) conforming to IEC 60068-2-6
Relative humidity	5...85 % without condensation
Ambient air temperature for operation	45...60 °C (with current derating 3 % per °C) 5...45 °C (without current derating)
Ambient air temperature for storage	-25...55 °C storage in original packaging -25...65 °C during transport
Operating altitude	<= 1000 m without current derating > 1000...4000 m with current derating 5 % per 1000 m
Standards	IEC 61000-3-12 IEC 61000-3-2 IEC 61000-3-4 IEC 61000-2-4 G5/4 engineering recommendation IEC 61000-2-2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	61.000 cm
Package 1 Width	60.000 cm
Package 1 Length	80.000 cm
Package 1 Weight	64.200 kg

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better


 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration

Use Again

 Repack and remanufacture	
Take-back	No

Dimensions Drawings

Dimensions



- (1) Front view
- (2) Right side view
- (3) Top view

Dimensions in mm

A	B	C	D	E1	E2	E3	F	G	H
242	330	547	594.08	145	233	145	353	378	460


Dimensions in in.

A	B	C	D	E1	E2	E3	F	G	H
9.53	12.99	21.54	23.39	5.71	9.17	5.71	13.90	14.88	18.11

Mounting and Clearance

Mounting Recommendations


Vertical Mounting Only



(1) Filter

Connections and Schema

Recommended Schema



- (1) Drive
- (2) Filter
- (3) Optional