Product datasheet

Specifications



Multi 9 - C60BPR - MCB - 1P - 20 A - C Curve - 277 V - 10 kA - UL 489

M9F52120

EAN Code: 3606481170774

Main

Range	Multi9
Product name	Multi9 C60
Product or component type	Miniature circuit-breaker
Device short name	C60BPR
Device application	Distribution
Poles description	1P
Number of protected poles	1
[In] rated current	20 A at 25 °C conforming to EN/IEC 60947-2
Network type	DC AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	3 kA Icu at 415 V AC conforming to EN/IEC 60947-2 10 kA Icu at 240 V AC conforming to EN/IEC 60947-2 20 kA Icu at 60 V DC conforming to EN/IEC 60947-2 3 kA Icu at 415 V AC conforming to GB/T 14048.2 10 kA Icu at 240 V AC conforming to GB/T 14048.2 20 kA Icu at 60 V DC conforming to GB/T 14048.2 10 kA AIR at 277 V AC conforming to UL 489 14 kA AIR at 240 V AC conforming to UL 489 14 kA AIR at 120 V AC conforming to UL 489 10 kA AIR at 60 V DC conforming to UL 489 10 kA AIR at 277 V AC conforming to CSA C22.2 No 5 14 kA AIR at 240 V AC conforming to CSA C22.2 No 5 14 kA AIR at 120 V AC conforming to CSA C22.2 No 5 10 kA AIR at 60 V DC conforming to CSA C22.2 No 5
Standards	EN/IEC 60947-2 GB/T 14048.2 UL 489 CSA C22.2 No 5
Product certifications	IEC CCC CSA UL

Complementary

[Ue] rated operational voltage	240 V AC 50/60 Hz 415 V AC 50/60 Hz 60 V DC
Magnetic tripping limit	8.5 x In +/- 20 % AC 12 x In +/- 20 % DC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Ics] rated service breaking capacity	2.25 kA 75 % conforming to EN/IEC 60947-2 - 415 V AC 7.5 kA 75 % conforming to EN/IEC 60947-2 - 240 V AC 2.25 kA 75 % conforming to GB/T 14048.2 - 415 V AC 7.5 kA 75 % conforming to GB/T 14048.2 - 240 V AC 15 kA 75 % conforming to GB/T 14048.2 - 60 V DC 15 kA 75 % conforming to EN/IEC 60947-2 - 60 V DC
[Ui] rated insulation voltage	500 V AC conforming to EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-2
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Contact position indicator	Yes
Control type	Toggle
Local signalling	ON/OFF indication
mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	2
Height	127 mm
Width	18 mm
Depth	72 mm
Colour	Grey
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Provision for padlocking	Padlockable
Connections - terminals	Ring terminal (top or bottom)
Tightening torque	2 N.m top or bottom
Earth-leakage protection	Without

Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3 conforming to EN/IEC 60947-2
Overvoltage category	IV
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Operating altitude	0...2000 m
Ambient air temperature for operation	-30…70 °C
Ambient air temperature for storage	-40…80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.500 cm
Package 1 Width	1.800 cm
Package 1 Length	12.700 cm
Package 1 Weight	150.000 g

Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	8.000 cm
Package 2 Width	22.000 cm
Package 2 Length	13.200 cm
Package 2 Weight	1.853 kg
Unit Type of Package 3	S03
Number of Units in Package 3	96
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	15.353 kg

Logistical informations

Country of origin	FR

Contractual warranty

Warranty (in months)	18

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Total lifecycle Carbon footprint	**13 kg CO2 eq.**
Carbon footprint of the manufacturing phase [A1 to A3]	**1 kg CO2 eq.**
Carbon footprint of the distribution phase [A4]	**0 kg CO2 eq.**
Carbon footprint of the installation phase [A5]	**0 kg CO2 eq.**
Carbon footprint of the use phase [B2, B3, B4, B6]	**12 kg CO2 eq.**
Carbon footprint of the end-of-life phase [C1 to C4]	**0.4 kg CO2 eq.**
Environmental Disclosure	**Product Environmental Profile**

Use Better

Materials and Substances

Packaging made with recycled cardboard	**Yes**
Packaging without single use plastic	**Yes**
SCIP Number	**40a4e715-7fff-45ff-88bf-38212f6a80a5**
EU RoHS Directive	**Compliant**
REACh Regulation	**Reference contains Substances of Very High Concern above the threshold**
Halogen-free status	**Halogen free plastic parts product**
PVC free	**Yes**
Silicone-free	**No**

Use Longer

Lifetime extension

Repair	**No**

Use Again

Repack and remanufacture

Recyclability potential, in %	**56**
End of life manual availability	**No need of specific recycling operations**
Take-back	**No**
WEEE Label	**The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins**