

# PTFIX 6/12X2,5-NS35 BU-EX - Distribution block




1221427

<https://www.phoenixcontact.com/gb/products/1221427>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Distribution block, Ex e certified, mounting type: NS 35/7,5, NS 35/15, color: blue



## Your advantages

- Ex e certified
- Flexible use, thanks to DIN rail mounting, direct mounting or adhesive mounting
- Clear wiring, thanks to eleven different color variants
- Time-saving conductor connection, thanks to tool-free Push-in direct connection technology
- Time savings of up to 80 %, thanks to ready-to-mount blocks without manual bridging
- Space savings of up to 50 % on the DIN rail, thanks to transverse mounting

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1221427       |
| Packing unit                         | 8 pc          |
| Minimum order quantity               | 8 pc          |
| Sales key                            | BEA123        |
| Product key                          | BEA123        |
| GTIN                                 | 4063151305888 |
| Weight per piece (including packing) | 35.83 g       |
| Weight per piece (excluding packing) | 35.83 g       |
| Country of origin                    | PL            |

## Technical data

### Notes

|                    |                                                                                                                        |
|--------------------|------------------------------------------------------------------------------------------------------------------------|
| Notes on operation | the blocks can be bridged with one another via the conductor shaft, for corresponding plug-in bridges, see accessories |
|--------------------|------------------------------------------------------------------------------------------------------------------------|

### General

|      |                                                                                                                                                          |
|------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note | The maximum load current of a single clamping unit must not be exceeded.                                                                                 |
|      | For power distribution applications, IEC 60364-4-43.2008; modified + corrigendum Okt. 2008 (DIN VDE 0100-430:2010-10) section 433.2 ff must be observed! |

### Product properties

|                |                            |
|----------------|----------------------------|
| Product type   | Distributor terminal block |
| Number of rows | 1                          |
| Potentials     | 1                          |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                                                 |        |
|-------------------------------------------------|--------|
| Rated surge voltage                             | 8 kV   |
| Maximum power dissipation for nominal condition | 0.77 W |

### Connection data

|                  |                |
|------------------|----------------|
| Stripping length | 8 mm ... 10 mm |
|------------------|----------------|

### Ex data

#### Rated data (ATEX/IECEx)

|                             |                                    |
|-----------------------------|------------------------------------|
| Identification              | Ⓔ II 2 G Ex eb IIC Gb              |
| Operating temperature range | -60 °C ... 110 °C                  |
| Ex-certified accessories    | 1204517 SZF 1-0,6X3,5              |
|                             | 3022276 CLIPFIX 35-5               |
|                             | 3022218 CLIPFIX 35                 |
| List of bridges             | Plug-in bridge / FBS 2-5 / 3030161 |
| Bridge data                 | 23 A (10 mm²)                      |
| Ex temperature increase     | 40 K (40 A / 6 mm²)                |
| Rated insulation voltage    | 400 V                              |
| output                      | (Permanent)                        |

#### Ex level General

|                       |               |
|-----------------------|---------------|
| Rated voltage         | 440 V         |
| Maximum total current | 55 A (10 mm²) |
| output                | (Permanent)   |

# PTFIX 6/12X2,5-NS35 BU-EX - Distribution block



1221427

<https://www.phoenixcontact.com/gb/products/1221427>

## Ex level Terminal point

|                      |                               |
|----------------------|-------------------------------|
| Rated current        | 22.5 A (2.5 mm <sup>2</sup> ) |
| Maximum load current | 27 A (4 mm <sup>2</sup> )     |
| Contact resistance   | 0.5 mΩ                        |

## Ex connection data Terminal point

|                              |                                              |
|------------------------------|----------------------------------------------|
| Stripping length             | 8 mm ... 10 mm                               |
| Nominal cross section        | 2.5 mm <sup>2</sup>                          |
| Rated cross section AWG      | 14                                           |
| Connection capacity rigid    | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Connection capacity AWG      | 26 ... 12                                    |
| Connection capacity flexible | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Connection capacity AWG      | 26 ... 14                                    |
| output                       | (Permanent)                                  |

## Ex level Feed-in contact

|                      |                            |
|----------------------|----------------------------|
| Rated current        | 40 A (6 mm <sup>2</sup> )  |
| Maximum load current | 55 A (10 mm <sup>2</sup> ) |
| Contact resistance   | 0.2 mΩ                     |

## Ex connection data Feed-in contact

|                              |                                            |
|------------------------------|--------------------------------------------|
| Stripping length             | 10 mm ... 12 mm                            |
| Nominal cross section        | 6 mm <sup>2</sup>                          |
| Rated cross section AWG      | 10                                         |
| Connection capacity rigid    | 0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup> |
| Connection capacity AWG      | 20 ... 8                                   |
| Connection capacity flexible | 0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup> |
| Connection capacity AWG      | 20 ... 8                                   |

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 28.6 mm |
| Height             | 58.1 mm |
| Depth on NS 15     | 30.4 mm |
| Depth on NS 35/7,5 | 32.4 mm |

## Material specifications

|                                        |                 |
|----------------------------------------|-----------------|
| Color                                  | blue (RAL 5015) |
| Flammability rating according to UL 94 | V0              |
| Insulating material group              | I               |
| Insulating material                    | PA              |

## Mechanical properties

### Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

1221427

<https://www.phoenixcontact.com/gb/products/1221427>

## Environmental and real-life conditions

### Ambient conditions

|                                          |                                                                                                                              |
|------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)                                                    |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                                                                              |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                                                                              |
| Permissible humidity (operation)         | 20 % ... 90 %                                                                                                                |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                                                                                |

## Mounting


|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

1221427

<https://www.phoenixcontact.com/gb/products/1221427>

## Drawings

Circuit diagram



1221427

<https://www.phoenixcontact.com/gb/products/1221427>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1221427>



**IECEx**

Approval ID: IECExSEV21.0023U



**ATEX**

Approval ID: SEV21ATEX0557U



**CCC**

Approval ID: 2022122313115884



**UKCA-EX**

Approval ID: CML 22UKEX3672U

# PTFIX 6/12X2,5-NS35 BU-EX - Distribution block



1221427

<https://www.phoenixcontact.com/gb/products/1221427>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250118 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000897 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

1221427

<https://www.phoenixcontact.com/gb/products/1221427>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)