



P1



PIN OUT

P1	P2	Color	FAM
1	1	BLUE	RED FAM
2	2	WHITE	
3	3	DRAIN	GREEN FAM
4	4	BLUE	
5	5	WHITE	BLUE FAM
3	3	DRAIN	
9	9	BLUE	BROWN FAM
10	10	WHITE	
11	11	DRAIN	PURPLE FAM
12	12	BLUE	
13	13	WHITE	YELLOW FAM
11	11	DRAIN	
17	17	BLUE	SILVER FAM
18	18	WHITE	
19	19	DRAIN	SHELL
20	20	BLUE	
21	21	WHITE	SHELL
19	19	DRAIN	
23	23	BLUE	SHELL
24	24	WHITE	
22	22	DRAIN	SHELL
6	6	YELLOW	
7	7	ORANGE	SHELL
14	14	RED	
15	15	WHITE	SHELL
16	16	PURPLE	

NOTES:

1. MATERIAL

1.1 DVI CABLE: {[7/0.10TCx1P+D(7/0.10TC)+FAM]x7PCS+7/0.12TCx1P+7/0.12TCx3C} +AM+D(7/0.12TC)+B(16/8/0.12ALM)+BLACK PVC JACKET.

OD:  $\varnothing 7.3 \pm 0.2$  mm

MARKING: VW-1 DVI CABLE 80°C 30V

1.2 DVI(24+1) MALE TO MALE: BLACK INSULATION, GOLD PLATED CONTACTS G/F, NICKEL PLATED SHELL.

1.3 THUMB SCREW TO BE MOLDED BLACK PVC. NICKEL PLATED SCREW.

1.4 ALL HOOD: MOLDED BLACK PVC.

2. ELECTRICAL

2.1 100% OPEN AND SHORT TEST.

2.2 CONDUCTOR RESISTANCE: 5 OHMS MAX.

2.3 INSULATION RESISTANCE: 10 MEGOHMS MIN.

2.4 HI-POT: DC300V/0.01S.

3. PACKAGING: A PC/PE-BAG PACKAGING .

4. ALL MATERIALS ARE REACH COMPLIANT.

P/N CHART

ITEM NO.	L
11.99.5521	1000±30mm
11.99.5525	2000±50mm
11.99.5535	3000±70mm
11.99.5555	5000±70mm

LENGTH TOLERANCE:	SCALE:
X. ± 0.5	FREE
.X ± 0.2	UNIT:
.XX ± 0.1	mm

ANGLE TOLERANCE:	VERSION:
X° ±3°	01
.X° ±1°	PAGE:
	1/1



VALUE DVI Cable, DVI M-M, dual link, black

ENG:

CHECKED:

APPROVED:

REV.	MODIFY DESCRIPTION	DATE
01	ADD THE ONE	2012-01-05
00	NEW ISSUE	2011-03-22