



Product data sheet

Power tools for trade & industry

Cordless Random Orbit Sander

PRO GEX 12V-150-3



Optimal control for high removal rates in the 12V system

The most important data

Sanding pad diameter	150 mm
Orbit diameter	3 mm
No-load speed	4,500 – 9,500 rpm

Part Number 0 601 373 301

Technical data

Technical data

Sanding pad diameter	150 mm
No-load speed	4,500 – 9,500 rpm
Orbital stroke rate	9,000 – 19,000 opm
Eccentricity	1.5 mm
Weight excl. battery	1.1 kg
Orbit diameter	3 mm
Packaging dimensions (width x length x height)	360 x 438 x 177 mm
Battery voltage	12.0 V

Noise/vibration information

Sanding solid wood

Vibration emission value a_h	3.1 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Optimised ergonomic grip with compact and balanced tool design for optimal control
- Fast working progress with high surface quality made possible by brushless motor with 3 mm orbit
- Easy and intuitive operation thanks to HMI and efficient dust collection with dust bag

**HEAVY
DUTY**4500–
9500
min⁻¹/rpm**PROFESSIONAL
12V
SYSTEM**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

