

Eaton 260201

Catalog Number: 260201

Eaton Moeller series NZM - Molded Case Circuit Breaker. Toggle lever locking device, NZM2/3

General specifications



Product Name	Catalog Number
Eaton Moeller series NZM operating element accessory	260201
	EAN
	4015082602017
Product Length/Depth	Product Height
70 mm	95 mm
Product Width	Product Weight
95 mm	0.146 kg
Compliances	Certifications
IEC	UL (File No. E140305)
RoHS conform	CSA-C22.2 No. 5-09
	CSA (File No. 22086)
	UL489
	UL listed
	CSA (Class No. 1437-01)
	UL (Category Control Number DIHS)
	CSA certified
	CE marking
	IEC60947

Product specifications

Used with

NZM2(-4), PN2(-4), N(S)2(-4)

NZM3(-4), PN3(-4), N(S)3(-4)

Type

Accessory, other Toggle lever interlock device

Features

Lockable

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

Resources

Brochures

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-03_NZM2](#)

Drawings

[eaton-general-nzm-tunnel-terminal-dimensions.eps](#)

[eaton-circuit-breaker-padlock-nzm-rotary-handle-dimensions.eps](#)

[eaton-circuit-breaker-device-nzm-mccb-dimensions.eps](#)

Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

mCAD model

[DA-CD-nzm2_3_xkav](#)

[DA-CS-nzm2_3_xkav](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Color

Other

Fitted with:

Padlock

Extension shaft

Frame

NZM2

Suitable for

Switch disconnecter

Power circuit breaker

Degree of protection / NEMA enclosure type

Other



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)