




Switches > DIP & SIP Switches



DIP & SIP Switch Type: **DIP**
Switch Contact Plating Material: **Gold Flash**
Case Color: **Black**
Case Material: **Polyphenylene Sulfide (PPS)**
Sealed Device: **No**

Features

Product Type Features

Leg Style	Gull Wing
DIP & SIP Switch Type	DIP
Sealed Device	No
Actuator Style	Flush Actuator, Slide Actuator

Configuration Features

Number of Positions	7
Number of Switches	7
Configuration (Pole-Throw)	Single Pole - Single Throw

Electrical Characteristics

Contact Current Rating	1 A
Operating Voltage	5 VDC

Body Features

Actuator Color	White
Case Color	Black



Case Material	Polyphenylene Sulfide (PPS)
---------------	-----------------------------

Contact Features

	1.2 µin
PCB Contact Termination Area Plating Material	Nickel
Switch Contact Plating Material	Gold Flash
Contact Base Material	Copper Alloy

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Product Length	19.76 mm[.778 in]
Product Height	3.5 mm[.138 in]

Usage Conditions

Operating Temperature Range	-30 – 85 °C
-----------------------------	-------------

Operation/Application

Assembly Process Feature	Auto-Insert Packaging
--------------------------	-----------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tape & Reel
Packaging Quantity	20

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC



Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 4-1825059-2
ADF08STTR04=DIP S,FLUSH,SMT-GW

TE Part # 5-1825059-4
ADF10STTR04=DIP S,FLUSH,SMT-GW

TE Part # 6-1825059-3
ADF06STR04

TE Part # 1-1825059-8
ADF04STTR04=DIP S,FLUSH,SMT-GW

TE Part # 1-1825059-3
ADF04S04=DIP SWT,FLUSH,SMT-GW

Also in the Series | Alcoswitch ADF

DIP & SIP Switches(10)



Customers Also Bought



TE Part #3-640428-2
02P MTA156 CONN ASSY 22AWG RED



TE Part #3-640601-3
03P MTA156 CONN ASSY 22AWG LF




TE Part #794189-1
04P MINI UMNL2 CAP HSG UL94V0




TE Part #1-794608-2
PIN CONT 20-24 30 GOLD STRIP



TE Part #350654-1
UMNL GRND PIN 20-14 PTPBR




TE Part #643067-2
02P MTA156 MOLDED COVER



TE Part #643067-3
03P MTA156 MOLDED COVER



TE Part #925819-3
MINI AMP-IN 26-22 AWG



TE Part #140760-2
250 FASTON,REC.,22-18 AWG,TPPB



TE Part #794221-1
MINI UMNL2 SOK 22-18 AWG SN

Documents

- CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1825059-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-1825059-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1825059-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

- Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English

3-1825059-1

DIP Switch, Gold Flash Contact Plating, Black, Polyphenylene Sulfide (PPS), 7 Switch,
-30 – 85 °C, Flush Actuator / Slide Actuator, Alcoswitch ADF

