



Brand of NTN corporation

## Technical data

### UCFCE214


Bearing units



## KIT CONTENT

UC214G2, FCE214

## VISUAL (S)



## PRODUCT DEFINITION

<b>Brand</b>	SNR
<b>A - Housing height</b>	33 mm
<b>A1 - Housing foot height / flange height</b>	18 mm
<b>A2 - Total height from mounting surface</b>	44,4 mm
<b>A3 - Centering depth / chamfer dimension</b>	6 mm
<b>B - Width of Inner Ring</b>	74,6 mm
<b>d - Shaft diameter</b>	70 mm



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

### PRODUCT DEFINITION

<b>G - Grease fitting</b>	R1/8"
<b>H3 - Centering dia</b>	150 mm
<b>J - Mounting holes distance</b>	177 mm
<b>L - Housing width / diameter</b>	215 mm
<b>N - Mounting hole dimension</b>	18 mm
<b>S - Distance front side/bearing centre</b>	30,2 mm

### PRODUCT PERFORMANCE

<b>C - Dynamic load rating</b>	62000000 mN
<b>C0 - Static load rating</b>	45000000 mN
<b>Operating temperature min.</b>	253,15 °K
<b>Operating temperature max.</b>	373,15 °K

### OTHER FEATURES

<b>Mass</b>	5,06 kg
<b>Recommended tightening torque for set screw</b>	33 N-m

