



STAINLESS STEEL SPRAY

Anti-corrosion coating in stainless steel finish

KEY FEATURES

- Anti-corrosion coating with stainless steel look
- Double corrosion protection through aluminum and zinc.
- Heat-resistant up to 350 °C without impairment.
- Excellent scratch and abrasion resistance.
- Excellent corrosion protection in marine atmosphere: 1000 hours in salt spray test (ASTM B117).
- Flawless finish, very easy to apply.
- Very good coverage.

AREAS OF APPLICATION

- Used to protect against corrosion on ferrous and non-ferrous metals.
- Corrosion protection and covering of welds on stainless steel.
- Metal structures, door and window frames, gates, stairs, masts, bodywork, cars, trailers, pipelines, boilers, tanks...
- Can also be used as a decorative coating.

APPLICATION

In order for STAINLESS STEEL SPRAY to adhere optimally, it is essential to thoroughly degrease, sand, brush, clean, dust and dry the surfaces completely.

- Do not paint at temperatures below 5 °C.
- Shake the spray can well upside down for 1 to 2 minutes so that the mixing ball mixes solvents, resins and pigments evenly.
- Start the spraying phase by moving the can upright at a distance of 15-25 cm from the surface.
- Spray in slightly overlapping strips and do not hold the can motionless in one direction to avoid dripping.
- For good coverage, alternate movements from left to right and top to bottom.
- Apply several thin coats instead of one thick one that could run.
- Wait 30 minutes between shifts.
- Complete drying takes place after 12 hours.
- When the job is finished, turn the can over and press the spray head to flush the entire spray system. Maintain the pressure until only propellant gas escapes.
- If necessary, clean the spray head with White Spirit.

PHYSICOCHEMICAL PROPERTIES

- Physical state: Liquid
- Color: Gray
- Odor: Organic solvent
- Flash point: < 0 °C
- Boiling point: < 0 °C
- Density: 0.876 g/cm³

PACK SIZE

Aerosol 650/500ml x 12

Part number: **805891**

EAN 13 Code: 3429978058917

STORAGE

Pressure vessel: May burst when heated. Keep away from heat, hot surfaces, sparks, open flames and other sources of ignition. No smoking. Do not puncture or burn, even after use. Protect from sunlight. Do not expose to temperatures above 50°C / 122°F.

This technical data sheet was created on 20.06.25 and replaces all previous editions. The information provided is based on our current knowledge and experience. We draw the user's attention to possible risks if the product is used for purposes other than those intended. This document does not relieve the user of the obligation to know and comply with all the regulations applicable to his activity. The responsibility for all precautions taken in connection with the use of the product lies solely with the user.