



Part Number : [747220001](#)

Product Description : 1-by-2 SFP Ganged Cage,
Elastomeric Gasket, Press-fit

Series Number : 74722

Status : Active

Product Category : High-Speed EMI Cages



Documents & Resources

Drawings

[747220001_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[TS-74722-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	High-Speed EMI Cages
Series	74722
Description	1-by-2 SFP Ganged Cage, Elastomeric Gasket, Press-fit
Application	Module-to-Board
Comments	PCB Thickness: 1.60mm Single Sided Use and 3.00mm Belly-to-belly Use, 2 Ports
Component Type	Cage Assembly
Product Name	SFP
UPC	822348095773

Electrical

Data Rate	10.0 Gbps
-----------	-----------

Physical

EMI Panel / Bezel Mount	Elastomer Gasket
Light Pipes per Port	0
Material - Metal	Copper Alloy
Net Weight	9.000/g
Orientation	Horizontal
Packaging Type	Tray
Port Configuration	1x2

Rear Legs	0
Termination Interface Style	N/A
Thermal Height	N/A
Thermal Solutions	Closed Top

Solder Process Data

Lead-Free Process Capability	N/A
Max-Temp	70

This document was generated on Aug 05, 2025