



## Datasheet HSS Countersink Handle: 25mm

RS Stock number 456-905



High speed steel panel hole countersink tool with red/black injection grip used for deburring holes in metal, wood and plastic. Three fluted construction with inclined angle of 90 degrees.

- Chemical black finish with machinery/grounding flute of panel hole countersink head and p.p./tpr double injection grip
- Heat treated to 60 66HRC for HSS countersink head
- Overall length: 145mm
- Handle style d-6000: 8mm

## **Specification of panel hole countersink tool:**

- Overall length of panel hole countersink head: 31mm (excluded shaft)
- Diameter and flute width of countersink head: 25.20mm/9.5mm (edges for the flute) and diameter of shaft: 10mm
- Twist angle for the top/bottom of individual flutes: 85 degrees
- Across flat for the connect shaft: 8mm (hexagon shank)